# **ON Semiconductor**

## Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com


onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



# FFB5551 **Dual-Chip NPN General-Purpose Amplifier**

#### **Features**

- This device is designed for general-purpose high voltage amplifier.
- E1 is Pin 1.






Figure 1. Device Package

Figure 2. Internal Connection

## **Ordering Information**

Part Number	Top Mark	Package	Packing Method
FFB5551	P1	SC70 6L	Tape and Reel

# **Absolute Maximum Ratings**(1),(2)

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at  $T_A = 25^{\circ}$ C unless otherwise noted.

Symbol	Parameter	Value	Unit
V <sub>CEO</sub>	Collector-Emitter Voltage	160	V
V <sub>CBO</sub>	Collector-Base Voltage	180	V
V <sub>EBO</sub>	Emitter-Base Voltage	6.0	V
I <sub>C</sub>	Collector Current - Continuous	200	mA
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Junction Temperature Range	-55 to 150	°C

#### Notes:

- 1. These ratings are based on a maximum junction temperature of 150°C.
- 2. These are steady-state limits. ON Semiconductor should be consulted on applications involving pulsed or lowduty-cycle operations.

## Thermal Characteristics(3)

Values are at T<sub>A</sub> = 25°C unless otherwise noted.

Symbol	Parameter	Max.	Unit
P <sub>D</sub>	Total Device Dissipation	200	mW
	Derate Above 25°C	1.6	mW/°C
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	625	°C/W

### Note:

3. PCB size: FR-4, 76 mm x 114 mm x 1.57 mm (3.0 inch x 4.5 inch x 0.062 inch) with minimum land pattern size.

## **Electrical Characteristics**

Values are at  $T_A = 25$ °C unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Max.	Unit
BV <sub>CEO</sub>	Collector-Emitter Breakdown Voltage <sup>(4)</sup>	I <sub>C</sub> = 1.0 mA, I <sub>B</sub> = 0	160		V
BV <sub>CBO</sub>	Collector-Base Breakdown Voltage	$I_C = 100 \mu\text{A},  I_E = 0$	180		V
BV <sub>EBO</sub>	Emitter-Base Breakdown Voltage	$I_E = 10 \mu A, I_C = 0$	6.0		V
		V <sub>CB</sub> = 120 V, I <sub>E</sub> = 0		50	nA
I <sub>CBO</sub>	Collector Cut-Off Current	V <sub>CB</sub> = 120 V, I <sub>E</sub> = 0, T <sub>A</sub> = 100°C		50	μА
I <sub>EBO</sub>	Emitter Cut-Off Current	V <sub>EB</sub> = 4.0 V, I <sub>C</sub> = 0		50	nA
	DC Current Gain <sup>(4)</sup>	$V_{CE} = 5 \text{ V}, I_{C} = 1.0 \text{ mA}$	80		
h <sub>FE</sub>		V <sub>CE</sub> = 5 V, I <sub>C</sub> = 10 mA	80	250	
		$V_{CE}$ = 5 V, $I_{C}$ = 50 mA	30		
V <sub>CE</sub> (sat)	Collector-Emitter Saturation Voltage <sup>(4)</sup>	$I_C = 10 \text{ mA}, I_B = 1.0 \text{ mA}$		0.15	V
	Collector-Entitler Saturation Voltage	$I_C = 50 \text{ mA}, I_B = 5.0 \text{ mA}$		0.20	
V <sub>BE</sub> (sat)	Base-Emitter Saturation Voltage <sup>(4)</sup>	$I_C = 10 \text{ mA}, I_B = 1.0 \text{ mA}$		1.0	V
	base-Emitter Saturation Voltage	$I_C = 50 \text{ mA}, I_B = 5.0 \text{ mA}$		1.0	
f <sub>T</sub>	Current Gain Bandwidth Product	V <sub>CE</sub> = 10 V, I <sub>C</sub> = 10 mA, f = 100 MHz	100	300	MHz
C <sub>obo</sub>	Output Capacitance	V <sub>CB</sub> = 10 V, I <sub>E</sub> = 0, f = 1.0 MHz		6.0	pF

#### Note:

4. Pulse test: pulse width  $\leq$  300  $\mu$ s, duty cycle  $\leq$  2.0%.

## **Typical Performance Characteristics**




Figure 3. DC Current Gain




Figure 5. Base-Emitter Saturation Voltage




Figure 4. Collector-Emitter Saturation Voltage




Figure 6. Base-Emitter On Voltage

# **Physical Dimensions**




Figure 7. 6-LEAD, SC70, EIAJ SC-88, 1.25 MM WIDE

30°.

0.46 0.26

DETAIL A

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative