ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor

FFPF20UP60DN 20 A, 600 V, Ultrafast Dual Diode

Features


- Ultrafast Recovery t_{rr} = 70 ns (@ I_F = 10 A)
- Max Forward Voltage, V_F = 2.2 V (@ T_C = 25°C)
- · 600 V Reverse Voltage and High Reliability
- · Avalanche Energy Rated
- · RoHS Compliant


Applications

- · General Purpose
- · SMPS, Power Switching Circuits
- · Boost Diode in Continuous Mode Power Factor Corrections

Description

The FFPF20UP60DN is a ultrafast dual diode with low forward voltage drop. This device is intended for use as freewheeling and clamping diodes in a variety of switching power supplies and other power switching applications. It is specially suited for use in switching power supplies and industrial application.





1. Anode 2. Cathode 3. Anode

Absolute Maximum Ratings $T_C = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter	Rating	Unit	
V_{RRM}	Peak Repetitive Reverse Voltage	600	V	
V_{RWM}	Working Peak Reverse Voltage	600	V	
V_R	DC Blocking Voltage	600	V	
I _{F(AV)}	Average Rectified Forward Current @ T _C = 103°C	10	Α	
I _{FSM}	Non-repetitive Peak Surge Current 60Hz Single Half-Sine Wave	50	А	
T _J , T _{STG}	Operating and Storage Temperature Range	-65 to +175	°C	

Thermal Characteristics

Symbol	Parameter	Max.	Unit	
$R_{\theta JC}$	Maximum Thermal Resistance, Junction to Case	7	°C/W	

Package Marking and Ordering Information

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Quantity
FFPF20UP60DNTU	FFPF20UP60DN	TO-220F	Tube	N/A	N/A	50

Electrical Characteristics $T_C = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter	Min.	Тур.	Max.	Unit	
V/ 1	I _F = 10 A	$T_{\rm C} = 25^{\rm o}{\rm C}$ $T_{\rm C} = 100^{\rm o}{\rm C}$	-	-	2.2	V
V _F 1	I _F = 10 A	$T_{\rm C} = 100^{\rm o}{\rm C}$	-	-	2.0	V
I _R 1	V _R = 600 V	$T_{\rm C} = 25^{\rm o}{\rm C}$ $T_{\rm C} = 100^{\rm o}{\rm C}$	-	-	100	μА
	V _R = 600 V	$T_{\rm C} = 100^{\rm o}{\rm C}$	-	-	500	
t _{rr}	$I_F = 10 \text{ A}, \text{ di}_F/\text{dt} = 200 \text{ A/}\mu\text{s}, \text{ V}_R = 390 \text{ V}$	T _C = 25°C	-	53	70	ns
t _{rr}	$I_F = 1 \text{ A, di}_F/\text{dt} = 100 \text{ A/}\mu\text{s, V}_R = 30 \text{ V}$	T _C = 25°C	-	30	40	ns
Irr			-	1.5	2	Α
Q _{rr}			-	20	30	nC
W _{AVL}	Avalanche Energy (L = 40 mH)		10	-	-	mJ

Notes:
1: Pulse: Test Pulse width = 300μs, Duty Cycle = 2%

Test Circuit and Waveforms




Figure 1. Diode Reverse Recovery Test Circuit & Waveform




Figure 2. Unclamped Inductive Switching Test Circuit & Waveform

Typical Performance Characteristics

Figure 3. Typical Forward Voltage Drop vs. Forward Current




Figure 5. Typical Junction Capacitance




Figure 7. Typical Reverse Recovery Current vs. di_F/dt




Figure 4. Typical Reverse Current vs. Reverse Voltage




Figure 6. Typical Reverse Recovery Time vs. di_F/dt





Figure 8. Forward Current Derating Curve



Package Dimensions




Figure 9. TO-220F 3L - TO220, MOLDED, 3LD, FULL PACK, EIAJ SC91, STRAIGHT LEAD

Package drawings are provided as a service to customers considering ON Semicinductor components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a ON Semicinductor Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specif-ically the warranty therein, which covers ON Semicinductor products.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative