onsemi

MOSFET – N-Channel, POWERTRENCH[®]

200 V

FDC2612

General Description

This N–Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low $R_{DS(ON)}$ and fast switching speed.

Features

- 1.1 A, 200 V. $R_{DS(ON)} = 725 \text{ m}\Omega @ V_{GS} = 10 \text{ V}$
- High Performance Trench Technology for Extremely Low R_{DS(ON)}
- High Power and Current Handling Capability
- Fast Switching Speed
- Low Gate Charge (8 nC Typical)
- This Device is Pb-Free, Halide Free and is RoHS Compliant

Applications

• DC/DC Converter

V _{DSS}	R _{DS(ON)} MAX	I _D MAX
200 V	725 mΩ @ 10 V	1.1 A




TSOT23 6-Lead (SUPERSOT™-6) CASE 419BL

MARKING DIAGRAM



M = Date Code

PIN CONNECTION



ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet.

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter			Unit
V _{DSS}	Drain-Source Voltage			V
V _{GSS}	Gate-Source Voltage		±20	V
I _D	Drain Current	Continuous (Note 1a)	1.1	А
		Pulsed	4	
PD	Maximum Power Dissipation	(Note 1a)	1.6	W
		(Note 1b)	0.8	
T _J , T _{STG}	Operating and Storage Junction Temperature Range		-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbo	Parameter	Ratings	Unit
Reja	Thermal Resistance, Junction-to-Ambient (Note 1a)	78	°C/W
Rejc	Thermal Resistance, Junction-to-Case (Note 1)	30	°C/W

1. $R_{\theta,JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta,JC}$ is guaranteed by design while $R_{\theta,CA}$ is determined by the user's board design.



a. 78°C/W when mounted on a 1 in² pad of 2 oz copper



b. 156°C/W when mounted on a minimum pad of 2 oz copper

Scale 1:1 on letter size paper

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions Min		Тур	Max	Unit
OFF CHAR	ACTERISTICS			-	-	-
BV_DSS	Drain–Source Breakdown Voltage	$V_{GS} = 0 \text{ V}, \text{ I}_{D} = 250 \ \mu\text{A}$	200	-	_	V
$\frac{\Delta \text{BV}_{\text{DSS}}}{\Delta \text{T}_{\text{J}}}$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, Referenced to 25° C	-	246	-	mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 160 \text{ V}, V_{GS} = 0 \text{ V}$	-	-	1	μΑ
I _{GSSF}	Gate–Body Leakage, Forward	$V_{GS} = 20 \text{ V}, V_{DS} = 0 \text{ V}$	-	-	100	nA
I _{GSSR}	Gate-Body Leakage, Reverse	$V_{GS} = -20 \text{ V}, V_{DS} = 0 \text{ V}$	-	-	-100	nA

ON CHARACTERISTICS (Note 2)

V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$	2	4	4.5	V
$\frac{\Delta V_{\text{GS(th)}}}{\Delta T_{\text{J}}}$	Gate Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, Referenced to 25° C	-	-8.7	-	mV/°C
R _{DS(on)}	Static Drain–Source On Resistance	$V_{GS} = 10 \text{ V}, I_D = 1.1 \text{ A}$ $V_{GS} = 10 \text{ V}, I_D = 1.1 \text{ A}, T_J = 125^{\circ}\text{C}$	-	605 1133	725 1430	mΩ
I _{D(on)}	On-State Drain Current	V_{GS} = 10 V, V_{DS} = 10 V	4	-	-	А
9 _{FS}	Forward Transconductance	$V_{DS} = 10 \text{ V}, \text{ I}_{D} = 1.1 \text{ A}$	-	4.4	-	S

DYNAMIC CHARACTERISTICS

C _{iss}	Input Capacitance	V_{DS} = 100 V, V_{GS} = 0 V, f = 1.0 MHz	_	234	-	pF
C _{oss}	Output Capacitance		-	18	-	pF
C _{rss}	Reverse Transfer Capacitance		-	8	-	pF

SWITCHING CHARACTERISTICS (Note 2)

t _{d(on)}	Turn–On Delay Time	$V_{DD} = 100 \text{ V}, \text{ I}_{D} = 1 \text{ A}, \text{ V}_{GS} = 10 \text{ V},$	-	6	12	ns
t _r	Turn–On Rise Time	$R_{GEN} = 6 \Omega$	-	6	12	ns
t _{d(off)}	Turn–Off Delay Time		-	17	30	ns
t _f	Turn–Off Fall Time		-	8	16	ns
Qg	Total Gate Charge	V_{DS} = 100 V, I _D = 1.1 A, V _{GS} = 10 V	-	8	11	nC
Q _{gs}	Gate-Source Charge		-	1.6	-	nC
Q _{gd}	Gate–Drain Charge		_	2.2	-	nC

DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATING

۱ _S	Maximum Continuous Drain–Source Diode Forward Current			_	1.3	Α
V _{SD}	Drain–Source Diode Forward Voltage	-	0.8	1.2	V	
t _{rr}	Diode Reverse Recovery Time	$I_F = 1.1 \text{ A}, d_{iF}/d_t = 300 \text{ A/}\mu\text{s} \text{ (Note 2)}$	-	74.5	-	nS
Q _{rr}	Diode Reverse Recovery Charge		-	194	-	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 2. Pulse Test: Pulse Width < $300 \ \mu$ s, Duty cycle < 2.0%.

TYPICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)






Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature

TYPICAL CHARACTERISTICS (continued)





PACKAGE MARKING AND ORDERING INFORMATION


Device	Device Marking	Package Type	Reel Size	Tape Width	Shipping [†]
FDC2612	262	TSOT23 6–Lead (Pb–Free)	7"	8 mm	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

SUPERSOT is trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.





ON Semiconductor and ()) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>