MOSFET – N-Channel, UltraFET Trench

200 V, 3.9 A, 70 m Ω

FDS2672

General Description

This single N–Channel MOSFET is produced using **onsemi**'s advanced UltraFET Trench process that has been especially tailored to minimize the on–state resistance and yet maintain superior switching performance.

Features

- Max $r_{DS(on)} = 70 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, $I_D = 3.9 \text{ A}$
- Max $r_{DS(on)} = 80 \text{ m}\Omega$ at $V_{GS} = 6 \text{ V}$, $I_D = 3.5 \text{ A}$
- Fast Switching Speed
- High Performance Trench Technology for Extremely Low RDS(on)
- These Device is Pb–Free, Halide Free and are RoHS Compliant

Applications

• DC-DC Conversion

ABSOLUTE MAXIMUM RATINGS $T_A = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter	Value	Unit
V _{DS}	Drain to Source Voltage	200	V
V _{GS}	Gate to Source Voltage	±20	V
ID	Drain Current – Continuous (Note 1a) – Pulsed	3.9 50	A
E _{AS}	Single Pulse Avalanche Energy (Note 3)	37.5	mJ
P _D	Power Dissipation (Note 1a) (Note 1b)	2.5 1.0	W
T _J , T _{STG}	Operating and Storage Junction Temperature Range	–55 to +150	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS


Symbol	Parameter	Value	Unit
$R_{ extsf{ heta}JC}$	Thermal Resistance, Junction-to-Case (Note 1)	25	°C/W
R _{θJA}	Thermal Resistance, Junction-to-Ambient (Note 1a) (Note 1b)	50 125	°C/W



MARKING DIAGRAM



PIN ASSIGNMENT



ORDERING INFORMATION

Device	Package	Shipping
FDS2672	SOIC8 (Pb-Free)	2500 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, <u>BRD8011/D</u>.

ELECTRICAL CHARACTERISTICS T_{.1} = 25°C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHAR	ACTERISTICS	•				
BV _{DSS}	Drain to Source Breakdown Voltage	$I_{D} = 250 \ \mu A, \ V_{GS} = 0 \ V$	200	-	-	V
$\frac{\Delta \text{BV}_{\text{DSS}}}{\Delta \text{T}_{\text{J}}}$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, Referenced to 25° C	-	206	-	mV/°C
I _{DSS}	Zero Gate Voltage Drain Current		-	-	1 10	μΑ
I _{GSSF}	Gate to Source Leakage Current	$V_{GS} = \pm 20 V$	-	-	±100	nA
N CHARAG	CTERISTICS (Note 2)					
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \ \mu A$	2	2.9	4	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, Referenced to 25° C	-	-11	_	mV/°C
r _{DS(on)}	Drain to Source On-Resistance	$ \begin{array}{l} V_{GS} = 10 \text{ V}, \text{ I}_{D} = 3.9 \text{ A} \\ V_{GS} = 6 \text{ V}, \text{ I}_{D} = 3.5 \text{ A}, \\ V_{GS} = 10 \text{ V}, \text{ I}_{D} = 3.9 \text{ A}, \text{ T}_{J} = 125^{\circ}\text{C} \end{array} $	_ _ _	58 63 124	70 80 148	mΩ
9fs	Forward Transconductance	V _{DS} = 10 V, I _D = 3.9 A	-	15	-	S
YNAMIC C	HARACTERISTICS					
C _{iss}	Input Capacitance	$V_{DS} = 100 \text{ V}, V_{GS} = 0 \text{ V},$	-	1905	2535	pF
C _{oss}	Output Capacitance	f = 1 MHz	_	100	135	pF
C _{rss}	Reverse Transfer Capacitance		_	30	45	pF
Rg	Gate Resistance	f = 1 MHz	-	0.7	-	Ω
WITCHING	CHARACTERISTICS			-		
t _{d(on)}	Turn-On Delay Time	V_{DD} = 100 V, I _D = 3.9 A, V _{GS} = 10 V, R _{GS} = 6 Ω	-	22	35	ns
t _r	Rise Time		_	10	20	ns
t _{d(off)}	Turn-Off Delay Time		_	35	56	ns
t _f	Fall Time		-	10	20	ns
Q _{g(TOT)}	Total Gate Charge at 10 V	V _{DS} = 100 V, I _D = 3.9 A	-	33	46	nC
Q _{gs}	Gate to Source Gate Charge	-	-	11	-	nC
Q _{gd}	Gate to Drain Charge	7	_	7	_	nC

DRAIN-SOURCE DIODE CHARACTERISTICS

V _{SD}	Source to Drain Diode Voltage	$V_{GS} = 0 \text{ V}, \text{ I}_{S} = 3.9 \text{ A}$	_	0.75	1.2	V
t _{rr}	Reverse Recovery Time	$I_F = 3.9 \text{ A,d}_{if} / d_t = 100 \text{ A} / \mu \text{s}$	-	67	101	ns
Q _{rr}	Reverse Recovery Change		-	179	269	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

NOTES:

1. R_{0JA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{0,JC} is guaranteed by design while R_{0CA} is determined by the user's board design.



a) 50°C/W (10 s) 62.5°C/W steady state when mounted on a 1in² pad of 2 oz copper.




b) 125°C/W when mounted on a minimum pad.

Scale 1:1 on letter size paper

- 2. Pulse Test: Pulse Width < 300 μ s, Duty Cycle < 2%.
- 3. Starting $T_J = 25^{\circ}C$, L = 3 mH, $I_{AS} = 5$ Å, $V_{DD} = 100$ V, $V_{GS} = 10$ V.

TYPICAL CHARACTERISTICS (T_J = 25°C UNLESS OTHERWISE NOTED)



www.onsemi.com

TYPICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ UNLESS OTHERWISE NOTED) (CONTINUED)







Figure 12. Single Pulse Maximum Power Dissipation

TYPICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ UNLESS OTHERWISE NOTED) (CONTINUED)









© Semiconductor Components Industries, LLC, 2019

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>