

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.

FAIRCHILD

SEMICONDUCTOR®

December 2008

FDS8882 N-Channel PowerTrench[®] MOSFET 30 V, 9 A, 20.0 m Ω

Features

- Max $r_{DS(on)}$ = 20.0 m Ω at V_{GS} = 10 V, I_D = 9 A
- Max $r_{DS(on)}$ = 22.5 m Ω at V_{GS} = 4.5 V, I_D = 8 A
- High performance trench technology for extremely low r_{DS(on)} and fast switching
- High power and current handling capability
- Termination is Lead-free and RoHS Compliant





General Description

The FDS8882 has been designed to minimize losses in power conversion application. Advancements in both silicon and package technologies have been combined to offer the lowest $r_{DS(on)}$ while maintaining excellent switching performance.

Applications

- Notebook System Regulators
- DC/DC Converters





MOSFET Maximum Ratings T_A = 25 °C unless otherwise noted

Symbol	Parameter			Ratings	Units	
V _{DS}	Drain to Source Voltage			30	V	
V _{GS}	Gate to Source Voltage			±20	V	
	Drain Current -Continuous			9	٨	
D	-Pulsed			21	— A	
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	32	mJ	
D	Power Dissipation	T _A = 25 °C	(Note 1a)	2.5	w	
PD	Power Dissipation	T _A = 25 °C	(Note 1b)	1.0	VV	
T _J , T _{STG}	Operating and Storage Junction Tempe	rature Range		-55 to +150	°C	

Thermal Characteristics

$R_{ ext{ heta}JC}$	Thermal Resistance, Junction to Case	(Note 1)	25	°C/W
R_{\thetaJA}	Thermal Resistance, Junction to Ambient	(Note 1a)	50	°C/w

Package Marking and Ordering Information


Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDS8882	FDS8882	SO8	13 "	12 mm	2500 units

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Chara	cteristics					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_{D} = 250 \ \mu A, V_{GS} = 0 \ V$	30			V
$\frac{\Delta BV_{DSS}}{\Delta T_{J}}$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \ \mu\text{A}$, referenced to 25 °C		4		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V			1	μA
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$			±100	nA
On Chara	cteristics					
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 250 \ \mu A$	1.0	1.7	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu\text{A}$, referenced to 25 °C		-6		mV/°C
r _{DS(on)} Static Drain to Source On R		V _{GS} = 10 V, I _D = 9 A		13.2	20.0	
	Static Drain to Source On Resistance	$V_{GS} = 4.5 \text{ V}, \text{ I}_{D} = 8 \text{ A}$		16.6	22.5	mΩ
		$V_{GS} = 10 \text{ V}, \ I_D = 9 \text{ A}, \text{ T}_J = 125 \text{ °C}$		18.5	28.0	
9 _{FS}	Forward Transconductance	$V_{DS} = 5 V, I_{D} = 9 A$		36		S
Dynamic	Characteristics					
C _{iss}	Input Capacitance			707	940	pF
C _{oss}	Output Capacitance	─ V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHz		138	185	pF
C _{rss}	Reverse Transfer Capacitance			88	135	pF
R _g	Gate Resistance			1.8		Ω
Switching	g Characteristics					
t _{d(on)}	Turn-On Delay Time			7	14	ns
t _r	Rise Time	$V_{DD} = 15 \text{ V}, \text{ I}_{D} = 9 \text{ A},$		3	10	ns
t _{d(off)}	Turn-Off Delay Time	$-V_{GS}$ = 10 V, R _{GEN} = 6 Ω		19	35	ns
t _f	Fall Time			4	10	ns
Qg	Total Gate Charge	$V_{GS} = 0 V \text{ to } 10 V$		14	20	nC
Qg	Total Gate Charge	$V_{GS} = 0 V \text{ to } 5 V$ $V_{DD} = 15 V,$ $I_{D} = 9 A$		8	11	nC
Q _{gs}	Gate to Source Charge	ID - 9 X		2.2		nC
Q _{gd}	Gate to Drain "Miller" Charge			2.8		nC
Drain-Sou	urce Diode Characteristics					
		V _{GS} = 0 V, I _S = 9 A		0.8	1.2	
V _{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 V, I_S = 2.1 A$		0.7	1.2	V
t _{rr}	Reverse Recovery Time	- I _F = 9 A, di/dt = 100 A/μs		17	31	ns
_		$T_{F} = 9 A$, $u/u = 100 A/\mu s$				-

NOTES:

 Q_{rr}

1. R_{01A} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. R_{0JC} is guaranteed by design while R_{0CA} is determined by the user's board design.



Reverse Recovery Charge

a) 50 °C/W when mounted on a 1 in² pad of 2 oz copper.



b) 125 °C/W when mounted on a minimum pad.


6


12

nC


2

FDS8882 N-Channel PowerTrench[®] MOSFET





FDS8882 N-Channel PowerTrench[®] MOSFET





SEMICONDUCTOR

TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

Build it Now™	FRFET [®]	Programmable Active Droop [™]	the
CorePLUS™	Global Power Resource SM	QFET [®]	p⊍wer
CorePOWER™	Green FPS™	QS™	franchise
CROSSVOLT™	Green FPS [™] e-Series [™]	Quiet Series™	TinyBoost™
CTL™	GTO™	RapidConfigure™	TinyBuck™
Current Transfer Logic™	IntelliMAX™		TinyLogic®
EcoSPARK®	ISOPLANAR™		TINYOPTO™
EfficentMax™	MegaBuck™	Saving our world, 1mW /W /kW at a time™	TinyPower™
			TinyPWM™
EZSWITCH™ *	MICROCOUPLER™	SmartMax [™]	TinyWire™
	MicroFET™	SMART START™	μSerDes™
	MicroPak™	SPM®	
R	MillerDrive™	STEALTH™	\mathcal{N}
F	MotionMax™	SuperFET™	SerDes
Fairchild®	Motion-SPM [™]	SuperSOT™-3	UHC®
Fairchild Semiconductor [®]	OPTOLOGIC®	SuperSOT™-6	Ultra FRFET™
FACT Quiet Series™	OPTOPLANAR®	SuperSOT™-8	UniFET™
FACT [®]	®	SupreMOS™	VCX™
FAST®		SyncFET™	VisualMax™
FastvCore™	U.	,	XS™
FlashWriter [®] *	PDP SPM™		
FPS™	Power-SPM [™]	The Power Franchise [®]	
F-PFS™	PowerTrench [®]	The Fower Franchise	
1 -FI 0	PowerXS™		

* EZSWITCH™ and FlashWriter[®] are trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Farichild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Farichild strongly encourages customers to purchase Farichild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Farichild's full range of up-to-date technical and product information. Fairchild and our Authorized porter go or other assistance for parts bought from Unauthorized Sources. Farichild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC