### **ON Semiconductor**

### Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor®

### FDS8949-F085

# Dual N-Channel Logic Level PowerTrench $^{(\!R\!)}$ MOSFET 40V, 6A, 29m $\Omega$

#### **Features**

- Max  $r_{DS(on)} = 29m\Omega$  at  $V_{GS} = 10V$
- Max  $r_{DS(on)} = 36m\Omega$  at  $V_{GS} = 4.5V$
- Low gate charge
- High performance trench technology for extremely low <sup>r</sup>DS(on)
- High power and current handling capability
- Qualified to AEC Q101
- RoHS compliant

## General Description These N-Channel Logic Le

These N-Channel Logic Level MOSFETs are produced using ON Semiconductor's advanced PowerTrench® process that has been especially tailored


PowerTrench process that has been especially tailored to minimize the on-state resistance and yet maintain superior switching performance.


These devices are well suited for low voltage and battery powered applications where low in-line power loss and fast switching are required.



#### **Applications**

- Inverter
- Power suppliers





### MOSFET Maximum Ratings T<sub>A</sub> = 25°C unless otherwise noted

Symbol	bol Parameter		Ratings	Units
$V_{DS}$	Drain to Source Voltage		40	V
$V_{GS}$	Gate to Source Voltage		±20	V
I <sub>D</sub>	Drain Current -Continuous	(Note 1a)	6	٨
	-Pulsed		20	Α
E <sub>AS</sub>	Drain-Source Avalanche Energy	(Note 3)	26	mJ
	Power Dissipation for Dual Operation		2	
$P_D$	Power Dissipation for Single Operation	(Note 1a)	1.6	W
		(Note 1b)	0.9	
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Junction Temperature Range		-55 to 150	°C

### **Thermal Characteristics**

$R_{\theta JA}$	Thermal Resistance-Single operation, Junction to Ambient	(Note 1a)	81	
$R_{\theta JA}$	Thermal Resistance-Single operation, Junction to Ambient	(Note 1b)	135	°C/W
$R_{\theta JC}$	Thermal Resistance, Junction to Case	(Note 1)	40	

### **Package Marking and Ordering Information**

Device Marking	Device	Reel Size	Tape Width	Quantity
FDS8949	FDS8949-F085	13"	12mm	2500 units

### **Electrical Characteristics** $T_J = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units			
Off Chara	Off Characteristics								
$BV_{DSS}$	Drain to Source Breakdown Voltage	I <sub>D</sub> = 250μA, V <sub>GS</sub> = 0V	40			V			
$\frac{\Delta BV_{DSS}}{\Delta T_{J}}$	Breakdown Voltage Temperature Coefficient	I <sub>D</sub> = 250μA, referenced to 25°C		33		mV/°C			
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> = 32V, V <sub>GS</sub> = 0V			1	μА			
טאטי	Zero edic voltage Brain Garrent	T <sub>J</sub> = 55°C			10	μΑ			
$I_{GSS}$	Gate to Source Leakage Current	$V_{GS} = \pm 20V, V_{DS} = 0\overline{V}$			±100	nA			

### On Characteristics (Note 2)

$V_{GS(th)}$	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = 250 \mu A$	1	1.9	3	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I <sub>D</sub> = 250μA, referenced to 25°C		-4.6		mV/°C
		V <sub>GS</sub> = 10V, I <sub>D</sub> = 6A		21	29	
r <sub>DS(on)</sub>	Drain to Source On Resistance	V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 4.5A		26	36	mΩ
		V <sub>GS</sub> = 10V, I <sub>D</sub> = 6A,T <sub>J</sub> = 125°C		29	43	
9 <sub>FS</sub>	Forward Transconductance	$V_{DS} = 10V, I_{D} = 6A$		22		S

### **Dynamic Characteristics**

C <sub>iss</sub>	Input Capacitance	V = 20V V = 0V	715	955	pF
C <sub>oss</sub>	Output Capacitance	V <sub>DS</sub> = 20V, V <sub>GS</sub> = 0V, f = 1MHz	105	140	pF
C <sub>rss</sub>	Reverse Transfer Capacitance	1 - 1101112	60	90	pF
$R_g$	Gate Resistance	f = 1MHz	1.1		Ω


### **Switching Characteristics**

t <sub>d(on)</sub>	Turn-On Delay Time		9	18	ns
t <sub>r</sub>	Rise Time	$V_{DD} = 20V, I_D = 1A$ 	5	10	ns
t <sub>d(off)</sub>	Turn-Off Delay Time	V <sub>GS</sub> = 10V, N <sub>GEN</sub> = 052	23	37	ns
t <sub>f</sub>	Fall Time		3	6	ns
$Q_g$	Total Gate Charge		7.7	11	nC
Q <sub>gs</sub>	Gate to Source Gate Charge	$V_{DS} = 20V, I_D = 6A, V_{GS} = 5V$	2.4		nC
$Q_{gd}$	Gate to Drain "Miller" Charge		2.8		nC

#### **Drain-Source Diode Characteristics** and Maximum Ratings

$V_{SD}$	Source to Drain Diode Forward Voltage	$V_{GS} = 0V, I_{S} = 6A \text{ (note 2)}$	0.8	1.2	V
t <sub>rr</sub>	Reverse Recovery Time (note 3)	$I_{\rm F}$ = 6A, $d_{\rm iF}/d_{\rm f}$ = 100A/µs	17	26	ns
Q <sub>rr</sub>	Reverse Recovery Charge	iF - 0A, α <sub>iF</sub> /α <sub>t</sub> - 100A/μs	7	11	nC

1: R<sub>0JA</sub> is the sum of the junction-to-case and case-to- ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.  $R_{\theta JC}$  is guaranteed by design while  $R_{\theta JA}$  is determined by the user's board design.



a) 81°C/W when mounted on a 1in<sup>2</sup> pad of 2 oz copper



b) 135°C/W when mounted on a minimum pad.

Scale 1:1 on letter size paper

2: Pulse Test: Pulse Width < 300 us, Duty Cycle < 2.0%.

**3:** Starting  $T_J = 25^{\circ}C$ , L = 1mH,  $I_{AS} = 7.3$ A,  $V_{DD} = 40$ V,  $V_{GS} = 10$ V.

### Typical Characteristics T<sub>J</sub> = 25°C unless otherwise noted




Figure 1. On Region Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3. Normalized On Resistance vs Junction Temperature




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

### Typical Characteristics T<sub>J</sub> = 25°C unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs
Ambient Temperature




Figure 11. Forward Bias Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation




Figure 13. Transient Thermal Response Curve

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative