# **IGBT - Field Stop**

600 V, 60 A

## FGH60N60SMD-F085

## Description

Using Novel Field Stop IGBT Technology, ON Semiconductor's new series of Field Stop Trench IGBTs offer the optimum performance for Automotive chargers, Solar Inverter, UPS and Digital Power Generator where low conduction and switching losses are essential.

## Features

- Maximum Junction Temperature:  $T_J = 175^{\circ}C$
- Positive Temperature Co-efficient for easy Parallel Operating
- High Current Capability
- Low Saturation Voltage:  $V_{CE(sat)} = 1.8 \text{ V} (Typ.) @ I_C = 60 \text{ A}$
- High Input Impedance
- Tightened Parameter Distribution
- This Device is Pb-Free and is RoHS Compliant
- Qualified to Automotive Requirements of AEC-Q101


## Applications


- Automotive Chargers, Converters, High Voltage Auxiliaries
- Solar Inverters, UPS, SMPS, PFC



## **ON Semiconductor®**


## www.onsemi.com





TO-247-3LD CASE 340CK

## MARKING DIAGRAM



#### **ORDERING INFORMATION**

See detailed ordering and shipping information on page 2 of this data sheet.

#### **ABSOLUTE MAXIMUM RATINGS**

Symbol	Description		Ratings	Unit	
V <sub>CES</sub>	Collector to Emitter Voltage		600	V	
V <sub>GES</sub>	Gate to Emitter Voltage		±20	V	
Ι <sub>C</sub>	Collector Current	$T_{C} = 25^{\circ}C$	120	А	
		$T_{C} = 100^{\circ}C$	60	А	
I <sub>CM</sub> (Note 1)	Pulsed Collector Current		180	А	
١ <sub>F</sub>	Diode Forward Current	$T_{C} = 25^{\circ}C$	60	А	
		T <sub>C</sub> = 100°C	30	А	
I <sub>FM</sub> (Note 1)	Pulsed Diode Maximum Forward Current		180	А	
P <sub>D</sub>	Maximum Power Dissipation	$T_{C} = 25^{\circ}C$	600	W	
		T <sub>C</sub> = 100°C	300	W	
TJ	Operating Junction Temperature		–55 to +175	°C	
T <sub>STG</sub>	Storage Temperature Range		–55 to +175	°C	
ΤL	Maximum Lead Temp. for Soldering Purposes, 1/8" from Case for 5 Seconds		300	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Repetitive rating: Pulse width limited by max. junction temperature.

## THERMAL CHARACTERISTICS

Symbol	Parameter	Max.	Unit
R <sub>θJC</sub> (IGBT) (Note 2)	Thermal Resistance, Junction to Case	0.25	°C/W
$R_{\theta JC}$ (Diode)	Thermal Resistance, Junction to Case	1.1	°C/W
R <sub>0JA</sub>	Thermal Resistance, Junction to Ambient (PCB Mount) (Note 2)	45	°C/W

2. Rthjc for TO-247 : according to Mil standard 883-1012 test method. Rthja for TO-247 : according to JESD51-2, test method environmental condition and JESD51-10, test boards for through hole perimeter leaded package thermal measurements. JESD51-3 : Low Effective Thermal Conductivity Test Board for Leaded Surface Mount Package.

#### PACKAGE MARKING AND ORDERING INFORMATION

Device Marking	Device	Package	Packing Method	Qty per Tube
FGH60N60SMD	FGH60N60SMD-F085	TO-247	Tube	30ea

## ELECTRICAL CHARACTERISTICS OF THE IGBT

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit	
OFF CHARAC	TERISTICS			•		•	
BV <sub>CES</sub>	Collector to Emitter Breakdown Voltage	$V_{GE}$ = 0 V, I <sub>C</sub> = 250 µA	600	-	-	V	
$\Delta \text{BV}_{\text{CES}}  /  \Delta \text{T}_{\text{J}}$	Temperature Coefficient of Breakdown Voltage	V <sub>GE</sub> = 0 V, I <sub>C</sub> = 250 μA	-	0.22	-	V/°C	
I <sub>CES</sub>	Collector Cut-Off Current	$V_{CE} = V_{CES}, V_{GE} = 0 V$	-	-	250	μΑ	
		I <sub>CES</sub> at 80 % *BVCES, 175 °C	-	-	1100		
I <sub>GES</sub>	G-E Leakage Current	$V_{GE} = V_{GES}, V_{CE} = 0 V$	-	-	±400	nA	
ON CHARACT	ERISTICS			•			
V <sub>GE(th)</sub>	G-E Threshold Voltage	$I_C$ = 250 $\mu$ A, $V_{CE}$ = $V_{GE}$	3.5	4.7	6.0	V	
V <sub>CE(sat)</sub>	Collector to Emitter Saturation Voltage	I <sub>C</sub> = 60 A, V <sub>GE</sub> = 15 V,	-	1.8	2.5	V	
		I <sub>C</sub> = 60 A, V <sub>GE</sub> = 15 V, T <sub>C</sub> = 175°C	-	2.14	-	v	
OYNAMIC CHA	ARACTERISTICS						
C <sub>ies</sub>	Input Capacitance	V <sub>CE</sub> = 30 V, V <sub>GE</sub> = 0 V, f = 1 MHz	-	2780	3700	pF	
C <sub>oes</sub>	Output Capacitance		-	260	345	pF	
C <sub>res</sub>	Reverse Transfer Capacitance		-	80	110	pF	
WITCHING C	HARACTERISTICS						
T <sub>d(on)</sub>	Turn–On Delay Time	$\label{eq:V_CC} \begin{array}{l} V_{CC} = 400 \; V, \; I_C = 60 \; A, \\ R_G = 3 \; \Omega, \; V_{GE} = 15 \; V, \\ Inductive \; Load, \; T_C = 25^\circ C \end{array}$	-	22	29	ns	
Tr	Rise Time		-	46	60	ns	
T <sub>d(off)</sub>	Turn-Off Delay Time		-	116	151	ns	
T <sub>f</sub>	Fall Time		-	14	18	ns	
Eon	Turn-On Switching Loss		-	1.59	2.23	mJ	
E <sub>off</sub>	Turn-Off Switching Loss		-	0.39	0.55	mJ	
E <sub>ts</sub>	Total Switching Loss		-	1.98	2.78	mJ	
T <sub>d(on)</sub>	Turn–On Delay Time	$V_{CC} = 400 \text{ V}, \text{ I}_{C} = 60 \text{ A},$	-	22	28	ns	
T <sub>r</sub>	Rise Time	$R_G = 3 \Omega$ , $V_{GE} = 15 V$ , Inductive Load, $T_C = 175^{\circ}C$	-	44	58	ns	
T <sub>d(off)</sub>	Turn-Off Delay Time		-	124	161	ns	
T <sub>f</sub>	Fall Time		-	15	20	ns	
Eon	Turn-On Switching Loss		-	2.41	3.13	mJ	
E <sub>off</sub>	Turn–Off Switching Loss		-	1.08	1.42	mJ	
E <sub>ts</sub>	Total Switching Loss	1	-	3.49	4.55	mJ	
Qg	Total Gate Charge	$V_{CE} = 400 \text{ V}, I_C = 60 \text{ A},$	-	187	280	nC	
Q <sub>ge</sub>	Gate to Emitter Charge	V <sub>GE</sub> = 15 V	-	20	29	nC	
Q <sub>gc</sub>	Gate to Collector Charge	-	-	92	138	nC	


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Symbol	Parameter	Test Co	Min	Тур	Max	Unit	
V <sub>FM</sub>	Diode Forward Voltage	I <sub>F</sub> = 30 A	$T_{C} = 25^{\circ}C$	-	2.1	2.7	V
			T <sub>C</sub> = 175°C	-	1.48	-	
T <sub>rr</sub>	$T_{rr}$ Diode Reverse Recovery Time $I_F = 30 \text{ A}, dI_F/dt = 200 \text{ A}/\mu \text{s}$	$T_{C} = 25^{\circ}C$	-	33	42	ns	
		αι <sub>F</sub> /αι – 200 Α/μο	T <sub>C</sub> = 175°C	-	115	-	
Q <sub>rr</sub>	Diode Reverse Recovery Charge		$T_C = 25^{\circ}C$	-	53	69	nC
			T <sub>C</sub> = 175°C	-	606	-	1

ELECTRICAL CHARACTERISTICS OF THE DIODE (T<sub>C</sub> = 25°C unless otherwise noted)

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

#### **TYPICAL PERFORMANCE CHARACTERISTICS**



**Figure 1. Typical Output Characteristics** 






Figure 3. Typical Saturation Voltage Characteristics





**Figure 2. Typical Output Characteristics** 




Figure 4. Transfer Characteristics




Figure 6. Saturation Voltage vs. V<sub>GE</sub>

## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)




Figure 7. Saturation Voltage vs. V<sub>GE</sub>




Figure 9. Capacitance Characteristics




Figure 11. SOA Characteristics




Figure 8. Saturation Voltage vs. V<sub>GE</sub>




Figure 10. Gate Charge Characteristics




Figure 12. Turn-on Characteristics vs. Gate Resistance

## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)




Figure 13. Turn-off Characteristics vs. Gate Resistance




Figure 15. Turn-off Characteristics vs. Collector Current





Figure 17. Switching Loss vs. Collector Current



vs. Conector Current




Figure 16. Switching Loss vs. Gate Resistance





Figure 18. Turn Off Switching SOA Characteristics

## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)






Figure 23. Transient Thermal Impedance of IGBT





ON Semiconductor and use trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent\_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

#### ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>