MBR1535CTG, MBR1545CTG

Switch-mode Power Rectifier

ON Semiconductor®

SCHOTTKY BARRIER RECTIFIERS
15 AMPERES
35 and 45 VOLTS

Features and Benefits

- Center−Tap Configuration
- Low Forward Voltage
- Low Power Loss / High Efficiency
- High Surge Capacity
- 175°C Operating Junction Temperature
- 15 A Total (7.5 A Per Diode Leg)
- These Devices are Pb−Free and are RoHS Compliant*

Applications

- Power Supply – Output Rectification
- Power Management
- Instrumentation

Mechanical Characteristics

- Case: Epoxy, Molded
- Epoxy Meets UL 94, V−0 @ 0.125 in
- Weight: 1.9 Grams (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- ESD Rating: Human Body Model = 3B
   Machine Model = C

TO−220
CASE 221A
STYLE 6

MARKING DIAGRAM

AYWW
MBR15x5CTG
AKA

A   = Assembly Location
Y   = Year
WW   = Work Week
x   = 3 or 4
G   = Pb−Free Package
AKA   = Diode Polarity

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage MBR1535CT MBR1545CT	V_{RRM} V_{RWM} V_R	 35 45	V
Average Rectified Forward Current (T_C = 163°C) Per Diode Per Device	$I_{F(AV)}$	 7.5 15	A
Peak Repetitive Forward Current (Square Wave, 20 kHz, T_C = 161°C) Per Diode	I_{FRM}	15	A
Non−Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz)	I_{FSM}	150	A
Peak Repetitive Reverse Surge Current (2.0 μs, 1.0 kHz)	I_{RRM}	1.0	A
Storage Temperature Range	T_{stg}	−65 to +175	°C
Operating Junction Temperature (Note 1)	T_J	−65 to +175	°C
Voltage Rate of Change (Rated V_R)	dv/dt	1000	V/μs

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.
1. The heat generated must be less than the thermal conductivity from Junction−to−Ambient: $dP_D/dT_J < 1/R_{\theta JA}$.

THERMAL CHARACTERISTICS PER DIODE

Characteristic	Symcbol	Value	Unit
Maximum Thermal Resistance, Junction−to−Case (Min. Pad)	$R_{\theta JC}$	3.0	°C/W
Maximum Thermal Resistance, Junction−to−Ambient (Min. Pad)	$R_{\theta JA}$	60	°C/W

ELECTRICAL CHARACTERISTICS PER DIODE

Characteristic	Symbol	Min	Typ	Max	Unit

Maximum Instantaneous Forward Voltage (Note 2)
    (i_F = 7.5 Amps, T_J = 125°C)
    (i_F = 15 Amps, T_J = 125°C)
    (i_F = 15 Amps, T_J = 25°C)
	v_F	
		−
		−
		−
			
			0.47
			0.63
			0.66
				
				0.57
				0.72
				0.84
					V

Maximum Instantaneous Reverse Current (Note 2)
    (Rated DC Voltage, T_J = 125°C)
    (Rated DC Voltage, T_J = 25°C)
	i_R	
		−
		−
			
			10
			0.025
				
				15
				0.1
					mA

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.
2. Pulse Test: Pulse Width = 300 μs, Duty Cycle ≤ 2.0%

ORDERING INFORMATION

| Device	Package	Shipping
MBR1535CTG	TO−220 (Pb−Free)	50 Units / Rail
MBR1545CTG	TO−220 (Pb−Free)	50 Units / Rail

Figure 1. Typical Forward Voltage

Figure 2. Maximum Forward Voltage

Figure 3. Typical Reverse Current

Figure 4. Maximum Reverse Current

Figure 5. Current Derating, Case Per Leg

Figure 6. Current Derating, Ambient Per Leg

MBR1535CTG, MBR1545CTG

Figure 7. Forward Power Dissipation

Figure 8. Typical Capacitance

ADDITIONAL INFORMATION

◊