

Low On-Resistance, Slew-Rate-Controlled Load Switch

FPF1038

Description

The FPF1038 advanced load-management switch target applications requiring a highly integrated solution for disconnecting loads powered from DC power rail (<6 V) with stringent shutdown current targets and high load capacitances (up to 200 μ F). The FPF1038 consists of slew-rate controlled low-impedance MOSFET switch (21 $m\Omega$ typical) and other integrated analog features. The slew-rate controlled turn-on characteristic prevents inrush current and the resulting excessive voltage droop on power rails.

These devices have exceptionally low shutdown current drain (<1 μ A maximum) that facilitates compliance in low standby power applications. The input voltage range operates from 1.2 V to 5.5 V DC to support a wide range of applications in consumer, optical, medical, storage, portable, and industrial device power management.


Switch control is managed by a logic input (active HIGH) capable of interfacing directly with low-voltage control signal / GPIO with no external pull-up required. The device is packaged in advanced fully “green” 1 mm x 1.5 mm Wafer-Level Chip-Scale Packaging (WLCSP); providing excellent thermal conductivity, small footprint, and low electrical resistance for wider application usage.

Features

- 1.2 V to 5.5 V Input Voltage Operating Range
- Typical R_{ON} :
 - ♦ 20 $m\Omega$ at $V_{IN} = 5.5$ V
 - ♦ 21 $m\Omega$ at $V_{IN} = 4.5$ V
 - ♦ 37 $m\Omega$ at $V_{IN} = 1.8$ V
 - ♦ 75 $m\Omega$ at $V_{IN} = 1.2$ V
- Slew Rate / Inrush Control with t_R : 2.7 ms (Typical)
- 3.5 A Maximum Continuous Current Capability
- Low <1 μ A Shutdown Current
- ESD Protected: Above 8 kV HBM, 1.5 kV CDM
- GPIO / CMOS-Compatible Enable Circuitry
- This Device is Pb-Free, Halide Free and is RoHS Compliant


Applications

- HDD, Storage, and Solid-State Memory Devices
- Portable Media Devices, UMPC, Tablets, MIDs
- Wireless LAN Cards and Modules
- SLR Digital Cameras
- Portable Medical Devices
- GPS and Navigation Equipment
- Industrial Handheld and Enterprise Equipment



WLCSP6 1.5x1.0x0.582
CASE 567RL

MARKING DIAGRAM



- QE = Specific Device Code
 &K = 2-Digits Lot Run Traceability Code
 &. = Pin One Dot
 &2 = 2-Digit Date Code
 &Z = Assembly Plant Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 11 of this data sheet.

FPF1038

APPLICATION DIAGRAM




Figure 1. Typical Application

FUNCTIONAL BLOCK DIAGRAM




Figure 2. Functional Block Diagram

FPF1038

PIN CONFIGURATION




Figure 3. Top View




Figure 4. Bottom View

PIN DEFINITIONS

Pin No.	Name	Description
A1, B1	V_{OUT}	Switch Output
A2, B2	V_{IN}	Supply Input: Input to the Power Switch
C1	GND	Ground
C2	ON	ON/OFF Control, Active High – GPIO Compatible

ABSOLUTE MAXIMUM RATINGS

Symbol	Parameters		Min	Max	Unit
V_{IN}	V_{IN} , V_{OUT} , V_{ON} to GND		-0.3	6.0	V
I_{SW}	Maximum Continuous Switch Current		-	3.5	A
P_D	Power Dissipation at $T_A = 25^{\circ}\text{C}$		-	1.2	W
T_{STG}	Storage Junction Temperature		-65	+150	$^{\circ}\text{C}$
T_A	Operating Temperature Range		-40	+85	$^{\circ}\text{C}$
Θ_{JA}	Thermal Resistance, Junction-to-Ambient		-	85 (Note 1)	$^{\circ}\text{C/W}$
			-	110 (Note 2)	
ESD	Electrostatic Discharge Capability	Human Body Model, JESD22-A114	8.0	-	kV
		Charged Device Model, JESD22-C101	1.5	-	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Measured using 2S2P JEDEC std. PCB.
2. Measured using 2S2P JEDEC PCB COLD PLATE method.

RECOMMENDED OPERATING CONDITIONS

Symbol	Parameters		Min	Max	Unit
V_{IN}	Input Voltage		1.2	5.5	V
T_A	Ambient Operating Temperature		-40	+85	$^{\circ}\text{C}$

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

FPF1038

ELECTRICAL CHARACTERISTICS (Unless otherwise noted, $V_{IN} = 1.2$ to 5.5 V and $T_A = -40$ to $+85^\circ\text{C}$; typical values are at $V_{IN} = 4.5$ V and $T_A = 25^\circ\text{C}$.)

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
--------	-----------	----------------	-----	-----	-----	------

BASIC OPERATION

V_{IN}	Input Voltage		1.2	–	5.5	V
$I_{Q(OFF)}$	Off Supply Current	$V_{ON} = \text{GND}, V_{OUT} = \text{Open}$	–	–	1.0	μA
I_{SD}	Shutdown Current	$V_{ON} = \text{GND}, V_{OUT} = \text{GND}$	–	0.2	1.0	μA
I_Q	Quiescent Current	$I_{OUT} = 0$ mA	–	5.5	8.0	μA
R_{ON}	On Resistance	$V_{IN} = 5.5$ V, $I_{OUT} = 1$ A (Note 3)	–	20	24	m Ω
		$V_{IN} = 4.5$ V, $I_{OUT} = 1$ A, $T_A = 25^\circ\text{C}$	–	21	25	
		$V_{IN} = 3.3$ V, $I_{OUT} = 500$ mA (Note 3)	–	24	29	
		$V_{IN} = 2.5$ V, $I_{OUT} = 500$ mA (Note 3)	–	28	35	
		$V_{IN} = 1.8$ V, $I_{OUT} = 250$ mA (Note 3)	–	37	45	
		$V_{IN} = 1.2$ V, $I_{OUT} = 250$ mA, $T_A = 25^\circ\text{C}$	–	75	100	
V_{IH}	On Input Logic HIGH Voltage		1.0	–	–	V
V_{IL}	On Input Logic LOW Voltage		–	–	0.4	V
I_{ON}	On Input Leakage		–	–	1.0	μA

DYNAMIC CHARACTERISTICS

t_{DON}	Turn-On Delay (Note 4)	$V_{IN} = 4.5$ V, $R_L = 5$ Ω , $C_L = 100$ μF , $T_A = 25^\circ\text{C}$		1.7	–	ms
t_R	V_{OUT} Rise Time (Note 4)		–	2.7	–	ms
t_{ON}	Turn-On Time (Note 6)		–	4.4	–	ms
t_{DOFF}	Turn-Off Delay (Note 4)	$V_{IN} = 4.5$ V, $R_L = 150$ Ω , $C_L = 100$ μF , $T_A = 25^\circ\text{C}$, No Load Discharge	–	2.0	–	ms
t_F	V_{OUT} Fall Time (Note 4)		–	30.0	–	ms
t_{OFF}	Turn-Off (Note 7)		–	32.0	–	ms

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. This parameter is guaranteed by design and characterization; not production tested.

4. $t_{DON}/t_{DOFF}/t_R/t_F$ are defined in Figure 27.

5. Output discharge enabled during off-state.

6. $t_{ON} = t_R + t_{DON}$

7. $t_{OFF} = t_F + t_{DOFF}$

TYPICAL CHARACTERISTICS




Figure 5. Shutdown Current vs. Temperature




Figure 6. Shutdown Current vs. Supply Voltage




Figure 7. Off Supply Current vs. Temperature
(V_{OUT} Floating)




Figure 8. Off Supply Current vs. Supply Voltage
(V_{OUT} Floating)




Figure 9. Quiescent Current vs. Temperature




Figure 10. Quiescent Current vs. Supply Voltage

TYPICAL CHARACTERISTICS (continued)




Figure 11. Quiescent Current vs. On Voltage ($V_{IN} = 4.5\text{ V}$)




Figure 12. Quiescent Current vs. On Voltage ($V_{IN} = 5.5\text{ V}$)




Figure 13. R_{ON} vs. Temperature




Figure 14. R_{ON} vs. Supply Voltage




Figure 15. On Pin Threshold Low vs. Temperature




Figure 16. On Pin Threshold Low vs. V_{IN}

TYPICAL CHARACTERISTICS (continued)




Figure 17. On Pin Threshold High vs. Temperature




Figure 18. On Pin Threshold High vs. V_{IN}




Figure 19. On Pin Threshold vs. Supply Voltage




Figure 20. I_{SW} vs. $(V_{IN}-V_{OUT})$ — SOA




Figure 21. t_R/t_{DON} vs. Temperature




Figure 22. t_R/t_F vs. Temperature

TYPICAL CHARACTERISTICS (continued)




Figure 23. t_R vs. Supply Voltage




Figure 24. t_R vs. Supply Voltage




Figure 25. Turn-On Response ($V_{IN} = 4.5\text{ V}$, $C_{IN} = 10\text{ }\mu\text{F}$, $C_L = 1\text{ }\mu\text{F}$, $R_L = 50\text{ }\Omega$)




Figure 26. Turn-On Response ($V_{IN} = 4.5\text{ V}$, $C_{IN} = 10\text{ }\mu\text{F}$, $C_L = 100\text{ }\mu\text{F}$, $R_L = 5\text{ }\Omega$)




Figure 27. Timing Diagram

APPLICATION INFORMATION

Input Capacitor

This IntelliMAX™ switch doesn't require an input capacitor. To reduce device inrush current, a 0.1 μF ceramic capacitor, C_{IN}, is recommended close to the V_{IN} pin. A higher value of C_{IN} can be used to reduce the voltage drop experienced as the switch is turned on into a large capacitive load.

Output Capacitor

While this switch works without an output capacitor: if parasitic board inductance forces V_{OUT} below GND when switching off; a 0.1 μF capacitor, C_{OUT}, should be placed between V_{OUT} and GND.

Fall Time

Device output fall time can be calculated based on RC constant of the external components as follows:

$$t_F = R_L \times C_L \times 2.2 \quad (\text{eq. 1})$$

where t_F is 90% to 10% fall time, R_L is output load, and C_L is output capacitor.

The same equation works for a device with a pull-down output resistor. R_L is replaced by a parallel connected pull-down and an external output resistor combination as:

$$t_F = \frac{R_L \times R_{PD}}{R_L + R_{PD}} \times C_L \times 2.2 \quad (\text{eq. 2})$$

where t_F is 90% to 10% fall time, R_L is output load, R_{PD} = 65 Ω is output pull-down resistor, and C_L is the output capacitor.

Resistive Output Load

If resistive output load is missing, the IntelliMAX switch without a pull-down output resistor does not discharge the output voltage. Output voltage drop depends, in that case, mainly on external device leaks.

Application Specifics




Figure 28. Device Setup

At maximum operational voltage (V_{IN} = 5.5 V), device inrush current might be higher than expected. Spike current should be taken into account if V_{IN} > 5 V and the output capacitor is much larger than the input capacitor. Input current can be calculated as:

$$I_{IN}(t) \approx \frac{V_{OUT}(t)}{R_{LOAD}} + (C_{LOAD} - C_{IN}) \frac{dV_{OUT}(t)}{dt} \quad (\text{eq. 3})$$

where switch and wire resistances are neglected and capacitors are assumed ideal.

Estimating V_{OUT}(t) = V_{IN} / 10 and using experimental formula for slew rate (dV_{OUT}(t) / dt), spike current can be written as:

$$\max(I_{IN}) = \frac{V_{IN}}{10R_{LOAD}} + (C_{LOAD} - C_{IN})(0.05V_{IN} - 0.255) \quad (\text{eq. 4})$$

where supply voltage V_{IN} is in volts, capacitances are in micro farads, and resistance is in ohms.

Example: If V_{IN} = 5.5 V, C_{LOAD} = 100 μF, C_{IN} = 10 μF, and R_{LOAD} = 50 Ω; calculate the spike current by:

$$\begin{aligned} \max(I_{IN}) &= \frac{5.5}{10 \times 50} + (100 - 10)(0.05 \times 5.5 - 0.255) \text{ A} = \\ &= 1.8 \text{ A} \end{aligned} \quad (\text{eq. 5})$$

Maximum spike current is 1.8 A, while average ramp-up current is:

$$\begin{aligned} I_{IN}(t) &\approx \frac{V_{OUT}(t)}{R_{LOAD}} + (C_{LOAD} - C_{IN}) \frac{dV_{IN}(t)}{dt} \\ &\approx 2.75 / 50 + 100 \times 0.0022 = 0.275 \text{ A} \end{aligned} \quad (\text{eq. 6})$$

Recommended Layout

For best thermal performance and minimal inductance and parasitic effects, it is recommended to keep input and output traces short and capacitors as close to the device as possible. Figure 29 is a recommended layout for this device to achieve optimum performance.




Figure 29. Recommended Land Pattern, Layout

FPF1038

ORDERING INFORMATION



Part Number	Top Mark	Switch R_{ON} (Typical) at $4.5 V_{IN}$	Input Buffer	Output Discharge	ON Pin Activity	t_R	Package	Shipping [†]
FPF1038UCX	QE	21 m Ω	CMOS	NA	Active HIGH	2.7 ms	6-Bump, WLCSP, 1.0 mm x 1.5 mm, 0.5 mm Pitch (Pb-Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


IntelliMAX is trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

WLCSP6 1.5x1.0x0.582
CASE 567RL
ISSUE O



DATE 30 NOV 2016



RECOMMENDED LAND PATTERN
(NSMD PAD TYPE)



SIDE VIEWS



BOTTOM VIEW

NOTES:

- A. NO JEDEC REGISTRATION APPLIES.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCE PER ASMEY14.5M, 1994.
- D. DATUM C IS DEFINED BY THE SPHERICAL CROWNS OF THE BALLS.
- E. PACKAGE NOMINAL HEIGHT IS 582 MICRONS ±43 MICRONS (539-625 MICRONS).
- F. FOR DIMENSIONS D, E, X, AND Y SEE PRODUCT DATASHEET.

DOCUMENT NUMBER:	98AON16578G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	WLCSP6 1.5x1.0x0.582	PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales