# **Complementary General Purpose Transistor**

The MBT3946DW1T1G device is a spin-off of our popular SOT-23/SOT-323 three-leaded device. It is designed for general purpose amplifier applications and is housed in the SOT-363-6 surface mount package. By putting two discrete devices in one package, this device is ideal for low-power surface mount applications where board space is at a premium.

#### Features

- h<sub>FE</sub>, 100–300
- Low  $V_{CE(sat)}$ ,  $\leq 0.4 V$
- Simplifies Circuit Design
- Reduces Board Space
- Reduces Component Count
- S Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Rating	Symbol	Value	Unit		
Collector – Emitter Voltage (NPN) (PNP)	V <sub>CEO</sub>	40 -40	Vdc		
Collector – Base Voltage (NPN) (PNP)	V <sub>CBO</sub>	60 -40	Vdc		
Emitter – Base Voltage (NPN) (PNP)	V <sub>EBO</sub>	6.0 -5.0	Vdc		
Collector Current – Continuous (NPN) (PNP)	Ι <sub>C</sub>	200 200	mAdc		
Electrostatic Discharge	ESD	HBM Class 2 MM Class B			

#### Table 1. MAXIMUM RATINGS

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

#### Table 2. THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Total Package Dissipation (Note 1) $T_A = 25^{\circ}C$	PD	150	mW
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	833	°C/W
Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C

1. Device mounted on FR4 glass epoxy printed circuit board using the minimum recommended footprint.




# **ON Semiconductor®**

http://onsemi.com



SOT-363/SC-88 CASE 419B STYLE 1



#### MARKING DIAGRAM



46 = Specific Device Code M = Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

#### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
MBT3946DW1T1G	SC-88 (Pb-Free)	3,000 / Tape & Reel
SMBT3946DW1T1G	SC-88 (Pb-Free)	3,000 / Tape & Reel
MBT3946DW1T2G	SC-88 (Pb-Free)	3,000 / Tape & Reel

+ For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


Characteristic		Symbol	Min	Max	Unit
OFF CHARACTERISTICS			1		
Collector – Emitter Breakdown Voltage (Note 2) ( $I_C = 1.0 \text{ mAdc}, I_B = 0$ ) ( $I_C = -1.0 \text{ mAdc}, I_B = 0$ )	(NPN) (PNP)	V <sub>(BR)CEO</sub>	40 -40		Vdc
Collector – Base Breakdown Voltage ( $I_C = 10 \ \mu Adc, I_E = 0$ ) ( $I_C = -10 \ \mu Adc, I_E = 0$ )	(NPN) (PNP)	V <sub>(BR)CBO</sub>	60 -40		Vdc
Emitter – Base Breakdown Voltage ( $I_E = 10 \ \mu Adc, I_C = 0$ ) ( $I_E = -10 \ \mu Adc, I_C = 0$ )	(NPN) (PNP)	V <sub>(BR)EBO</sub>	6.0 -5.0		Vdc
Base Cutoff Current (V <sub>CE</sub> = 30 Vdc, V <sub>EB</sub> = 3.0 Vdc) (V <sub>CE</sub> = -30 Vdc, V <sub>EB</sub> = -3.0 Vdc)	(NPN) (PNP)	I <sub>BL</sub>		50 50	nAdc
Collector Cutoff Current ( $V_{CE} = 30 \text{ Vdc}, V_{EB} = 3.0 \text{ Vdc}$ ) ( $V_{CE} = -30 \text{ Vdc}, V_{EB} = -3.0 \text{ Vdc}$ )	(NPN) (PNP)	I <sub>CEX</sub>		50 -50	nAdc
ON CHARACTERISTICS (Note 2)			ł.	ł	ł
$ \begin{array}{l} \text{DC Current Gain} \\ (I_{C} = 0.1 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}) \\ (I_{C} = 1.0 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}) \\ (I_{C} = 10 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}) \\ (I_{C} = 50 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}) \\ (I_{C} = 100 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}) \\ \end{array} $	(NPN)	h <sub>FE</sub>	40 70 100 60 30	- - 300 - -	_
	(PNP)		60 80 100 60 30	_  300 _ _	
Collector – Emitter Saturation Voltage ( $I_C = 10 \text{ mAdc}, I_B = 1.0 \text{ mAdc}$ ) ( $I_C = 50 \text{ mAdc}, I_B = 5.0 \text{ mAdc}$ )	(NPN)	V <sub>CE(sat)</sub>		0.2 0.3	Vdc
(I <sub>C</sub> = –10 mAdc, I <sub>B</sub> = –1.0 mAdc) (I <sub>C</sub> = –50 mAdc, I <sub>B</sub> = –5.0 mAdc)	(PNP)			-0.25 -0.4	
Base – Emitter Saturation Voltage (I <sub>C</sub> = 10 mAdc, I <sub>B</sub> = 1.0 mAdc) (I <sub>C</sub> = 50 mAdc, I <sub>B</sub> = 5.0 mAdc)	(NPN)	V <sub>BE(sat)</sub>	0.65 -	0.85 0.95	Vdc
(I <sub>C</sub> = –10 mAdc, I <sub>B</sub> = –1.0 mAdc) (I <sub>C</sub> = –50 mAdc, I <sub>B</sub> = –5.0 mAdc)	(PNP)		-0.65 -	-0.85 -0.95	
SMALL-SIGNAL CHARACTERISTICS	•			•	
$\label{eq:current-Gain-Bandwidth Product} \begin{aligned} &(I_C = 10 \text{ mAdc}, V_{CE} = 20 \text{ Vdc}, \text{f} = 100 \text{ MHz}) \\ &(I_C = -10 \text{ mAdc}, V_{CE} = -20 \text{ Vdc}, \text{f} = 100 \text{ MHz}) \end{aligned}$	(NPN) (PNP)	f <sub>T</sub>	300 250		MHz
Output Capacitance ( $V_{CB} = 5.0 \text{ Vdc}, I_E = 0, f = 1.0 \text{ MHz}$ ) ( $V_{CB} = -5.0 \text{ Vdc}, I_E = 0, f = 1.0 \text{ MHz}$ )	(NPN) (PNP)	C <sub>obo</sub>		4.0 4.5	pF
Input Capacitance (V <sub>EB</sub> = 0.5 Vdc, I <sub>C</sub> = 0, f = 1.0 MHz) (V <sub>EB</sub> = -0.5 Vdc, I <sub>C</sub> = 0, f = 1.0 MHz)	(NPN) (PNP)	C <sub>ibo</sub>		8.0 10.0	pF
Input Impedance ( $V_{CE} = 10 \text{ Vdc}, I_C = 1.0 \text{ mAdc}, f = 1.0 \text{ kHz}$ ) ( $V_{CE} = -10 \text{ Vdc}, I_C = -1.0 \text{ mAdc}, f = 1.0 \text{ kHz}$ )	(NPN) (PNP)	h <sub>ie</sub>	1.0 2.0	10 12	kΩ
Voltage Feedback Ratio (V <sub>CE</sub> = 10 Vdc, I <sub>C</sub> = 1.0 mAdc, f = 1.0 kHz) (V <sub>CE</sub> = -10 Vdc, I <sub>C</sub> = -1.0 mAdc, f = 1.0 kHz)	(NPN) (PNP)	h <sub>re</sub>	0.5 0.1	8.0 10	X 10 <sup>-4</sup>
Small – Signal Current Gain (V <sub>CE</sub> = 10 Vdc, I <sub>C</sub> = 1.0 mAdc, f = 1.0 kHz) (V <sub>CE</sub> = -10 Vdc, I <sub>C</sub> = -1.0 mAdc, f = 1.0 kHz)	(NPN) (PNP)	h <sub>fe</sub>	100 100	400 400	-

#### Table 4. ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise noted) (continued)

Characteristic		Symbol	Min	Max	Unit
Output Admittance ( $V_{CE} = 10$ Vdc, $I_C = 1.0$ mAdc, f = 1.0 kHz) ( $V_{CE} = -10$ Vdc, $I_C = -1.0$ mAdc, f = 1.0 kHz)	(NPN) (PNP)	h <sub>oe</sub>	1.0 3.0	40 60	μmhos
Noise Figure ( $V_{CE}$ = 5.0 Vdc, $I_{C}$ = 100 $\mu$ Adc, $R_{S}$ = 1.0 k $\Omega$ , f = 1.0 kHz) ( $V_{CE}$ = -5.0 Vdc, $I_{C}$ = -100 $\mu$ Adc, $R_{S}$ = 1.0 k $\Omega$ , f = 1.0 kHz)	(NPN) (PNP)	NF		5.0 4.0	dB
SWITCHING CHARACTERISTICS					
Delay Time $(V_{CC} = 3.0 \text{ Vdc}, V_{PE} = -0.5 \text{ Vdc})$	(NPN)	ta	_	35	

Delay Time	$(V_{CC} = 3.0 \text{ Vdc}, V_{BE} = -0.5 \text{ Vdc})$ $(V_{CC} = -3.0 \text{ Vdc}, V_{BE} = 0.5 \text{ Vdc})$	(NPN) (PNP)	t <sub>d</sub>	-	35 35	
Rise Time	$(I_{C} = 10 \text{ mAdc}, I_{B1} = 1.0 \text{ mAdc})$ $(I_{C} = -10 \text{ mAdc}, I_{B1} = -1.0 \text{ mAdc})$	(NPN) (PNP)	t <sub>r</sub>	-	35 35	ns
Storage Time	$(V_{CC} = 3.0 \text{ Vdc}, I_C = 10 \text{ mAdc})$ $(V_{CC} = -3.0 \text{ Vdc}, I_C = -10 \text{ mAdc})$	(NPN) (PNP)	t <sub>s</sub>		200 225	20
Fall Time	$(I_{B1} = I_{B2} = 1.0 \text{ mAdc})$ $(I_{B1} = I_{B2} = -1.0 \text{ mAdc})$	(NPN) (PNP)	t <sub>f</sub>	-	50 75	ns

2. Pulse Test: Pulse Width  $\leq$  300  $\mu$ s; Duty Cycle  $\leq$  2.0%.




(NPN)


\* Total shunt capacitance of test jig and connectors

Figure 1. Delay and Rise Time **Equivalent Test Circuit** 

Figure 2. Storage and Fall Time **Equivalent Test Circuit** 


### **TYPICAL TRANSIENT CHARACTERISTICS**





#### TYPICAL AUDIO SMALL-SIGNAL CHARACTERISTICS NOISE FIGURE VARIATIONS

(V<sub>CE</sub> = 5.0 Vdc,  $T_A$  = 25°C, Bandwidth = 1.0 Hz)



(NPN)







Figure 13. Input Impedance






(NPN) TYPICAL STATIC CHARACTERISTICS




(PNP)



\* Total shunt capacitance of test jig and connectors


Figure 20. Delay and Rise Time Equivalent Test Circuit

Figure 21. Storage and Fall Time Equivalent Test Circuit



#### **TYPICAL TRANSIENT CHARACTERISTICS**


#### (PNP)





http://onsemi.com 8


#### (PNP)















Figure 36. Safe Operating Area

#### SC-88 2.00x1.25x0.90, 0.65P CASE 419B-02 **ISSUE Z**


#### DATE 18 APR 2024


DUSEM




# NOTES:


- DIMENSIONING AND TOLERANCING CONFORM TO ASME 1. Y14.5-2018.
- 2.
- ALL DIMENSION ARE IN MILLIMETERS. DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.20 3. PER END.
- 4. DIMENSIONS D AND E1 AT THE OUTERMOST EXTREMES OF
- DATUMS A AND B ARE DETERMINED AT DATUM H. 5.
- DIMENSIONS & AND C APPLY TO THE FLAT SECTION OF THE LEAD BETWEEN 0.08 AND 0.15 FROM THE TIP. 6.
- DIMENSION b DOES NOT INCLUDE DAMBAR PROTRUSION. 7 ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 TOTAL IN EXCESS OF DIMENSION & AT MAXIMUM MATERIAL CONDITION. THE DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OF THE FOOT.







	MILLIMETERS				
DIM	MIN.	NOM.	MAX.		
A			1.10		
A1	0.00		0.10		
A2	0.70	0.90	1.00		
b	0.15	0.20	0.25		
с	0.08	0.15	0.22		
D	2.00 BSC				
E	2.10 BSC				
E1	1.25 BSC				
е		0.65 BSC	)		
L	0.26	0.36	0.46		
L2	0.15 BSC				
aaa	0.15				
bbb	0.30				
ccc	0.10				
ddd		0.10			



RECOMMENDED MOUNTING FOOTPRINT\*

FOR ADDITIONAL INFORMATION ON OUR Pb-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

XXX = Specific Device Code

XXXM-

0

GENERIC **MARKING DIAGRAM\*** 

6

Μ

- = Date Code\*
- = Pb-Free Package

(Note: Microdot may be in either location)

\*Date Code orientation and/or position may vary depending upon manufacturing location.

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

### **STYLES ON PAGE 2**

DOCUMENT NUMBER:	98ASB42985B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION:	N: SC-88 2.00x1.25x0.90, 0.65P		SC-88 2.00x1.25x0.90, 0.65P		PAGE 1 OF 2
onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its pattent rights nor the rights of others.					

#### SC-88 2.00x1.25x0.90, 0.65P CASE 419B-02 ISSUE Z

#### DATE 18 APR 2024

STYLE 1: PIN 1. EMITTER 2 2. BASE 2 3. COLLECTOR 1 4. EMITTER 1 5. BASE 1 6. COLLECTOR 2	STYLE 2: CANCELLED	STYLE 3: CANCELLED	STYLE 4: PIN 1. CATHODE 2. CATHODE 3. COLLECTOR 4. EMITTER 5. BASE 6. ANODE	STYLE 5: PIN 1. ANODE 2. ANODE 3. COLLECTOR 4. EMITTER 5. BASE 6. CATHODE	STYLE 6: PIN 1. ANODE 2 2. N/C 3. CATHODE 1 4. ANODE 1 5. N/C 6. CATHODE 2
STYLE 7: PIN 1. SOURCE 2 2. DRAIN 2 3. GATE 1 4. SOURCE 1 5. DRAIN 1 6. GATE 2	STYLE 8: CANCELLED	STYLE 9: PIN 1. EMITTER 2 2. EMITTER 1 3. COLLECTOR 1 4. BASE 1 5. BASE 2 6. COLLECTOR 2	STYLE 10: PIN 1. SOURCE 2 2. SOURCE 1 3. GATE 1 4. DRAIN 1 5. DRAIN 2 6. GATE 2	STYLE 11: PIN 1. CATHODE 2 2. CATHODE 2 3. ANODE 1 4. CATHODE 1 5. CATHODE 1 6. ANODE 2	STYLE 12: PIN 1. ANODE 2 2. ANODE 2 3. CATHODE 1 4. ANODE 1 5. ANODE 1 6. CATHODE 2
STYLE 13:	STYLE 14:	STYLE 15:	STYLE 16:	STYLE 17:	STYLE 18:
PIN 1. ANODE	PIN 1. VREF	PIN 1. ANODE 1	PIN 1. BASE 1	PIN 1. BASE 1	PIN 1. VIN1
2. N/C	2. GND	2. ANODE 2	2. EMITTER 2	2. EMITTER 1	2. VCC
3. COLLECTOR	3. GND	3. ANODE 3	3. COLLECTOR 2	3. COLLECTOR 2	3. VOUT2
4. EMITTER	4. IOUT	4. CATHODE 3	4. BASE 2	4. BASE 2	4. VIN2
5. BASE	5. VEN	5. CATHODE 2	5. EMITTER 1	5. EMITTER 2	5. GND
6. CATHODE	6. VCC	6. CATHODE 1	6. COLLECTOR 1	6. COLLECTOR 1	6. VOUT1
STYLE 19:	STYLE 20:	STYLE 21:	STYLE 22:	STYLE 23:	STYLE 24:
PIN 1. I OUT	PIN 1. COLLECTOR	PIN 1. ANODE 1	PIN 1. D1 (i)	PIN 1. Vn	PIN 1. CATHODE
2. GND	2. COLLECTOR	2. N/C	2. GND	2. CH1	2. ANODE
3. GND	3. BASE	3. ANODE 2	3. D2 (i)	3. Vp	3. CATHODE
4. V CC	4. EMITTER	4. CATHODE 2	4. D2 (c)	4. N/C	4. CATHODE
5. V EN	5. COLLECTOR	5. N/C	5. VBUS	5. CH2	5. CATHODE
6. V REF	6. COLLECTOR	6. CATHODE 1	6. D1 (c)	6. N/C	6. CATHODE
STYLE 25:	STYLE 26:	STYLE 27:	STYLE 28:	STYLE 29:	STYLE 30:
PIN 1. BASE 1	PIN 1. SOURCE 1	PIN 1. BASE 2	PIN 1. DRAIN	PIN 1. ANODE	PIN 1. SOURCE 1
2. CATHODE	2. GATE 1	2. BASE 1	2. DRAIN	2. ANODE	2. DRAIN 2
3. COLLECTOR 2	3. DRAIN 2	3. COLLECTOR 1	3. GATE	3. COLLECTOR	3. DRAIN 2
4. BASE 2	4. SOURCE 2	4. EMITTER 1	4. SOURCE	4. EMITTER	4. SOURCE 2
5. EMITTER	5. GATE 2	5. EMITTER 2	5. DRAIN	5. BASE/ANODE	5. GATE 1
6. COLLECTOR 1	6. DRAIN 1	6. COLLECTOR 2	6. DRAIN	6. CATHODE	6. DRAIN 1

Note: Please refer to datasheet for style callout. If style type is not called out in the datasheet refer to the device datasheet pinout or pin assignment.

DOCUMENT NUMBER:	98ASB42985B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION:	PAGE 2 OF 2				
onsemi and ONSEMi. are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.					

© Semiconductor Components Industries, LLC, 2019

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent\_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

#### ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>