# **ON Semiconductor**

# Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# MOSFET – Power, Single P-Channel -30 V, 215 mΩ, -2.0 A

This Power MOSFET is produced using ON Semiconductor's trench technology, which is specifically designed to minimize gate charge and low on resistance. This device is suitable for applications with low gate charge driving or low on resistance requirements.

### **Features**

- Low On-Resistance
- 1.8V drive
- ESD Diode-Protected Gate
- Pb-Free, Halogen Free and RoHS compliance

# **Typical Applications**

• Load Switch

### **SPECIFICATIONS**

# **ABSOLUTE MAXIMUM RATING** at Ta = 25°C (Note 1)

Parameter	Symbol	Value	Unit
Drain to Source Voltage	VDSS	-30	V
Gate to Source Voltage	VGSS	±10	V
Drain Current (DC)	ID	-2.0	Α
Drain Current (Pulse) PW ≤ 10μs, duty cycle ≤ 1%	IDP	-8.0	Α
Power Dissipation When mounted on ceramic substrate (1000mm² × 0.8mm)	PD	0.9	W
Junction Temperature	Tj	150	°C
Storage Temperature	Tstg	-55 to +150	°C
$PW \leq 10 \mu s, \ duty \ cycle \leq 1 \%$ $Power \ Dissipation$ $When \ mounted \ on \ ceramic \ substrate$ $(1000 mm^2 \times 0.8 mm)$ $Junction \ Temperature$	PD Tj Tstg	0.9	W °C

Note 1: Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

# THERMAL RESISTANCE RATINGS

Parameter	Symbol	Value	Unit
Junction to Ambient When mounted on ceramic substrate (1000mm² × 0.8mm)	$R_{ heta}$ JA	138.8	°C/W




# ON Semiconductor®

www.onsemi.com

V <sub>DSS</sub>	RDS(on) Max	I <sub>D Max</sub>
	215mΩ@ –4V	
-30V	280mΩ@ –2.5V	-2A
	430mΩ@ –1.8V	

# ELECTRICAL CONNECTION P-Channel



#### **PACKING TYPE: TL**

# TL

# MARKING



### ORDERING INFORMATION


See detailed ordering and shipping information on page 5 of this data sheet.


**ELECTRICAL CHARACTERISTICS** at  $Ta = 25^{\circ}C$  (Note 2)


			Value			
Parameter	Symbol	Conditions	min	typ	max	Unit
Drain to Source Breakdown Voltage	V(BR)DSS	I <sub>D</sub> =-1mA, V <sub>G</sub> S=0V -30				V
Zero-Gate Voltage Drain Current	IDSS	VDS=-30V, VGS=0V			-1	μА
Gate to Source Leakage Current	IGSS	V <sub>GS</sub> =±8V, V <sub>DS</sub> =0V			±10	μА
Gate Threshold Voltage	VGS(th)	V <sub>DS</sub> =-10V, I <sub>D</sub> =-1mA	-0.4		-1.3	V
Forward Transconductance	gFS	V <sub>DS</sub> =-10V, I <sub>D</sub> =-1.0A		2.5		S
	RDS(on)1	I <sub>D</sub> =-1.0A, V <sub>G</sub> S=-4V		165	215	mΩ
Static Drain to Source On-State Resistance	RDS(on)2	I <sub>D</sub> =-0.5A, V <sub>G</sub> S=-2.5V		200	280	mΩ
	RDS(on)3	ID=-0.2A, VGS=-1.8V		270	430	mΩ
Input Capacitance	Ciss			240		pF
Output Capacitance	Coss	V <sub>DS</sub> =-10V, f=1MHz		39		pF
Reverse Transfer Capacitance	Crss			31		pF
Turn-ON Delay Time	t <sub>d</sub> (on)			5.7		ns
Rise Time	t <sub>r</sub>			9.7		ns
Turn-OFF Delay Time	t <sub>d</sub> (off)	See specified Test Circuit		27		ns
Fall Time	tf			16		ns
Total Gate Charge	Qg	Vps=-15V, Vgs=-4V, Ip=-2.0A		2.8		nC
Gate to Source Charge	Qgs			0.3		nC
Gate to Drain "Miller" Charge	Qgd			0.95		nC
Forward Diode Voltage	VSD	I <sub>S</sub> =-2.0A, V <sub>G</sub> S=0V		-0.87	-1.5	V

Note 2 : Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# **Switching Time Test Circuit**








### **PACKAGE DIMENSIONS**

unit : mm SC-70FL / MCPH3 CASE 419AQ ISSUE O



# ORDERING INFORMATION

Device	Marking	Package	Shipping (Qty / Packing)	
MCH3333A-TL-H	QI.	SC-70FL / MCPH3	3,000 / Tape & Reel	
MCH3333A-TL-W	QU	(Pb-Free / Halogen Free)		

<sup>†</sup> For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D. http://www.onsemi.com/pub\_link/Collateral/BRD8011-D.PDF

Note on usage: Since the MCH3333A is a MOSFET product, please avoid using this device in the vicinity of highly charged objects.

ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors hamless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent reg