# Switch-mode Power Rectifier 150 V, 30 A

#### **Features and Benefits**

- Low Forward Voltage
- Low Power Loss/High Efficiency
- High Surge Capability
- 30 A Total (15 A Per Diode Leg)
- Guard-Ring for Stress Protection
- These Devices are Pb-Free and are RoHS Compliant

#### **Applications**

- Power Supply Output Rectification
- Power Management
- Instrumentation

#### **Mechanical Characteristics:**


- Case: Epoxy, Molded
- Epoxy Meets UL 94 V-0 @ 0.125 in
- Weight (Approximately): 1.9 Grams (TO-220 & TO-220FP)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 Seconds




#### ON Semiconductor®

www.onsemi.com


# SCHOTTKY BARRIER RECTIFIER 30 AMPERES, 150 VOLTS



#### MARKING DIAGRAMS







TO-220 CASE 221A STYLE 6



A = Assembly Location

Y = Year
WW = Work Week
B30H150 = Device Code
G = Pb-Free Device
AKA = Polarity Designator

#### ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

#### MAXIMUM RATINGS (Per Diode Leg)

Rating		Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	150	V
Average Rectified Forward Current (Rated $V_R$ ) $T_C = 124$ °C	(Per Leg) (Per Device)	I <sub>F(AV)</sub>	15 30	А
Nonrepetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase,	60 Hz)	I <sub>FSM</sub>	200	А
Operating Junction Temperature (Note 1)		TJ	-20 to +150	°C
Storage Temperature		T <sub>stg</sub>	-65 to +150	°C
Voltage Rate of Change (Rated V <sub>R</sub> )		dv/dt	10,000	V/μs
ESD Ratings:	Machine Model = C Human Body Model = 3B		> 400 > 8000	V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL CHARACTERISTICS

Rating		Symbol	Value	Unit
Maximum Thermal Resistance (MBR30H150CTG)	<ul><li>Junction-to-Case</li><li>Junction-to-Ambient</li></ul>	R <sub>0</sub> JC	2.0 45	°C/W
(MBRF30H150CTG)	- Junction-to-Case	$R_{ hetaJA} \ R_{ hetaJC}$	2.5	

#### **ELECTRICAL CHARACTERISTICS** (Per Diode Leg)

Rating	Symbol	Тур	Max	Unit
Maximum Instantaneous Forward Voltage (Note 2) $ \begin{array}{l} (I_F=5~A,~T_C=25^\circ C)\\ (I_F=5~A,~T_C=125^\circ C)\\ (I_F=15~A,~T_C=25^\circ C)\\ (I_F=15~A,~T_C=125^\circ C) \end{array} $	VF	0.69 0.55 0.98 0.68	0.75 0.60 1.11 0.73	V
Maximum Instantaneous Reverse Current (Note 2) (Rated DC Voltage, T <sub>C</sub> = 25°C) (Rated DC Voltage, T <sub>C</sub> = 125°C)	i <sub>R</sub>		60 50	μA mA


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 2. Pulse Test: Pulse Width =  $300 \mu s$ , Duty Cycle  $\leq 2.0\%$ .

#### **DEVICE ORDERING INFORMATION**

Device Order Number	Package Type	Shipping <sup>†</sup>
MBRF30H150CTG	TO-220FP (Pb-Free)	50 Units / Rail
MBR30H150CTG	TO-220 (Pb-Free)	50 Units / Rail

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

<sup>1.</sup> The heat generated must be less than the thermal conductivity from Junction-to-Ambient:  $dP_D/dT_J < 1/R_{\theta JA}$ .








Figure 2. Maximum Forward Voltage




Figure 3. Typical Reverse Current

Figure 4. Maximum Reverse Current




Figure 5. Current Derating




Figure 6. Forward Power Dissipation




Figure 7. Capacitance




Figure 8. Thermal Response Junction-to-Ambient for MBR30H150CTG




Figure 9. Thermal Response Junction-to-Case for MBR30H150CTG







Figure 10. Thermal Response Junction-to-Case for MBRF30H150CTG



**DATE 30 SEP 2014** 







NOTES:

## SECTION D-D

**FRONT VIEW** 






**ALTERNATE CONSTRUCTION** 

#### **GENERIC MARKING DIAGRAM\***

 DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: MILLIMETERS.
3. CONTOUR UNCONTROLLED IN THIS AREA.

3. CONTOUR UNCONTROLLED IN THIS AREA.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH AND GATE PROTRUSIONS. MOLD FLASH AND GATE PROTRUSIONS NOT TO EXCEED 0.13 PER SIDE. THESE DIMENSIONS ARE TO BE MEASURED AT OUTERMOST EXTREME OF THE PLASTIC BODY.
5. DIMENSION b2 DOES NOT INCLUDE DAMBAR PROTRUSION. LEAD WIDTH INCLUDING PROTRUSION SHALL NOT EXCEED 2.00.
6. CONTOURS AND FEATURES OF THE MOLDED PACKAGE BODY.

MAY VARY WITHIN THE ENVEL OR DEFINED BY UNIENSIONS A1



= Assembly Location

WL = Wafer Lot

= Year

WW = Work Week

G = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

STYLE 1:		STYLE 2:	
PIN 1.	MAIN TERMINAL 1	PIN 1.	CATHODE
2.	MAIN TERMINAL 2	2.	ANODE
3.	GATE	3.	GATE

DOCUMENT NUMBER:	98AON52577E	Electronic versions are uncontrolled except when accessed directly from the Document Repos Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION	TO-220 FULL PACK 3-1 FA	ΔD	PAGE 1 OF 1

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

#### ADDITIONAL INFORMATION

**TECHNICAL PUBLICATIONS:** 

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales