**ON Semiconductor** 

Is Now

# Onsemi

To learn more about onsemi<sup>™</sup>, please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

# **Voltage Reference Family**

The MC1404 of ICs is a family of temperature–compensated voltage references for precision data conversion applications, such as A/D, D/A, V/F, and F/V. Advances in laser–trimming and ion–implanted devices, as well as monolithic fabrication techniques, make these devices stable and accurate to 12 bits over both military and commercial temperature ranges. In addition to excellent temperature stability, these parts offer excellent long–term stability and low noise.

- Output Voltages: Standard, 5.0 V, 6.25 V, 10 V
- Trimmable Output: >  $\pm 6\%$
- Wide Input Voltage Range: V<sub>ref</sub> + 2.5 V to 40 V
- Low Quiescent Current: 1.25 mA Typical
- Temperature Coefficient: 10 ppm/°C Typical
- Low Output Noise: 12 µV p–p Typical
- Excellent Ripple Rejection: > 80 dB Typical

#### **Typical Applications**

- Voltage Reference for 8 to 12 Bit D/A Converters
- Low T<sub>C</sub> Zener Replacement
- High Stability Current Reference
- MPU D/A and A/D Applications

#### Figure 1. Voltage Output 8-Bit DAC Using MC1404P10




## **ON Semiconductor®**

http://onsemi.com


PRECISION LOW DRIFT VOLTAGE REFERENCES 5.0, 6.25, and 10-VOLT OUTPUT VOLTAGES SEMICONDUCTOR TECHNICAL DATA



P SUFFIX PLASTIC PACKAGE CASE 626



## **PIN CONNECTIONS**



#### **ORDERING INFORMATION**

Device	Operating Temperature Range	Package
MC1404P5		Plastic DIP
MC1404P6	$T_A = 0^\circ$ to +70°C	Plastic DIP
MC1404P10		Plastic DIP

#### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Input Voltage	V <sub>in</sub>	40	V
Storage Temperature	T <sub>stg</sub>	– 65 to + 150	°C
Junction Temperature	Т <sub>Ј</sub>	+ 175	°C
Operating Ambient Temperature Range	T <sub>A</sub>	0 to + 70	°C

# **ELECTRICAL CHARACTERISTICS** ( $V_{in}$ = 15 V, $T_A$ = 25°C, and Trim Terminal not connected, unless otherwise noted.)


Characteristic		Symbol	Min	Тур	Max	Unit
Output Voltage (I <sub>O</sub> = 0 mA)	MC1404P5 MC1404P6 MC1404P10	Vo	4.95 6.19 9.9	5.0 6.25 10	5.05 6.31 10.1	V
Output Voltage Tolerance			- )	±[0.1	±[1.0	%
Output Trim Range (Figure 10) $(R_P = 100 \text{ k}\Omega)$		ΔV <sub>TRIM</sub>	± <b>6</b> .0	-	-	%
Output Voltage Temperature Coefficient, Over Full Temperature Range (Note 1)		$\Delta V_O / \Delta T$	-	10	40	ppm/°C
Maximum Output Voltage Change Over Temperature Range (Note 1)	MC1404P5 MC1404P6 MC1404P10	ΔVo		MON I	14 17.5 28	mV
Line Regulation (Note 2) ( $V_{in} = V_{out} + 2.5 V \text{ to } 40 V$ , $I_{out} = 0 \text{ mA}$ )		Reg <sub>line</sub>	NI	2.0	6.0	mV
Load Regulation (Note 2) $(0 \le I_0 \le 10 \text{ mA})$		Reg <sub>load</sub>	V-O	_	10	mV
Quiescent Current (I <sub>O</sub> = 0 mA)		Q	<u> </u>	1.2	1.5	mA
Short Circuit Current	10-1	I <sub>sc</sub>	-	20	45	mA
Long Term Stability	0, 12	_	-	25	-	ppm/1000 hrs


**NOTE:** 1. Guaranteed but not tested. **NOTE:** 2. Includes thermal effects.

# DYNAMIC CHARACTERISTICS ( $V_{in}$ = 15 V, $T_A$ = 25°C, all voltage ranges, unless otherwise noted.)

Characteristic	Symbol	Min	Тур	Max	Unit
Turn–On Settling Time (to ±[0.01%)	t <sub>S</sub>	-	50	-	μs
Output Noise Voltage – P to P (Bandwidth 0.1 to 10 Hz)	Vn	-	12	-	μV
Small–Signal Output Impedance 120 Hz 500 Hz	r <sub>o</sub>		0.15 0.2		Ω
Power Supply Rejection Ratio	PSRR	70	80	-	dB

#### **TYPICAL CHARACTERISTICS**






0.001 μF

 $I_{\text{omax}} \approx \frac{0.6 \text{ V}}{\text{R}_{co}}$ 


Ro

 $\leq$  4.7 k



#### Figure 13. 5.0 V, 6.0 Amp, 25 kHz Switching Regulator with Separate Ultra-Stable Reference

#### **OUTLINE DIMENSIONS**



ON Semiconductor and use registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death agsociated with such unintended or unauthorized use payers that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunit//Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5773–3850 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative