Zener Voltage Regulators

500 mW SOD-523, Tight Tolerance Series

MM5ZxxxST1G Series, SZMM5ZxxxST1G Series

This series of Zener diodes is packaged in a SOD-523 surface mount package. They are designed to provide voltage regulation protection and are especially attractive in situations where space is at a premium. They are well suited for applications such as cellular phones, hand held portables, and high density PC boards.

Specification Features

- Standard Zener Breakdown Voltage Range -2.4 V to 18 V
- Tight Tolerance Series
- Steady State Power Rating of 500 mW
- Small Body Outline Dimensions: 0.047" x 0.032" (1.20 mm x 0.80 mm) Low Body Height: 0.028" (0.7 mm)
- ESD Rating of Class 3 (> 16 kV) per Human Body Model
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant*

Mechanical Characteristics

CASE: Void-free, transfer-molded, thermosetting plastic Epoxy Meets UL 94, V-0 LEAD FINISH: 100% Matte Sn (Tin) MOUNTING POSITION: Any QUALIFIED MAX REFLOW TEMPERATURE: 260°C Device Meets MSL 1 Requirements

MAXIMUM RATINGS

Rating	Symbol	Max	Unit	
Total Device Dissipation FR-4 Board, (Note 1) @ T _A = 25°C Derate above 25°C	P _D	500 4.0	mW mW/°C	
Thermal Resistance from Junction-to-Ambient (Note 1)	$R_{\theta JA}$	250	°C/W	
Operating Junction and Storage Temperature Range	T _J , T _{stg}	−65 to +150	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. FR-4 printed circuit board, single-sided copper, mounting pad 1 cm².



ON Semiconductor®

www.onsemi.com



CASE 502 STYLE 1



MARKING DIAGRAM



XX = Specific Device Code M Date Code*

= Pb-Free Package

(Note: Microdot may be in either location)

*Date Code orientation may vary depending upon manufacturing location.

ORDERING INFORMATION

Device	Package	Shipping [†]
MM5ZxxxST1G	SOD–523 (Pb–Free)	3,000 / Tape & Reel
SZMM5ZxxxST1G	SOD–523 (Pb–Free)	3,000 / Tape & Reel
MM5ZxxxST5G	SOD–523 (Pb–Free)	8,000 / Tape & Reel
SZMM5ZxxxST5G	SOD–523 (Pb–Free)	8,000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

DEVICE MARKING INFORMATION See specific marking information in the device marking

column of the Electrical Characteristics table on page 2 of

this data sheet


*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

© Semiconductor Components Industries, LLC, 2014

ELECTRICAL CHARACTERISTICS

 $(T_A = 25^{\circ}C \text{ unless otherwise noted}, V_F = 0.9 V Max. @ I_F = 10 mA for all types)$

Symbol	Parameter			
VZ	Reverse Zener Voltage @ IZT			
I _{ZT}	Reverse Current			
Z _{ZT}	Maximum Zener Impedance @ I _{ZT}			
I _{ZK}	Reverse Current			
Z _{ZK}	Maximum Zener Impedance @ I _{ZK}			
I _R	Reverse Leakage Current @ V _R			
V _R	Reverse Voltage			
١ _F	Forward Current			
V _F	Forward Voltage @ I _F			
ΘV_Z	Maximum Temperature Coefficient of V_Z			
С	Max. Capacitance $@V_R = 0$ and f = 1 MHz			





ELECTRICAL CHARACTERISTICS – Tight Tolerance Series

Device*		Test	Zener Voltage VZ			Z _{ZT} I _Z = IZT @ 10%	Max IR @ VR		d _{VZ} /dt (mV/k) @ I _{ZT1} = 5 mA		C pF Max @
		Current Izt mA	Min	Max	mA Ω Max	Mod Ω Max	μΑ	v	Min	Max	V _R = 0 f = 1 MHz
MM5Z2V4ST1G/T5G	T2	5.0	2.43	2.63	1000	100	120	1.0	-3.5	0	450
MM5Z2V7ST1G	Т3	5.0	2.67	2.91	1000	100	100	1.0	-3.5	0	450
MM5Z3V3ST1G	T5	5.0	3.32	3.53	1000	95	5.0	1.0	-3.5	0	450
MM5Z3V6ST1G	T6	5.0	3.60	3.85	1000	90	5.0	1.0	-3.5	0	450
MM5Z3V9ST1G	T7	5.0	3.89	4.16	1000	90	3.0	1.0	-3.5	-2.5	450
MM5Z4V3ST1G	Т8	5.0	4.17	4.43	1000	90	3.0	1.0	-3.5	0	450
MM5Z4V7ST1G/T5G	Т9	5.0	4.55	4.75	800	80	3.0	2.0	-3.5	0.2	260
MM5Z5V1ST1G/T5G	TA	5.0	4.98	5.2	500	60	2.0	2.0	-2.7	1.2	225
MM5Z5V6ST1G/T5G	TC	5.0	5.49	5.73	200	40	1.0	2.0	-2.0	2.5	200
MM5Z6V2ST1G/T5G	TE	5.0	6.06	6.33	100	10	3.0	4.0	0.4	3.7	185
MM5Z6V8ST1G/T5G	TF	5.0	6.65	6.93	160	15	2.0	4.0	1.2	4.5	155
MM5Z7V5ST1G	TG	5.0	7.28	7.6	160	15	1.0	5.0	2.5	5.3	140
MM5Z8V2ST1G/T5G	TH	5.0	8.02	8.36	160	15	0.7	5.0	3.2	6.2	135
MM5Z9V1ST1G/T5G	ТК	5.0	8.85	9.23	160	15	0.5	6.0	3.8	7.0	130
MM5Z12VST1G	TN	5.0	11.74	12.24	80	25	0.1	8.0	6.0	10	130
MM5Z16VST1G	TU	5.0	15.85	16.51	80	40	0.05	11.2	10.4	14	105
MM5Z18VST1G	TW	5.0	17.56	18.35	80	45	0.05	12.6	12.4	16	100

 $(V_F = 0.9 \text{ Max} @ I_F = 10 \text{ mA for all types})$

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. *Includes SZ-prefix devices where applicable.

MM5ZxxxST1G Series, SZMM5ZxxxST1G Series

TYPICAL CHARACTERISTICS






Figure 2. Steady State Power Derating


MECHANICAL CASE OUTLINE

PACKAGE DIMENSIONS










GENERIC **MARKING DIAGRAM***



Μ Date Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

STYLE 1:	STYLE 2:	
PIN 1. CATHODE (POLARITY BAND)		NO POLARITY
2. ANODE		

DATE 08 FEB 2024


DURSEM

NDTES:

CASE 502 ISSUE F

- 1.
- 2.
- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018. CONTROLLING DIMENSION: MILLIMETERS. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH, MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS З. OF BASE MATERIAL.
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. 4.

	MILLIMETERS			
DIM	MIN.	NDM.	MAX.	
A	0.50	0.60	0.70	
b	0.25	0.30	0.35	
С	0.07	0.14	0.20	
D	1.10	1.20	1.30	
E	0.70	0.80	0.90	
Н	1.50	1.60	1.70	
L	0.30 REF			
L2	0.15	0.20	0.25	





RECOMMENDED MOUNTING FOOTPRINT

*For additional information on our Pb-Free strategy and soldering details, please download the DN Semiconductor Soldering and Mounting Techniques Reference manual, SOLDERRM/D.

DOCUMENT NUMBER:	98AON11524D	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SOD-523 1.20x0.80x0.60		PAGE 1 OF 1	

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>