ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

MMBT2131T1G

General Purpose Transistors

PNP Bipolar Junction Transistor

NOTE: Voltage and Current are negative for the PNP Transistor.

Features

• These Devices are Pb-Free and are RoHS Compliant

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V _{CEO}	30	V
Collector-Base Voltage	V _{CBO}	40	V
Emitter-Base Voltage	V _{EBO}	5.0	V
Collector Current	۱ _C	700	mA
Base Current	Ι _Β	350	mA
Total Power Dissipation @ $T_C = 25^{\circ}C$ Total Power Dissipation @ $T_C = 85^{\circ}C$ Thermal Resistance, Junction-to-Ambient (Note 1)	P _D P _D R _{θJA}	342 178 366	mW mW °C/W
Total Power Dissipation @ $T_C = 25^{\circ}C$ Total Power Dissipation @ $T_C = 85^{\circ}C$ Thermal Resistance, Junction-to-Ambient (Note 2)	P _D P _D R _{θJA}	665 346 188	mW mW °C/W
Operating and Storage Temperature Range	T _J , T _{stg}	-55 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


1. Minimum FR-4 or G-10 PCB, Operating to Steady State.


 Mounted onto a 2" square FR-4 Board (1" sq. 2 oz Cu 0.06" thick single sided), Operating to Steady State.



ON Semiconductor®

http://onsemi.com





*Date Code orientation may vary depending upon manufacturing location.

ORDERING INFORMATION

Device	Package	Shipping [†]
MMBT2131T1G	SC–74 (Pb–Free)	3000/Tape & Reel


†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.


MMBT2131T1G


ELECTRICAL CHARACTERISTICS ($T_C = 25^{\circ}C$ unless otherwise noted)

Character	Symbol	Min	Тур	Max	Unit	
OFF CHARACTERISTICS						
Collector – Base Breakdown Voltage	(I _C = 100 μA)	V _{(BR)CBO}	40	-	-	V
Collector – Emitter Breakdown Voltage (I _C = 10 mA)		V _{(BR)CEO}	30	-	-	V
Emitter-Base Breakdown Voltage	(I _E = 100 μA)	V _{(BR)EBO}	5.0	-	-	V
$\begin{tabular}{lllllllllllllllllllllllllllllllllll$		I _{CBO}	-	-	1.0 10	μΑ
Emitter Cutoff Current	$(V_{EB} = 5.0 \text{ V}, \text{ I}_{C} = 0 \text{ A})$	I _{EBO}	-	-	10	μA
ON CHARACTERISTICS						
DC Current Gain	$(V_{CE} = 3.0 \text{ V}, I_{C} = 100 \text{ mA})$	h _{FE}	150	-	-	V
Collector - Emitter Saturation Voltage	(I _C = 500 mA, I _B = 50 mA)	V _{CE(sat)}	-	-	0.25	V
Collector - Emitter Saturation Voltage	(I _C = 700 mA, I _B = 70 mA)	V _{CE(sat)}	-	-	0.4	V
Base-Emitter Saturation Voltage	$(I_{C} = 700 \text{ mA}, I_{B} = 70 \text{ mA})$	V _{BE(sat)}	-	-	1.1	V
Collector-Emitter Saturation Voltage	$(I_{C} = 700 \text{ mA}, V_{CE} = 1.0 \text{ V})$	V _{BE(on)}	-	-	1.0	V


TYPICAL CHARACTERISTICS












MMBT2131T1G

TYPICAL CHARACTERISTICS






Figure 7. Collector–Emitter Saturation Voltage

0

0.1

Figure 8. V_{BE(on)} Voltage

0.1

1.0





Figure 9. Thermal Response Curve

PACKAGE DIMENSIONS

SC-74 CASE 318F-05 **ISSUE N**



NOTES

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 CONTROLLING DIMENSION: INCH.
- 3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
- 318F-01, -02, -03, -04 OBSOLETE. NEW STANDARD 318F-05. 4


	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.90	1.00	1.10	0.035	0.039	0.043
A1	0.01	0.06	0.10	0.001	0.002	0.004
b	0.25	0.37	0.50	0.010	0.015	0.020
c	0.10	0.18	0.26	0.004	0.007	0.010
D	2.90	3.00	3.10	0.114	0.118	0.122
Е	1.30	1.50	1.70	0.051	0.059	0.067
e	0.85	0.95	1.05	0.034	0.037	0.041
L	0.20	0.40	0.60	0.008	0.016	0.024
ΗE	2.50	2.75	3.00	0.099	0.108	0.118
θ	0°	-	10°	0°	-	10°

STYLE 2: PIN 1. NO CONNECTION

2. COLLECTOR 3. EMITTER

4. NO CONNECTION 5. COLLECTOR

6. BASE



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and 💷 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative