## MMBD352WT1G, NSVMMBD352WT1G

## **Dual Schottky Barrier Diode**

These devices are designed primarily for UHF mixer applications but are suitable also for use in detector and ultra-fast switching circuits.

#### Features

- Very Low Capacitance Less Than 1.0 pF @ 0 V
- Low Forward Voltage 0.5 V (Typ) @  $I_F = 10 \text{ mA}$
- AEC Qualified and PPAP Capable
- NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant\*

#### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Continuous Reverse Voltage	V <sub>R</sub>	7.0	V <sub>CC</sub>

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Total Device Dissipation FR-5 Board (Note 1) $T_A = 25^{\circ}C$	P <sub>D</sub>	200	mW
Derate above 25°C		1.6	mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	625	°C/W
Total Device Dissipation Alumina Substrate (Note 2)	PD		
T <sub>A</sub> = 25°C Derate above 25°C		300 2.4	mW mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	417	°C/W
Junction and Storage Temperature	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C

1. FR-5 =  $1.0 \times 0.75 \times 0.062$  in.

2. Alumina = 0.4  $\times$  0.3  $\times$  0.024 in. 99.5% alumina.




#### **ON Semiconductor®**

http://onsemi.com



SOT-323 (SC-70) CASE 419 STYLE 9



#### MARKING DIAGRAM



M5	= Specific Device Code
М	= Date Code
	= Pb-Free Package

(Note: Microdot may be in either location)

#### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
MMBD352WT1G	SOT-323 (Pb-Free)	3,000 / Tape & Reel
NSVMMBD352WT1G	SOT-323 (Pb-Free)	3,000 / Tape & Reel

+ For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

### MMBD352WT1G, NSVMMBD352WT1G

#### **ELECTRICAL CHARACTERISTICS** ( $T_A = 25^{\circ}C$ unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS				
Forward Voltage (I <sub>F</sub> = 10 mAdc)	V <sub>F</sub>	_	0.60	V
Reverse Voltage Leakage Current $(V_R = 3.0 \text{ V})$ $(V_R = 7.0 \text{ V})$	I <sub>R</sub>		0.25 10	μΑ
Capacitance (V <sub>R</sub> = 0 V, f = 1.0 MHz)	C	-	1.0	pF

#### **TYPICAL CHARACTERISTICS**

1.0





Figure 1. Forward Voltage

Figure 2. Capacitance

#### MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS

# onsemi



onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

#### ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>