ON Semiconductor

Is Now



To learn more about onsemi[™], please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

MPS5179

Preferred Device

High Frequency Transistor

NPN Silicon

Features

• Pb-Free Packages are Available*


MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector - Emitter Voltage	V _{CEO}	12	Vdc
Collector - Base Voltage	V _{CBO}	20	Vdc
Emitter – Base Voltage	V _{EBO}	2.5	Vdc
Collector Current – Continuous	I _C	50	mAdc
Total Device Dissipation @ T _A = 25°C Derate above 25°C			W mW/°C
Total Device Dissipation @ T _C = 25°C Derate above 25°C	P _D	300 1.71	W mW/°C
Storage Temperature Range	T _{stg}	-55 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


ON Semiconductor®

http://onsemi.com



MARKING DIAGRAM





MPS5179 = Device Code

A = Assembly Location

Y = Year WW = Work Week ■ Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping [†]	
MPS5179	TO-92	5000 Units/Box	
MPS5179G	TO-92 (Pb-Free)	5000 Units/Box	
MPS5179RLRA	TO-92	2000/Tape & Reel	
MPS5179RLRAG	TO-92 (Pb-Free)	2000/Tape & Reel	
MPS5179RLRP	TO-92	2000/Tape & Ammo	
MPS5179RLRPG	TO-92 (Pb-Free)	2000/Tape & Ammo	

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

Preferred devices are recommended choices for future use and best overall value.

ON

^{*}For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MPS5179

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)


Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS	·			
Collector – Emitter Sustaining Voltage ($I_C = 3.0 \text{ mAdc}, I_B = 0$)	V _{CEO(sus)}	12	_	Vdc
Collector – Base Breakdown Voltage ($I_C = 0.001 \text{ mAdc}, I_E = 0$)	V _(BR) CBO	20	-	Vdc
Emitter – Base Breakdown Voltage $(I_E = 0.01 \text{ mAdc}, I_C = 0)$	V _{(BR)EBO}	2.5	-	Vdc
Collector Cutoff Current $(V_{CB} = 15 \text{ Vdc}, I_E = 0)$ $(V_{CB} = 15 \text{ Vdc}, I_E = 0, T_A = 150^{\circ}\text{C})$	I _{CBO}	_ _	0.02 1.0	μAdc
ON CHARACTERISTICS	<u> </u>		•	
DC Current Gain (I _C = 3.0 mAdc, V _{CE} = 1.0 Vdc)	h _{FE}	25	250	-
Collector – Emitter Saturation Voltage ($I_C = 10 \text{ mAdc}$, $I_B = 1.0 \text{ mAdc}$)	V _{CE(sat)}	-	0.4	Vdc
Base – Emitter Saturation Voltage ($I_C = 10 \text{ mAdc}$, $I_B = 1.0 \text{ mAdc}$)	V _{BE(sat)}	_	1.0	Vdc
SMALL-SIGNAL CHARACTERISTICS	<u> </u>		•	
Current – Gain – Bandwidth Product (Note 1) (I _C = 5.0 mAdc, V _{CE} = 6.0 Vdc, f = 100 MHz)	f⊤	900	2000	MHz
Collector–Base Capacitance $(V_{CB} = 10 \text{ Vdc}, I_E = 0, f = 0.1 \text{ to } 1.0 \text{ MHz})$	C _{cb}	-	1.0	pF
Small Signal Current Gain (I _C = 2.0 mAdc, V _{CE} = 6.0 Vdc, f = 1.0 kHz)	h _{fe}	25	300	-

f_T is defined as the frequency at which |h_{fe}| extrapolates to unity.

MPS5179

PACKAGE DIMENSIONS

TO-92 (TO-226) CASE 29-11 **ISSUE AL**





NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- 114-3M, 1902.
 CONTROLLING DIMENSION: INCH.
 CONTOUR OF PACKAGE BEYOND DIMENSION R
 IS UNCONTROLLED.
 LEAD DIMENSION IS UNCONTROLLED IN P AND
- BEYOND DIMENSION K MINIMUM.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.175	0.205	4.45	5.20
В	0.170	0.210	4.32	5.33
С	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
Н	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500		12.70	
L	0.250		6.35	
N	0.080	0.105	2.04	2.66
P		0.100		2.54
R	0.115		2.93	
v	0.135		3 43	

STYLE 1:

PIN 1. EMITTER

BASE 2.

COLLECTOR

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082-1312 USA **Phone**: 480–829–7710 or 800–344–3860 Toll Free USA/Canada **Fax**: 480–829–7709 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Japan: ON Semiconductor, Japan Customer Focus Center 2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051 Phone: 81-3-5773-3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.