

# 6-Pin DIP Photodarlington **Optocoupler (No Base Connection**)

# MOC8021M, MOC8050M


The MOC8021M and MOC8050M are photodarlington-type optically coupled optocouplers. The devices have a gallium arsenide infrared emitting diode coupled with a silicon darlington phototransistor.


#### **Features**

- High BV<sub>CEO</sub>:
  - Minimum 50 V (MOC8021M)
  - Minimum 80 V (MOC8050M)
- High Current Transfer Ratio:
  - Minimum 1000% (MOC8021M)
  - Minimum 500% (MOC8050M)
- No Base Connection for Improved Noise Immunity
- Safety and Regulatory Approvals:
  - ◆ UL1577, 4,170 VAC<sub>RMS</sub> for 1 Minute
  - ◆ DIN-EN/IEC60747-5-5, 850 V Peak Working Insulation Voltage
- These are Pb-Free Devices


### **Applications**

- Appliances, Measuring Instruments
- I/O Interface for Computers
- Programmable Controllers
- Portable Electronics
- Interfacing and Coupling Systems of Different Potentials and Impedance
- Solid State Relays





### **MARKING DIAGRAM**



= Logo MOC8021 = Device Code = DIN EN/IEC60747-5-5 Option (only appears on component ordered with this option) = One-Digit Year Code, e.g., "5" = Digit Work Week, Ranging from "01" to "53" Q = Assembly Package Code

\$Y

### ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 7 of this data sheet.

### **Table 1. SAFETY AND INSULATION RATINGS**

As per DIN EN/IEC 60747-5-5, this optocoupler is suitable for "safe electrical insulation" only within the safety limit data. Compliance with the safety ratings shall be ensured by means of protective circuits.

Parameter		Characteristics
Installation Classifications per DIN VDE 0110/1.89 Table 1,	DIN VDE 0110/1.89 Table 1, < 150 V <sub>RMS</sub>	
For Rated Mains Voltage	< 300 V <sub>RMS</sub>	I–IV
Climatic Classification	55/100/21	
Pollution Degree (DIN VDE 0110/1.89)	2	
Comparative Tracking Index		175

Symbol	Parameter	Value	Unit
V <sub>PR</sub>	Input–to–Output Test Voltage, Method A, $V_{IORM} \times 1.6 = V_{PR}$ , Type and Sample Test with $t_m = 10 \text{ s}$ , Partial Discharge < 5 pC	1360	V <sub>peak</sub>
	Input–to–Output Test Voltage, Method B, $V_{IORM} \times 1.875 = V_{PR}$ , 100% Production Test with $t_m = 1$ s, Partial Discharge < 5 pC	1594	V <sub>peak</sub>
V <sub>IORM</sub>	Maximum Working Insulation Voltage	850	V <sub>peak</sub>
V <sub>IOTM</sub>	Highest Allowable Over-Voltage	6,000	V <sub>peak</sub>
	External Creepage	≥ 7	mm
	External Clearance	≥ 7	mm
	External Clearance (for Option TV, 0.4" Lead Spacing)	≥ 10	mm
DTI	Distance Through Insulation (Insulation Thickness)	≥ 0.5	mm
T <sub>S</sub>	Case Temperature (Note 1)	175	°C
I <sub>S,INPUT</sub>	Input Current (Note 1)	350	mA
P <sub>S,OUTPUT</sub>	Output Power (Note 1)	800	mW
R <sub>IO</sub>	Insulation Resistance at T <sub>S</sub> , V <sub>IO</sub> = 500 V (Note 1)	> 10 <sup>9</sup>	Ω

### NOTE:

### **Table 2. ABSOLUTE MAXIMUM RATINGS**

Symbol	Parameter	Value	Units
TOTAL DEVICE			
T <sub>STG</sub>	Storage Temperature	-40 to +125	°C
T <sub>OPR</sub>	Operating Temperature	-40 to +100	°C
TJ	Junction Temperature	-40 to +125	°C
T <sub>SOL</sub>	Lead Solder Temperature	260 for 10 seconds	°C
P <sub>D</sub>	Total Device Power Dissipation @ T <sub>A</sub> = 25°C	270	mW
	Derate above 25°C	2.94	mW/°C
EMITTER			
IF	DC/Average Forward Input Current	60	mA
V <sub>R</sub>	Reverse Input Voltage	3	V
P <sub>D</sub>	LED Power Dissipation @ T <sub>A</sub> = 25°C	120	mW
	Derate Above 25°C	1.41	mW/°C
DETECTOR			
I <sub>C</sub>	Continuous Collector Current	150	mA
V <sub>CEO</sub>	Collector-Emitter Voltage - MOC8021M	50	V
	Collector-Emitter Voltage - MOC8050M	80	V
P <sub>D</sub>	Detector Power Dissipation @ T <sub>A</sub> = 25°C	150	mW
	Derate Above 25°C	1.76	mW/°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

<sup>1.</sup> Safety limit values – maximum values allowed in the event of a failure.

Table 3. ELECTRICAL CHARACTERISTICS  $T_A = 25^{\circ}C$  unless otherwise specified

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
EMITTER						
V <sub>F</sub>	Input Forward Voltage	I <sub>F</sub> = 10 mA		1.18	2.00	V
I <sub>R</sub>	Reverse Leakage Current	V <sub>R</sub> = 3.0 V		0.001	10	μΑ
DETECTOR						
BV <sub>CEO</sub>	Collector-Emitter Breakdown Voltage (MOC8021M)	I <sub>C</sub> = 1.0 mA, I <sub>F</sub> = 0	50	100		V
	(MOC8050M)		80	100		V
BV <sub>ECO</sub>	Emitter-Collector Breakdown Voltage	$I_E = 100  \mu A,  I_F = 0$	5	10		V
I <sub>CEO</sub>	Collector-Emitter Dark Current	V <sub>CE</sub> = 60 V, I <sub>F</sub> = 0			1	μΑ
C <sub>CE</sub>	Capacitance	V <sub>CE</sub> = 0 V, f = 1 MHz		8		pF

# Table 4. TRANSFER CHARACTERISTICS $T_A = 25$ °C unless otherwise specified

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
DC CHARACT	ERISTICS		•	•	•	•
CTR	Current Transfer Ratio, Collector-to-Emitter (MOC8021M)	$I_F = 10 \text{ mA}, V_{CE} = 5 \text{ V}$	1,000			%
	(MOC8050M)	$I_F = 10 \text{ mA}, V_{CE} = 1.5 \text{ V}$	500			%
AC CHARACT	ERISTICS					
t <sub>on</sub>	Turn-on Time	$I_F$ = 5 mA, $V_{CC}$ = 10 V, $R_L$ = 100 $\Omega$		8.5		μs
t <sub>off</sub>	Turn-off Time	$I_F$ = 5 mA, $V_{CC}$ = 10 V, $R_L$ = 100 $\Omega$		95		μs

### **Table 5. ISOLATION CHARACTERISTICS**

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
V <sub>ISO</sub>	Input-Output Isolation Voltage	t = 1 Minute	4170			VAC <sub>RMS</sub>
C <sub>ISO</sub>	Isolation Capacitance	V <sub>I-O</sub> = 0 V, f = 1 MHz		0.2		pF
R <sub>ISO</sub>	Isolation Resistance	$V_{I-O} = \pm 500 \text{ VDC}, T_A = 25^{\circ}\text{C}$	10 <sup>11</sup>			Ω

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

### **TYPICAL CHARACTERISTICS**




Figure 1. LED Forward Voltage vs. Forward Current




Figure 3. Normalized CTR vs. Ambient Temperature




Figure 5. Turn-off Time vs. Forward Current




Figure 2. Normalized CTR vs. Forward Current




Figure 4. Turn-on Time vs. Forward Current




Figure 6. Normalized Collector–Emitter Current vs. Collector–Emitter Voltage

# **Typical Performance Curves** (Continued)




Figure 7. Dark Current vs. Ambient Temperature

# **Switching Time Test Circuit and Waveform**




Figure 8. Switching Time Test Circuit and Waveform

### **REFLOW PROFILE**




Figure 9. Reflow Profile

Profile Freature	Pb – Free Assembly Profile
Temperature Min. (Tsmin)	150°C
Temperature Max. (Tsmax)	200°C
Time (t <sub>S</sub> ) from (Tsmin to Tsmax)	60-120 seconds
Ramp – up Rate (tto t <sub>P</sub> )	3°C/second max.
Liquidous Temperature (T <sub>L</sub> )	217°C
Time (t <sub>L</sub> ) Maintained Above (T <sub>L</sub> )	60-150 seconds
Peak Body Package Temperature	260°C +0°C / -5°C
Time (t <sub>P</sub> ) within 5°C of 260°C	30 seconds
Ramp – down Rate (T <sub>P</sub> to T <sub>L</sub> )	6°C / second max.
Time 25°C to Peak Temperature	8 minutes max.

### **ORDERING INFORMATION**

Device Order Number	Package	Packing Method <sup>†</sup>
MOC8021M	DIP 6-Pin	Tube (50 Units)
MOC8021SM	SMT 6-Pin (Lead Bend)	Tube (50 Units)
MOC8021SR2M	SMT 6-Pin (Lead Bend)	Tape and Reel (1000 Units)
MOC8021VM	DIP 6-Pin, DIN EN/IEC60747-5-5 Option	Tube (50 Units)
MOC8021SVM	SMT 6-Pin (Lead Bend), DIN EN/IEC60747-5-5 Option	Tube (50 Units)
MOC8021SR2VM	SMT 6-Pin (Lead Bend), DIN EN/IEC60747-5-5 Option	Tape and Reel (1000 Units)
MOC8021TVM	DIP 6-Pin, 0.4" Lead Spacing, DIN EN/IEC60747-5-5 Option	Tube (50 Units)

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.


### NOTE:


2. The product orderable part number system listed in this table also applies to the MOC8050M device.




### PDIP6 8.51x6.35, 2.54P CASE 646BX ISSUE O

**DATE 31 JUL 2016** 







### NOTES:


- A) NO STANDARD APPLIES TO THIS PACKAGE.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSION

DOCUMENT NUMBER:	98AON13449G	Electronic versions are uncontrolled except when accessed directly from the Document Reposit Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	PDIP6 8.51X6.35, 2.54P		PAGE 1 OF 1	

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

### PDIP6 8.51x6.35, 2.54P CASE 646BY ISSUE A

**DATE 15 JUL 2019** 





DOCUMENT NUMBER:	98AON13450G	Electronic versions are uncontrolled except when accessed directly from Printed versions are uncontrolled except when stamped "CONTROLLED (	
DESCRIPTION:	PDIP6 8.51x6.35, 2.54P		PAGE 1 OF 1


ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

### PDIP6 8.51x6.35, 2.54P CASE 646BZ ISSUE O

**DATE 31 JUL 2016** 







### NOTES:

- A) NO STANDARD APPLIES TO THIS PACKAGE.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSION

DOCUMENT NUMBER:	98AON13451G	Electronic versions are uncontrolled except when accessed directly from the Document Reposit Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	PDIP6 8.51X6.35, 2.54P		PAGE 1 OF 1	

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI., and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems. or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales