# Switch-mode Power **Rectifier**

# MURF1660CTG

These state-of-the-art devices are designed for use in switching power supplies, inverters and as free wheeling diodes.

### Features

- Ultrafast 60 Nanosecond Recovery Times
- 150°C Operating Junction Temperature
- Epoxy Meets UL 94 V-0 @ 0.125 in
- High Temperature Glass Passivated Junction
- Low Leakage Specified @ 150°C Case Temperature
- Current Derating @ Both Case and Ambient Temperatures
- Electrically Isolated. No Isolation Hardware Required.
- This is a Pb-Free Package\*

#### **Mechanical Characteristics:**

- Case: Epoxy, Molded
- Weight: 1.9 Grams (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 Seconds

#### MAXIMUM RATINGS (Per Leg)

Rating	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	600	V
Average Rectified Forward Current Total Device, (Rated V <sub>R</sub> ), T <sub>C</sub> = 150°C Per Diode Per Device	I <sub>F(AV)</sub>	8 16	A
Peak Repetitive Forward Current (Rated V <sub>R</sub> , Square Wave, 20 kHz), $T_{C} = 150^{\circ}C$	I <sub>FM</sub>	16	A
Non-repetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz)	I <sub>FSM</sub>	100	A
Operating Junction and Storage Temperature	T <sub>J</sub> , T <sub>stg</sub>	– 65 to +150	°C
$\begin{array}{l} RMS \mbox{ Isolation Voltage} \\ (t=0.3 \mbox{ second, R.H.} \leq 30\%, \mbox{ T}_A = 25^\circ C) \\ (Note 1) \mbox{ Per Figure 3} \end{array}$	V <sub>iso1</sub>	4500	V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques


1. Proper strike and creepage distance must be provided.



## ON Semiconductor®

www.onsemi.com

## **ULTRAFAST RECTIFIER** 16 AMPERES, 600 VOLTS





= Assembly Location = Year WW = Work Week

U1660

А Y

- = Device Code
- G = Pb-Free Package AKA

= Diode Polarity

## **ORDERING INFORMATION**

Device	Package	Shipping
MURF1660CTG	TO-220 (Pb-Free)	50 Units / Rail

Reference Manual, SOLDERRM/D.

## MURF1660CTG

#### THERMAL CHARACTERISTICS (Per Leg)

Characteristic	Symbol	Value	Unit
Maximum Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	3.0	°C/W
Lead Temperature for Soldering Purposes: 1/8" from Case for 5 Seconds	ΤL	260	°C

#### ELECTRICAL CHARACTERISTICS (Per Leg)

Characteristic	Symbol	Value	Unit
Maximum Instantaneous Forward Voltage (Note 2) ( $i_F = 8.0 \text{ A}, T_C = 150^{\circ}\text{C}$ ) ( $i_F = 8.0 \text{ A}, T_C = 25^{\circ}\text{C}$ )	VF	1.20 1.50	V
Maximum Instantaneous Reverse Current (Note 2) (Rated DC Voltage, $T_C = 150^{\circ}$ C) (Rated DC Voltage, $T_C = 25^{\circ}$ C)	İR	500 10	μΑ
Maximum Reverse Recovery Time (I <sub>F</sub> = 1.0 A, di/dt = 50 A/μs) (I <sub>F</sub> = 0.5 A, i <sub>R</sub> = 1.0 A, I <sub>REC</sub> = 0.25 A)	t <sub>rr</sub>	60 50	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. Pulse Test: Pulse Width = 300  $\mu$ s, Duty Cycle  $\leq$  2.0%.




Figure 1. Typical Forward Voltage, Per Leg




Figure 2. Typical Reverse Current, Per Leg\*

## MURF1660CTG

## **TEST CONDITION FOR ISOLATION TEST\***





Figure 3. Mounting Position

\* Measurement made between leads and heatsink with all leads shorted together.

## **MOUNTING INFORMATION**




**Clip-Mounted** 

Figure 4. Typical Mounting Technique

FULLPAK is a trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.





DOCUMENT NUMBER:	98ASB42514B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	TO-220 FULLPAK		PAGE 1 OF 1	
ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the				

© Semiconductor Components Industries, LLC, 2019

rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent\_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

#### ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>