# **TinyLogic ULP-A 2-Input Non-Inverting Multiplexer**

# NC7SV157

The NC7SV157 is a single 2-input non-inverting multiplexer in tiny footprint packages. The device is designed to operate for  $V_{CC} = 0.9 \text{ V}$ to 3.6 V.

# Features

- Designed for 0.9 V to 3.6 V V<sub>CC</sub> Operation
- 1.9 ns t<sub>PD</sub> at 3.3 V (Typ)
- Inputs/Outputs Over-Voltage Tolerant up to 3.6 V
- I<sub>OFF</sub> Supports Partial Power Down Protection
- Source/Sink 24 mA at 3.3 V
- Available in SC-88A and MicroPak<sup>TM</sup> Packages
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant




Figure 1. Pinout Diagrams (Top Views)




Figure 2. Logic Symbol

#### **PIN ASSIGNMENT**

| Pin | Function        |
|-----|-----------------|
| 1   | 11              |
| 2   | GND             |
| 3   | 10              |
| 4   | Z               |
| 5   | V <sub>CC</sub> |
| 6   | S               |




CC

KK

XY

Ζ

# MARKING DIAGRAMS



- = Date Code Μ
- = Pb-Free Package

**ORDERING INFORMATION** 

See detailed ordering, marking and shipping information on page 6 of this data sheet.

| FUN | стю | N TA | BLE |
|-----|-----|------|-----|
|     |     |      |     |

| Inputs |                |                | Output   |  |
|--------|----------------|----------------|--|--|
| S      | I <sub>1</sub> | I <sub>0</sub> | $Z = (I_0) \cdot (\overline{S}) + (I_1) \cdot (S)$ |  |
| L      | Х              | L              | L  |  |
| L      | Х              | Н              | Н  |  |
| Н      | L              | Х              | L  |  |
| Н      | Н              | Х              | Н  |  |

H = HIGH Logic Level

L = LOW Logic Level

X = Don't Care

© Semiconductor Components Industries, LLC, 2021 January, 2024 - Rev. 3

# MAXIMUM RATINGS

| Symbol                              | Characteristic                               | s   | Value   | Unit |
|-------------------------------------|--|---|---|------|
| V <sub>CC</sub>                     | DC Supply Voltage                            |   | -0.5 to +4.3  | V    |
| V <sub>IN</sub>                     | DC Input Voltage                             |   | -0.5 to +4.3  | V    |
| V <sub>OUT</sub>                    | DC Output Voltage                            | Active-Mode (High or Low State)<br>Tri-State Mode (Note 1)<br>Power-Down Mode (V <sub>CC</sub> = 0 V) | -0.5 to V <sub>CC</sub> + 0.5<br>-0.5 to +4.3<br>-0.5 to +4.3 | V    |
| I <sub>IK</sub>                     | DC Input Diode Current                       | V <sub>IN</sub> < GND   | -50   | mA   |
| I <sub>OK</sub>                     | DC Output Diode Current                      | V <sub>OUT</sub> < GND  | -50   | mA   |
| IOUT                                | DC Output Source/Sink Current                |   | ±50   | mA   |
| I <sub>CC</sub> or I <sub>GND</sub> | DC Supply Current per Supply Pin or Ground F | Pin   | ±50   | mA   |
| T <sub>STG</sub>                    | Storage Temperature Range                    |   | -65 to +150   | °C   |
| ΤL                                  | Lead Temperature, 1 mm from Case for 10 Sec  | conds   | 260   | °C   |
| TJ                                  | Junction Temperature Under Bias              |   | +150  | °C   |
| $\theta_{JA}$                       | Thermal Resistance (Note 2)                  | SC-88A<br>MicroPak  | 377<br>154  | °C/W |
| PD                                  | Power Dissipation in Still Air               | SC-88A<br>MicroPak  | 332<br>812  | mW   |
| MSL                                 | Moisture Sensitivity                         |   | Level 1   | -    |
| F <sub>R</sub>                      | Flammability Rating                          | Oxygen Index: 28 to 34  | UL 94 V-0 @ 0.125 in  | -    |
| $V_{\text{ESD}}$                    | ESD Withstand Voltage (Note 3)               | Human Body Model<br>Charged Device Model  | 2000<br>1000  | V    |
| I <sub>Latchup</sub>                | Latchup Performance (Note 4)                 |   | ±100  | mA   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

should not be assumed, damage may occur and reliability may be affected.
Applicable to devices with outputs that may be tri-stated.
Measured with minimum pad spacing on an FR4 board, using 10 mm-by-1 inch, 2 ounce copper trace no air flow per JESD51-7.
HBM tested to EIA / JESD22-A114-A. CDM tested to JESD22-C101-A. JEDEC recommends that ESD qualification to EIA/JESD22-A115A (Machine Model) be discontinued.
Tested to EIA/JESD78 Class II.

# **RECOMMENDED OPERATING CONDITIONS**

| Symbol                          | Parameter                           |   | Min         | Max                           | Unit |
|---------------------------------|-------------------------------------|---|-------------|-------------------------------|------|
| V <sub>CC</sub>                 | Positive DC Supply Voltage          |   | 0.9         | 3.6                           | V    |
| V <sub>IN</sub>                 | DC Input Voltage                    |   | 0           | 3.6                           | V    |
| V <sub>OUT</sub>                | DC Output Voltage                   | Active-Mode (High or Low State)<br>Tri-State Mode (Note 1)<br>Power-Down Mode (V <sub>CC</sub> = 0 V) | 0<br>0<br>0 | V <sub>CC</sub><br>3.6<br>3.6 |      |
| T <sub>A</sub>                  | Operating Temperature Range         |   | -40         | +85                           | °C   |
| t <sub>r</sub> , t <sub>f</sub> | Input Transition Rise and Fall Time | $V_{CC}=3.3~V\pm0.3~V$  | 0           | 10                            | ns/V |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

# DC ELECTRICAL CHARACTERISTICS

|                 |                   |                                      |                     | T                    | A = 25°                  | c                    | T <sub>A</sub> = -40°0 | C to +85°C             |      |  |
|-----------------|-------------------|--------------------------------------|---------------------|----------------------|--------------------------|----------------------|------------------------|------------------------|------|--|
| Symbol          | Parameter         | Condition                            | V <sub>CC</sub> (V) | Min                  | Тур                      | Max                  | Min                    | Мах                    | Unit |  |
| VIH             | High-Level Input  |                                      | 0.9                 | _                    | 0.5                      | -                    | -                      | -                      | V    |  |
|                 | Voltage           |                                      | 1.1 to 1.3          | $0.65 \times V_{CC}$ | -                        | -                    | $0.65 \times V_{CC}$   | -                      |      |  |
|                 |                   |                                      | 1.4 to 1.6          | $0.65 \times V_{CC}$ | -                        | -                    | $0.65 \times V_{CC}$   | -                      |      |  |
|                 |                   |                                      | 1.65 to 1.95        | $0.65 \times V_{CC}$ | -                        | -                    | $0.65 \times V_{CC}$   | -                      |      |  |
|                 |                   |                                      | 2.3 to <2.7         | 1.6                  | -                        | -                    | 1.6                    | -                      |      |  |
|                 |                   |                                      | 2.7 to 3.6          | 2.0                  | -                        | -                    | 2.0                    | -                      |      |  |
| VIL             | Low-Level Input   |                                      | 0.9                 | -                    | 0.5                      | -                    | -                      | -                      | V    |  |
|                 | Voltage           |                                      | 1.1 to 1.3          | -                    | -                        | $0.35 \times V_{CC}$ | -                      | 0.35 x V <sub>CC</sub> |      |  |
|                 |                   |                                      | 1.4 to 1.6          | -                    | -                        | $0.35 \times V_{CC}$ | _                      | 0.35 x V <sub>CC</sub> |      |  |
|                 |                   |                                      | 1.65 to 1.95        | -                    | -                        | $0.35 \times V_{CC}$ | _                      | 0.35 x V <sub>CC</sub> |      |  |
|                 |                   |                                      | 2.3 to <2.7         | -                    | -                        | 0.7                  | -                      | 0.7                    |      |  |
|                 |                   |                                      | 2.7 to 3.6          | -                    | -                        | 0.8                  | -                      | 0.8                    |      |  |
| V <sub>OH</sub> | High-Level Output | $V_{IN} = V_{IH} \text{ or } V_{IL}$ |                     |                      |                          |                      |                        |                        | V    |  |
|                 | Voltage           | I <sub>OH</sub> = -100 μA            | 0.9                 | _                    | V <sub>CC</sub> -<br>0.1 | -                    | -                      | -                      |      |  |
|                 |                   |                                      | 1.1 to 1.3          | $V_{CC}-0.1$         | -                        | -                    | $V_{CC}-0.1$           | -                      |      |  |
|                 |                   |                                      | 1.4 to 1.6          | $V_{CC} - 0.1$       | -                        | -                    | V <sub>CC</sub> - 0.1  | -                      |      |  |
|                 |                   |                                      |                     | 1.65 to 1.95         | $V_{CC} - 0.2$           | -                    | -                      | $V_{CC} - 0.2$         | -    |  |
|                 |                   |                                      | 2.3 to <2.7         | $V_{CC}-0.2$         | -                        | -                    | $V_{CC}-0.2$           | -                      |      |  |
|                 |                   |                                      | 2.7 to 3.6          | $V_{CC} - 0.2$       | -                        | -                    | $V_{CC} - 0.2$         | -                      |      |  |
|                 |                   | $I_{OH} = -2 \text{ mA}$             | 1.1 o 1.3           | $0.75 \times V_{CC}$ | -                        | -                    | $0.75 \times V_{CC}$   | -                      |      |  |
|                 |                   | I <sub>OH</sub> = -4 mA              | 1.4 to 1.6          | $0.75 \times V_{CC}$ | -                        | -                    | $0.75 \times V_{CC}$   | -                      |      |  |
|                 |                   | I <sub>OH</sub> = -6 mA              | 1.65 to 1.95        | 1.25                 | -                        | -                    | 1.25                   | -                      |      |  |
|                 |                   |                                      | 2.3 to <2.7         | 2.0                  | -                        | -                    | 2.0                    | -                      |      |  |
|                 |                   | I <sub>OH</sub> = -12 mA             | 2.3 to <2.7         | 1.8                  | -                        | -                    | 1.8                    | -                      |      |  |
|                 |                   |                                      | 2.7 to 3.6          | 2.2                  | -                        | -                    | 2.2                    | -                      |      |  |
|                 |                   | I <sub>OH</sub> = -18 mA             | 2.3 to <2.7         | 1.7                  | -                        | -                    | 1.7                    | -                      |      |  |
|                 |                   |                                      | 2.7 to 3.6          | 2.4                  | -                        | -                    | 2.4                    | -                      |      |  |
|                 |                   | I <sub>OH</sub> = -24 mA             | 2.7 to 3.6          | 2.2                  | -                        | -                    | 2.2                    | -                      |      |  |

## DC ELECTRICAL CHARACTERISTICS (continued)

|                  |                              |  |                     | ٦   | Γ <sub>A</sub> = 25° | С                    | T <sub>A</sub> = -40° | C to +85°C           |      |
|------------------|------------------------------|--|---------------------|-----|----------------------|----------------------|-----------------------|----------------------|------|
| Symbol           | Parameter                    | Condition  | V <sub>CC</sub> (V) | Min | Тур                  | Max                  | Min                   | Max                  | Unit |
| V <sub>OL</sub>  | Low-Level                    | $V_{IN} = V_{IH} \text{ or } V_{IL}$   |                     |     |                      |                      |                       |                      | V    |
|                  | Output Voltage               | I <sub>OL</sub> = 100 μA   | 0.9                 | _   | 0.1                  | -                    | -                     | -                    |      |
|                  |                              |  | 1.1 to 1.3          | -   | -                    | 0.1                  | I                     | 0.1                  |      |
|                  |                              |  | 1.4 to 1.6          | -   | -                    | 0.1                  | -                     | 0.1                  |      |
|                  |                              |  | 1.65 to 1.95        | -   | -                    | 0.2                  | I                     | 0.2                  |      |
|                  |                              |  | 2.3 to < 2.7        | -   | -                    | 0.2                  | -                     | 0.2                  |      |
|                  |                              |  | 2.7 to 3.6          | -   | -                    | 0.2                  | -                     | 0.2                  |      |
|                  |                              | I <sub>OL</sub> = 2 mA   | 1.1 o 1.3           | -   | -                    | $0.25 \times V_{CC}$ | -                     | $0.25 \times V_{CC}$ |      |
|                  |                              | I <sub>OL</sub> = 4 mA   | 1.4 to 1.6          | -   | -                    | $0.25 \times V_{CC}$ | -                     | $0.25 \times V_{CC}$ |      |
|                  |                              | I <sub>OL</sub> = 6 mA   | 1.65 to 1.95        | -   | -                    | 0.3                  | -                     | 0.3                  |      |
|                  |                              | I <sub>OL</sub> = 12 mA  | 2.3 to <2.7         | -   | -                    | 0.4                  | -                     | 0.4                  |      |
|                  |                              |  | 2.7 to 3.6          | -   | -                    | 0.4                  | -                     | 0.4                  |      |
|                  |                              | I <sub>OL</sub> = 18 mA  | 2.3 to <2.7         | -   | -                    | 0.6                  | -                     | 0.6                  |      |
|                  |                              |  | 2.7 to 3.6          | -   | -                    | 0.4                  | -                     | 0.4                  |      |
|                  |                              | I <sub>OL</sub> = 24 mA  | 2.7 to 3.6          | -   | -                    | 0.55                 | -                     | 0.55                 |      |
| I <sub>IN</sub>  | Input Leakage<br>Current     | $V_{IN} = 0 V \text{ to } 3.6 V$   | 0.9 to 3.6          | -   | -                    | ±0.1                 | -                     | ±0.5                 | μA   |
| I <sub>OFF</sub> | Power Off Leakage<br>Current | $V_{IN} = 0 V \text{ to } 3.6 V \text{ or}$<br>$V_{OUT} = 0 V \text{ to } 3.6 V$ | 0                   | _   | -                    | 0.5                  | -                     | 0.5                  | μA   |
| Icc              | Quiescent Supply<br>Current  | $V_{IN} = V_{CC}$ or GND   | 0.9 to 3.6          | _   | -                    | 0.9                  | -                     | 0.9                  | μA   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

#### AC ELECTRICAL CHARACTERISTICS


|                    |  |  |                     | ٦   | A = 25°C | )    | T <sub>A</sub> = -40°C | C to +85°C |      |
|--------------------|--|--|---------------------|-----|----------|------|------------------------|------------|------|
| Symbol             | Parameter  | Condition                                      | V <sub>CC</sub> (V) | Min | Тур      | Max  | Min                    | Мах        | Unit |
| t <sub>PLH</sub> , | Propagation Delay,   | $R_L$ = 1 M $\Omega$ , $C_L$ = 15 pF           | 0.9                 | -   | 26.2     | -    | -                      | -          | ns   |
| t <sub>PHL</sub>   | (S or I <sub>0</sub> or I <sub>1</sub> ) to Z<br>(Figures 3 and 4) | $R_L = 2 \text{ k}\Omega, C_L = 15 \text{ pF}$ | 1.1 to 1.3          | -   | 7.2      | 17.7 | -                      | 20.5       |      |
|                    |  |  | 1.4 to 1.6          | -   | 3.8      | 8.5  | -                      | 9.5        |      |
|                    |  | $R_L$ = 500 $\Omega$ , $C_L$ = 30 pF           | 1.65 to 1.95        | -   | 3.1      | 6.7  | -                      | 7.5        |      |
|                    |  |  | 2.3 to 2.7          | -   | 2.2      | 4.1  | -                      | 4.4        |      |
|                    |  |  | 2.7 to 3.6          | -   | 1.9      | 3.4  | -                      | 3.6        |      |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# **CAPACITIVE CHARACTERISTICS**

| Symbol           | Parameter                              | Test Condition  | Typical (T <sub>A</sub> = 25°C) | Unit |
|------------------|--|---|---------------------------------|------|
| C <sub>IN</sub>  | Input Capacitance                      | V <sub>CC</sub> = 0 V                                     | 2.0                             | pF   |
| C <sub>OUT</sub> | Output Capacitance                     | V <sub>CC</sub> = 0 V                                     | 4.5                             | pF   |
| C <sub>PD</sub>  | Power Dissipation Capacitance (Note 5) | f = 10 MHz, V_{CC} = 0.9 to 3.6 V, V_{IN} = 0 V or V_{CC} | 10.0                            | pF   |


5.  $C_{PD}$  is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation  $I_{CC(OPR)} = C_{PD} \bullet V_{CC} \bullet f_{in} + I_{CC}$ .  $C_{PD}$  is used to determine the no-load dynamic power consumption:  $P_D = C_{PD} \bullet V_{CC}^2 \bullet f_{in} + I_{CC} \bullet V_{CC}$ .



f = 1 MHz

| Test                                | Switch Position     |
|-------------------------------------|---------------------|
| t <sub>PLH</sub> / t <sub>PHL</sub> | Open                |
| t <sub>PLZ</sub> / t <sub>PZL</sub> | 2 x V <sub>CC</sub> |
| t <sub>PHZ</sub> / t <sub>PZH</sub> | GND                 |

Figure 3. Test Circuit



| V <sub>CC</sub> , V | V <sub>mi</sub> , V | V <sub>mo</sub> , V | V <sub>Y</sub> , V |
|---------------------|---------------------|---------------------|--------------------|
| 0.9                 | V <sub>CC</sub> / 2 | V <sub>CC</sub> / 2 | 0.1                |
| 1.1 to 1.3          | V <sub>CC</sub> / 2 | V <sub>CC</sub> / 2 | 0.1                |
| 1.4 to 1.6          | V <sub>CC</sub> / 2 | V <sub>CC</sub> / 2 | 0.1                |
| 1.65 to 1.95        | V <sub>CC</sub> / 2 | V <sub>CC</sub> / 2 | 0.15               |
| 2.3 to 2.7          | V <sub>CC</sub> / 2 | V <sub>CC</sub> / 2 | 0.15               |
| 3.0 to 3.6          | 1.5                 | 1.5                 | 0.3                |


Figure 4. Switching Waveforms

### **ORDERING INFORMATION**

| Device      | Package  | Marking | Pin 1 Orientation<br>(See below) | Shipping <sup>†</sup> |
|-------------|----------|---------|----------------------------------|-----------------------|
| NC7SV157P6X | SC-88A   | VF7     | Q4                               | 3000 / Tape & Reel    |
| NC7SV157L6X | MicroPak | H9      | Q4                               | 5000 / Tape & Reel    |

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


## Pin 1 Orientation in Tape and Reel



MicroPak is trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.


#### PACKAGE DIMENSIONS


SIP6 1.45X1.0 CASE 127EB ISSUE O



OTHER LINE IN THE MARK CODE LAYOUT.

#### PACKAGE DIMENSIONS





NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. CONTROLLING DIMENSION: MILLIMETERS. 2
- 3
- DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRU-SIONS, OR GATE BURRS SHALL NOT EXCEED 0.20 PER END. DIMENSIONS D AND E1 AT THE OUTERMOST EXTREMES OF 4
- THE PLASTIC BODY AND DATUM H. DATUMS A AND B ARE DETERMINED AT DATUM H. 5
- DIMENSIONS b AND c APPLY TO THE FLAT SECTION OF THE LEAD BETWEEN 0.08 AND 0.15 FROM THE TIP. 6
- 7. DIMENSION & DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 TOTAL IN EXCESS OF DIMENSION b AT MAXIMUM MATERIAL CONDI TION. THE DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OF THE FOOT.

|     | MILLIMETERS |      |      | INCHES    |       |       |
|-----|-------------|------|------|-----------|-------|-------|
| DIM | MIN         | NOM  | MAX  | MIN       | NOM   | MAX   |
| Α   |             |      | 1.10 |           |       | 0.043 |
| A1  | 0.00        |      | 0.10 | 0.000     |       | 0.004 |
| A2  | 0.70        | 0.90 | 1.00 | 0.027     | 0.035 | 0.039 |
| p   | 0.15        | 0.20 | 0.25 | 0.006     | 0.008 | 0.010 |
| С   | 0.08        | 0.15 | 0.22 | 0.003     | 0.006 | 0.009 |
| D   | 1.80        | 2.00 | 2.20 | 0.070     | 0.078 | 0.086 |
| Е   | 2.00        | 2.10 | 2.20 | 0.078     | 0.082 | 0.086 |
| E1  | 1.15        | 1.25 | 1.35 | 0.045     | 0.049 | 0.053 |
| е   | 0.65 BSC    |      |      | 0.026 BSC |       |       |
| L   | 0.26        | 0.36 | 0.46 | 0.010     | 0.014 | 0.018 |
| L2  | 0.15 BSC    |      |      | 0.006 BSC |       |       |
| aaa | 0.15        |      |      | 0.006     |       |       |
| bbb | 0.30        |      |      | 0.012     |       |       |
| ccc | 0.10        |      |      | 0.004     |       |       |
| ddd | 0.10        |      |      | 0.004     |       |       |
|     |             |      |      |           |       |       |

6X 0.30 -0.66 2.50 0.65 PITCH DIMENSIONS: MILLIMETERS

RECOMMENDED SOLDERING FOOTPRINT\*

\*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

onsemi. OnSemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries. LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### ADDITIONAL INFORMATION

#### TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales