

# NDF05N50Z, NDD05N50Z

## N-Channel Power MOSFET 500 V, 1.5 Ω

### Features

- Low ON Resistance
- Low Gate Charge
- ESD Diode-Protected Gate
- 100% Avalanche Tested
- 100% Rg Tested
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

### ABSOLUTE MAXIMUM RATINGS (T<sub>C</sub> = 25°C unless otherwise noted)

| Rating  | Symbol                            | NDF             | NDD | Unit |
|---|-----------------------------------|-----------------|-----|------|
| Drain-to-Source Voltage   | V <sub>DSS</sub>                  | 500             |     | V    |
| Continuous Drain Current R <sub>θJC</sub>   | I <sub>D</sub>                    | 5.5<br>(Note 1) | 4.7 | A    |
| Continuous Drain Current R <sub>θJC</sub> , T <sub>A</sub> = 100°C                  | I <sub>D</sub>                    | 3.5<br>(Note 1) | 3   | A    |
| Pulsed Drain Current, V <sub>GS</sub> @ 10 V  | I <sub>DM</sub>                   | 20              | 19  | A    |
| Power Dissipation R <sub>θJC</sub>  | P <sub>D</sub>                    | 30              | 83  | W    |
| Gate-to-Source Voltage  | V <sub>GS</sub>                   | ±30             |     | V    |
| Single Pulse Avalanche Energy, I <sub>D</sub> = 5.0 A                               | E <sub>AS</sub>                   | 130             |     | mJ   |
| ESD (HBM) (JESD22-A114)   | V <sub>esd</sub>                  | 3000            |     | V    |
| RMS Isolation Voltage (t = 0.3 sec., R.H. ≤ 30%, T <sub>A</sub> = 25°C) (Figure 17) | V <sub>ISO</sub>                  | 4500            |     | V    |
| Peak Diode Recovery (Note 2)  | dV/dt                             | 4.5             |     | V/ns |
| MOSFET dV/dt  | dV/dt                             | 60              |     | V/ns |
| Continuous Source Current (Body Diode)  | I <sub>S</sub>                    | 5               |     | A    |
| Maximum Temperature for Soldering Leads   | T <sub>L</sub>                    | 260             |     | °C   |
| Operating Junction and Storage Temperature Range                                    | T <sub>J</sub> , T <sub>stg</sub> | -55 to 150      |     | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



1. Limited by maximum junction temperature
2. I<sub>S</sub> = 4.4 A, di/dt ≤ 100 A/μs, V<sub>DD</sub> ≤ BV<sub>DSS</sub>, T<sub>J</sub> = +150°C




**ON Semiconductor**®

[www.onsemi.com](http://www.onsemi.com)


| V <sub>DSS</sub> | R <sub>DS(on)</sub> (MAX) @ 2.2 A |
|------------------|-----------------------------------|
| 500 V            | 1.5 Ω                             |



**NDF05N50ZG,  
NDF05N50ZH  
TO-220FP  
CASE 221AH**



**NDD05N50Z-1G  
IPAK  
CASE 369D**



**NDD05N50ZT4G  
DPAK  
CASE 369AA**

### ORDERING AND MARKING INFORMATION

See detailed ordering, marking and shipping information on page 7 of this data sheet.

# NDF05N50Z, NDD05N50Z

## THERMAL RESISTANCE

| Parameter                        | Symbol           | Value                | Unit |
|----------------------------------|------------------|----------------------|------|
| Junction-to-Case (Drain)         | R <sub>θJC</sub> | NDF05N50Z            | 4.2  |
|                                  |                  | NDD05N50Z            | 1.5  |
| Junction-to-Ambient Steady State | R <sub>θJA</sub> | (Note 3) NDF05N50Z   | 50   |
|                                  |                  | (Note 4) NDD05N50Z   | 38   |
|                                  |                  | (Note 3) NDD05N50Z-1 | 80   |

3. Insertion mounted

4. Surface mounted on FR4 board using 1" sq. pad size, (Cu area = 1.127 in sq [2 oz] including traces).

## ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25°C unless otherwise noted)

| Characteristic | Symbol | Test Conditions | Min | Typ | Max | Unit |
|----------------|--------|-----------------|-----|-----|-----|------|
|----------------|--------|-----------------|-----|-----|-----|------|

### OFF CHARACTERISTICS

|  |                                     |  |       |     |     |      |
|--|-------------------------------------|--|-------|-----|-----|------|
| Drain-to-Source Breakdown Voltage          | BV <sub>DSS</sub>                   | V <sub>GS</sub> = 0 V, I <sub>D</sub> = 1 mA   | 500   |     |     | V    |
| Breakdown Voltage Temperature Co-efficient | ΔBV <sub>DSS</sub> /ΔT <sub>J</sub> | Reference to 25°C, I <sub>D</sub> = 1 mA       |       | 0.6 |     | V/°C |
| Drain-to-Source Leakage Current            | I <sub>DSS</sub>                    | V <sub>DS</sub> = 500 V, V <sub>GS</sub> = 0 V | 25°C  |     | 1   | μA   |
|  |                                     |  | 150°C |     | 50  |      |
| Gate-to-Source Forward Leakage             | I <sub>GSS</sub>                    | V <sub>GS</sub> = ±20 V                        |       |     | ±10 | μA   |

### ON CHARACTERISTICS (Note 5)

|                                      |                     |  |     |      |     |   |
|--------------------------------------|---------------------|--|-----|------|-----|---|
| Static Drain-to-Source On-Resistance | R <sub>DS(on)</sub> | V <sub>GS</sub> = 10 V, I <sub>D</sub> = 2.2 A             |     | 1.25 | 1.5 | Ω |
| Gate Threshold Voltage               | V <sub>GS(th)</sub> | V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 50 μA | 3.0 | 3.9  | 4.5 | V |
| Forward Transconductance             | g <sub>FS</sub>     | V <sub>DS</sub> = 15 V, I <sub>D</sub> = 2.5 A             |     | 3.5  |     | S |

### DYNAMIC CHARACTERISTICS

|  |                  |   |     |      |     |    |
|--|------------------|---|-----|------|-----|----|
| Input Capacitance (Note 6)               | C <sub>iss</sub> | V <sub>DS</sub> = 25 V, V <sub>GS</sub> = 0 V, f = 1.0 MHz            | 421 | 530  | 632 | pF |
| Output Capacitance (Note 6)              | C <sub>oss</sub> |   | 50  | 68   | 80  |    |
| Reverse Transfer Capacitance (Note 6)    | C <sub>rss</sub> |   | 8   | 15   | 25  |    |
| Total Gate Charge (Note 6)               | Q <sub>g</sub>   | V <sub>DD</sub> = 250 V, I <sub>D</sub> = 5 A, V <sub>GS</sub> = 10 V | 9   | 18.5 | 28  | nC |
| Gate-to-Source Charge (Note 6)           | Q <sub>gs</sub>  |   | 2   | 4    | 6   |    |
| Gate-to-Drain ("Miller") Charge (Note 6) | Q <sub>gd</sub>  |   | 5   | 10   | 15  |    |
| Plateau Voltage                          | V <sub>GP</sub>  |   |     | 6.5  |     | V  |
| Gate Resistance                          | R <sub>g</sub>   |   | 1.5 | 4.5  | 8   | Ω  |

### RESISTIVE SWITCHING CHARACTERISTICS

|                     |                     |   |  |    |  |    |
|---------------------|---------------------|---|--|----|--|----|
| Turn-On Delay Time  | t <sub>d(on)</sub>  | V <sub>DD</sub> = 250 V, I <sub>D</sub> = 5 A, V <sub>GS</sub> = 10 V, R <sub>G</sub> = 5 Ω |  | 11 |  | ns |
| Rise Time           | t <sub>r</sub>      |   |  | 15 |  |    |
| Turn-Off Delay Time | t <sub>d(off)</sub> |   |  | 24 |  |    |
| Fall Time           | t <sub>f</sub>      |   |  | 14 |  |    |

### SOURCE-DRAIN DIODE CHARACTERISTICS (T<sub>C</sub> = 25°C unless otherwise noted)

|                         |                 |   |  |      |     |    |
|-------------------------|-----------------|---|--|------|-----|----|
| Diode Forward Voltage   | V <sub>SD</sub> | I <sub>S</sub> = 5 A, V <sub>GS</sub> = 0 V   |  |      | 1.6 | V  |
| Reverse Recovery Time   | t <sub>rr</sub> | V <sub>GS</sub> = 0 V, V <sub>DD</sub> = 30 V, I <sub>S</sub> = 5 A, di/dt = 100 A/μs |  | 255  |     | ns |
| Reverse Recovery Charge | Q <sub>rr</sub> |   |  | 1.25 |     | μC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Width ≤ 380 μs, Duty Cycle ≤ 2%.

6. Guaranteed by design.

# NDF05N50Z, NDD05N50Z

## TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Region versus Gate-to-Source Voltage




Figure 4. On-Resistance versus Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature




Figure 6.  $BV_{DSS}$  Variation with Temperature

# NDF05N50Z, NDD05N50Z

## TYPICAL CHARACTERISTICS




Figure 7. Drain-to-Source Leakage Current versus Voltage




Figure 8. Capacitance Variation




Figure 9. Gate-to-Source Voltage and Drain-to-Source Voltage versus Total Charge




Figure 10. Resistive Switching Time Variation versus Gate Resistance




Figure 11. Diode Forward Voltage versus Current

# NDF05N50Z, NDD05N50Z

## TYPICAL CHARACTERISTICS




Figure 12. Maximum Rated Forward Biased Safe Operating Area NDF05N50Z




Figure 13. Maximum Rated Forward Biased Safe Operating Area NDD05N50Z




Figure 14. Thermal Impedance (Junction-to-Case) for NDF05N50Z




Figure 15. Thermal Impedance (Junction-to-Case) for NDD05N50Z

# NDF05N50Z, NDD05N50Z

## TYPICAL CHARACTERISTICS




Figure 16. Thermal Impedance (Junction-to-Ambient) for NDD05N50Z




Figure 17. Isolation Test Diagram

Measurement made between leads and heatsink with all leads shorted together.

\*For additional mounting information, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.




# NDF05N50Z, NDD05N50Z

## ORDERING INFORMATION

| Order Number | Package                             | Shipping†            |
|--------------|-------------------------------------|----------------------|
| NDF05N50ZG   | TO-220FP<br>(Pb-Free, Halogen-Free) | 50 Units / Rail      |
| NDF05N50ZH   | TO-220FP<br>(Pb-Free, Halogen-Free) | 50 Units / Rail      |
| NDD05N50Z-1G | IPAK<br>(Pb-Free, Halogen-Free)     | 75 Units / Rail      |
| NDD05N50ZT4G | DPAK<br>(Pb-Free, Halogen-Free)     | 2500 / Tape and Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## MARKING DIAGRAMS



A = Location Code  
 Y = Year  
 WW = Work Week  
 G, H = Pb-Free, Halogen-Free Package

# MECHANICAL CASE OUTLINE


## PACKAGE DIMENSIONS

ON Semiconductor®






### TO-220 FULLPACK, 3-LEAD CASE 221AH ISSUE F

DATE 30 SEP 2014




- NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
  2. CONTROLLING DIMENSION: MILLIMETERS.
  3. CONTOUR UNCONTROLLED IN THIS AREA.
  4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH AND GATE PROTRUSIONS. MOLD FLASH AND GATE PROTRUSIONS NOT TO EXCEED 0.13 PER SIDE. THESE DIMENSIONS ARE TO BE MEASURED AT OUTERMOST EXTREME OF THE PLASTIC BODY.
  5. DIMENSION b2 DOES NOT INCLUDE DAMBAR PROTRUSION. LEAD WIDTH INCLUDING PROTRUSION SHALL NOT EXCEED 2.00.
  6. CONTOURS AND FEATURES OF THE MOLDED PACKAGE BODY MAY VARY WITHIN THE ENVELOPE DEFINED BY DIMENSIONS A1 AND H1 FOR MANUFACTURING PURPOSES.

| MILLIMETERS |          |       |
|-------------|----------|-------|
| DIM         | MIN      | MAX   |
| A           | 4.30     | 4.70  |
| A1          | 2.50     | 2.90  |
| A2          | 2.50     | 2.90  |
| b           | 0.54     | 0.84  |
| b2          | 1.10     | 1.40  |
| c           | 0.49     | 0.79  |
| D           | 14.70    | 15.30 |
| E           | 9.70     | 10.30 |
| e           | 2.54 BSC |       |
| H1          | 6.60     | 7.10  |
| L           | 12.50    | 14.73 |
| L1          | ---      | 2.80  |
| P           | 3.00     | 3.40  |
| Q           | 2.80     | 3.20  |



### GENERIC MARKING DIAGRAM\*



- A = Assembly Location
- WL = Wafer Lot
- Y = Year
- WW = Work Week
- G = Pb-Free Package

- STYLE 1:  
PIN 1. MAIN TERMINAL 1  
2. MAIN TERMINAL 2  
3. GATE
- STYLE 2:  
PIN 1. CATHODE  
2. ANODE  
3. GATE

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present.

|                  |                         |  |
|------------------|-------------------------|--|
| DOCUMENT NUMBER: | 98AON52577E             | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | TO-220 FULLPACK, 3-LEAD | PAGE 1 OF 1  |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.



# MECHANICAL CASE OUTLINE


## PACKAGE DIMENSIONS

ON Semiconductor®




### IPAK CASE 369D-01 ISSUE C

DATE 15 DEC 2010



SCALE 1:1



- NOTES:
- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  - CONTROLLING DIMENSION: INCH.

| DIM | INCHES |       | MILLIMETERS |      |
|-----|--------|-------|-------------|------|
|     | MIN    | MAX   | MIN         | MAX  |
| A   | 0.235  | 0.245 | 5.97        | 6.35 |
| B   | 0.250  | 0.265 | 6.35        | 6.73 |
| C   | 0.086  | 0.094 | 2.19        | 2.38 |
| D   | 0.027  | 0.035 | 0.69        | 0.88 |
| E   | 0.018  | 0.023 | 0.46        | 0.58 |
| F   | 0.037  | 0.045 | 0.94        | 1.14 |
| G   | 0.090  | BSC   | 2.29        | BSC  |
| H   | 0.034  | 0.040 | 0.87        | 1.01 |
| J   | 0.018  | 0.023 | 0.46        | 0.58 |
| K   | 0.350  | 0.380 | 8.89        | 9.65 |
| R   | 0.180  | 0.215 | 4.45        | 5.45 |
| S   | 0.025  | 0.040 | 0.63        | 1.01 |
| V   | 0.035  | 0.050 | 0.89        | 1.27 |
| Z   | 0.155  | ---   | 3.93        | ---  |

- |  |   |  |  |
|--|---|--|--|
| <p>STYLE 1:<br/>PIN 1. BASE<br/>2. COLLECTOR<br/>3. EMITTER<br/>4. COLLECTOR</p> | <p>STYLE 2:<br/>PIN 1. GATE<br/>2. DRAIN<br/>3. SOURCE<br/>4. DRAIN</p> | <p>STYLE 3:<br/>PIN 1. ANODE<br/>2. CATHODE<br/>3. ANODE<br/>4. CATHODE</p>      | <p>STYLE 4:<br/>PIN 1. CATHODE<br/>2. ANODE<br/>3. GATE<br/>4. ANODE</p> |
| <p>STYLE 5:<br/>PIN 1. GATE<br/>2. ANODE<br/>3. CATHODE<br/>4. ANODE</p>         | <p>STYLE 6:<br/>PIN 1. MT1<br/>2. MT2<br/>3. GATE<br/>4. MT2</p>        | <p>STYLE 7:<br/>PIN 1. GATE<br/>2. COLLECTOR<br/>3. EMITTER<br/>4. COLLECTOR</p> |  |

### MARKING DIAGRAMS



- xxxxxxxxx = Device Code  
A = Assembly Location  
IL = Wafer Lot  
Y = Year  
WW = Work Week


|                         |                                    |  |
|-------------------------|------------------------------------|--|
| <b>DOCUMENT NUMBER:</b> | <b>98AON10528D</b>                 | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>IPAK (DPAK INSERTION MOUNT)</b> | <b>PAGE 1 OF 1</b>   |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

# MECHANICAL CASE OUTLINE

## PACKAGE DIMENSIONS

ON Semiconductor®




SCALE 1:1

### DPAK (SINGLE GAUGE)

#### CASE 369AA-01

#### ISSUE B

DATE 03 JUN 2010




NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- CONTROLLING DIMENSION: INCHES.
- THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS b3, L3 and Z.
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.006 INCHES PER SIDE.
- DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 0.086     | 0.094 | 2.18        | 2.38  |
| A1  | 0.000     | 0.005 | 0.00        | 0.13  |
| b   | 0.025     | 0.035 | 0.63        | 0.89  |
| b2  | 0.030     | 0.045 | 0.76        | 1.14  |
| b3  | 0.180     | 0.215 | 4.57        | 5.46  |
| c   | 0.018     | 0.024 | 0.46        | 0.61  |
| c2  | 0.018     | 0.024 | 0.46        | 0.61  |
| D   | 0.235     | 0.245 | 5.97        | 6.22  |
| E   | 0.250     | 0.265 | 6.35        | 6.73  |
| e   | 0.090 BSC |       | 2.29 BSC    |       |
| H   | 0.370     | 0.410 | 9.40        | 10.41 |
| L   | 0.055     | 0.070 | 1.40        | 1.78  |
| L1  | 0.108 REF |       | 2.74 REF    |       |
| L2  | 0.020 BSC |       | 0.51 BSC    |       |
| L3  | 0.035     | 0.050 | 0.89        | 1.27  |
| L4  | ---       | 0.040 | ---         | 1.01  |
| Z   | 0.155     | ---   | 3.93        | ---   |

- |  |   |  |  |
|--|---|--|--|
| <p>STYLE 1:<br/>PIN 1. BASE<br/>2. COLLECTOR<br/>3. EMITTER<br/>4. COLLECTOR</p> | <p>STYLE 2:<br/>PIN 1. GATE<br/>2. DRAIN<br/>3. SOURCE<br/>4. DRAIN</p> | <p>STYLE 3:<br/>PIN 1. ANODE<br/>2. CATHODE<br/>3. ANODE<br/>4. CATHODE</p>  | <p>STYLE 4:<br/>PIN 1. CATHODE<br/>2. ANODE<br/>3. GATE<br/>4. ANODE</p> |
| <p>STYLE 5:<br/>PIN 1. GATE<br/>2. ANODE<br/>3. CATHODE<br/>4. ANODE</p>         | <p>STYLE 6:<br/>PIN 1. MT1<br/>2. MT2<br/>3. GATE<br/>4. MT2</p>        | <p>STYLE 7:<br/>PIN 1. GATE<br/>2. ANODE<br/>3. EMITTER<br/>4. COLLECTOR</p> |  |

### GENERIC MARKING DIAGRAM\*




IC Discrete

- XXXXXX = Device Code
- A = Assembly Location
- L = Wafer Lot
- Y = Year
- WW = Work Week
- G = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking.

### SOLDERING FOOTPRINT\*



SCALE 3:1 (mm/inches)

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

|                  |                     |  |
|------------------|---------------------|--|
| DOCUMENT NUMBER: | 98AON13126D         | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | DPAK (SINGLE GAUGE) | PAGE 1 OF 1  |

ON Semiconductor and ON are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)