NIC9N05TS1, NIC9N05ATS1

Protected Power MOSFET

2.6 A, 52 V, N-Channel, Logic Level, Clamped MOSFET w/ ESD Protection

MAXIMUM RATINGS ($T_J = 25^{\circ}C$ unless otherwise specified)


Rating		Symbol	Value	Unit
Drain-to-Source Voltage Internally Clamped		V_{DSS}	52-59	V
Gate-to-Source Voltage - Continuous		V_{GS}	±15	V
Operating and Storage Temperature Range		T _J , T _{stg}	-55 to 150	°C
Electro-Static Discharge Capability (HBM) (MM)	ESD	5000 500	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.



ON Semiconductor®

http://onsemi.com



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

NIC9N05TS1, NIC9N05ATS1

MOSFET ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise specified) (Note 1)

Characteristic		Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS		•		•		
Drain-to-Source Breakdown Voltage (V _{GS} = 0 V, I _D = 1.0 mA, T _J = 25°C)		V _{(BR)DSS}	52	55	59	V
Zero Gate Voltage Drain Current (V _{DS} = 40 V, V _{GS} = 0 V)		I _{DSS}			10	μΑ
Gate-Body Leakage Current $(V_{GS} = \pm 8 \text{ V}, V_{DS} = 0 \text{ V})$ $(V_{GS} = \pm 14 \text{ V}, V_{DS} = 0 \text{ V})$		l _{GSS}		±22	±10	μΑ
ON CHARACTERISTICS						
Gate Threshold Voltage $(V_{DS} = V_{GS}, I_D = 100 \mu A)$		V _{GS(th)}	1.3	1.75	2.5	V
Static Drain-to-Source On-Resistance ($V_{GS} = 3.5 \text{ V}$, $I_D = 0.6 \text{ A}$) ($V_{GS} = 4.0 \text{ V}$, $I_D = 1.5 \text{ A}$) ($V_{GS} = 10 \text{ V}$, $I_D = 2.6 \text{ A}$)		R _{DS(on)}		190 165 107	380 200 125	mΩ
SOURCE-DRAIN DIODE CHARACTERISTICS						
Forward On-Voltage	I _S = 2.6 A, V _{GS} = 0 V I _S = 2.6 A, V _{GS} = 0 V, T _J = 125°C	V _{SD}		0.81 0.66	1.5	V

^{1.} Wafers tested prior to sawing.

ORDERING INFORMATION

Device	Shipping
NIC9N05TS1	5000 / Reel
NIC9N05ATS1	5000 / Reel

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales