**ON Semiconductor** 

Is Now

# Onsemi

To learn more about onsemi<sup>™</sup>, please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

# **N-Channel Power MOSFET 620 V, 1.2** Ω

#### **Features**

- Low ON Resistance
- Low Gate Charge
- ESD Diode-Protected Gate
- 100% Avalanche Tested
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant


ABSOLUTE MAXIMUM RATINGS (T<sub>C</sub> = 25°C unless otherwise noted)



## **ON Semiconductor®**

#### http://onsemi.com

V <sub>DSS</sub>	R <sub>DS(ON)</sub> (MAX) @ 3 A
620 V	1.2 Ω



#### Г Symbol NDF06N62Z Unit Rating

1	1	1
V <sub>DSS</sub>	620	V
I <sub>D</sub>	6.0	А
I <sub>D</sub>	3.8	A
I <sub>DM</sub>	20	A
PD	31	W
V <sub>GS</sub>	±30	V
E <sub>AS</sub>	113	mJ
V <sub>esd</sub>	3000	V
V <sub>ISO</sub>	4500	V
dv/dt	4.5	V/ns
۱ <sub>S</sub>	6.0	А
TL	260	°C
T <sub>J</sub> , T <sub>stg</sub>	–55 to 150	°C
	ID ID ID VGS EAS Vesd VISO dv/dt IS TL	$\begin{array}{c c c c c c c c c c c c c c c c c c c $

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Limited by maximum junction temperature

2. I\_{SD} = 6.0 A, di/dt  $\leq$  100 A/µs, V\_{DD}  $\leq$  BV\_{DSS}, T\_J = +150 ^{\circ}C

#### **ORDERING INFORMATION**

Device	Package	Shipping
NDF06N62ZG	TO-220FP (Pb-Free, Halogen-Free)	50 Units / Rail

© Semiconductor Components Industries, LLC, 2011 September, 2011 - Rev. 1

#### THERMAL RESISTANCE

Parameter	Symbol	NDF06N62Z	Unit
Junction-to-Case (Drain)	$R_{\thetaJC}$	4.0	°C/W
Junction-to-Ambient Steady State (Note 3)	$R_{\theta JA}$	50	


### **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = $25^{\circ}C$ unless otherwise noted)

Characteristic	Test Conditions		Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	$V_{GS} = 0 \text{ V}, \text{ I}_{D} = 1 \text{ mA}$	A	BV <sub>DSS</sub>	620			V
Breakdown Voltage Temperature Coefficient	Reference to 25°C, $I_D = 1 \text{ mA}$		$\Delta BV_{DSS}/ \Delta T_J$		0.6		V/°C
Drain-to-Source Leakage Current		25°C	I <sub>DSS</sub>			1	μA
	$V_{DS}$ = 620 V, $V_{GS}$ = 0 V	125°C				50	
Gate-to-Source Forward Leakage	$V_{GS} = \pm 20 V$	•	I <sub>GSS</sub>			±10	μA
ON CHARACTERISTICS (Note 4)							
Static Drain-to-Source On-Resistance	$V_{GS} = 10 \text{ V}, \text{ I}_{D} = 3.0 \text{ J}$	A	R <sub>DS(on)</sub>		0.98	1.2	Ω
Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = 100 \mu$	ιA	V <sub>GS(th)</sub>	3.0		4.5	V
Forward Transconductance	$V_{DS} = 15 \text{ V}, \text{ I}_{D} = 3.0 \text{ J}$	A	9 <sub>FS</sub>		5.0		S
OYNAMIC CHARACTERISTICS							
Input Capacitance			C <sub>iss</sub>		923		pF
Output Capacitance	V <sub>DS</sub> = 25 V, V <sub>GS</sub> = 0 V, f = 1.0 MHz		C <sub>oss</sub>		106		1
Reverse Transfer Capacitance			C <sub>rss</sub>		23		
Total Gate Charge	V <sub>DD</sub> = 310 V, I <sub>D</sub> = 6.0 A,		Qg		32		nC
Gate-to-Source Charge			Q <sub>gs</sub>		6.3		
Gate-to-Drain ("Miller") Charge	V <sub>GS</sub> = 10 V		Q <sub>gd</sub>		17		
Plateau Voltage			V <sub>gp</sub>		6.3		V
Gate Resistance			Rg		3.2		Ω
RESISTIVE SWITCHING CHARACTERI	STICS						
Turn–On Delay Time	$V_{DD}$ = 310 V, I <sub>D</sub> = 6.0 A, V <sub>GS</sub> = 10 V, R <sub>G</sub> = 5 Ω		t <sub>d(on)</sub>		13		ns
Rise Time			t <sub>r</sub>		19		
Turn-Off Delay Time			t <sub>d(off)</sub>		32		
Fall Time			t <sub>f</sub>		28		1


Diode Forward Voltage	$I_{\rm S}$ = 6.0 A, $V_{\rm GS}$ = 0 V	V <sub>SD</sub>		1.6	V
Reverse Recovery Time	$V_{GS} = 0 V, V_{DD} = 30 V$	t <sub>rr</sub>	338		ns
Reverse Recovery Charge	$I_{S} = 6.0 \text{ A}, \text{ di/dt} = 100 \text{ A/}\mu\text{s}$	Q <sub>rr</sub>	2.0		μC

3. Insertion mounted 4. Pulse Width  $\leq$  380 µs, Duty Cycle  $\leq$  2%.

#### **TYPICAL CHARACTERISTICS**



#### **TYPICAL CHARACTERISTICS**



#### **TYPICAL CHARACTERISTICS**





Figure 13. Thermal Impedance for NDF06N62Z






Measurement made between leads and heatsink with all leads shorted together.

\*For additional mounting information, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### PACKAGE DIMENSIONS

TO-220FP CASE 221D-03 **ISSUE K** 



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH

221D-01 THRU 221D-02 OBSOLETE, NEW 3. STANDARD 221D-03

	INC	HES	MILLIN	IETERS	
DIM	MIN	MAX	MIN	MAX	
Α	0.617	0.635	15.67	16.12	
В	0.392	0.419	9.96	10.63	
С	0.177	0.193	4.50	4.90	
D	0.024	0.039	0.60	1.00	
F	0.116	0.129	2.95	3.28	
G	0.100	BSC	2.54	BSC	
Н	0.118	0.135	3.00	3.43	
J	0.018	0.025	0.45	0.63	
Κ	0.503	0.541	12.78	13.73	
L	0.048	0.058	1.23	1.47	
Ν	0.200 BSC		5.08 BSC		
Q	0.122	0.138	3.10	3.50	
R	0.099	0.117	2.51	2.96	
S	0.092	0.113	2.34	2.87	
U	0.239	0.271	6.06	6.88	

STYLE 1: PIN 1. GATE

2. DRAIN SOURCE 3.

ON Semiconductor and 💷 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILC does not convey any license under its patent rights or the rights of others. SCILC products are not designed, intended, or authorized for use a components in systems intended for surgical implant into the body, or other applications. intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative