# **ON Semiconductor**

# Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# IGBT with Monolithic Free Wheeling Diode

This Insulated Gate Bipolar Transistor (IGBT) features a robust and cost effective Field Stop (FS) Trench construction, and provides superior performance in demanding switching applications, offering both low on–state voltage and minimal switching loss. The IGBT is well suited for resonant or soft switching applications.

#### **Features**

- Extremely Efficient Trench with Fieldstop Technology
- 1350 V Breakdown Voltage
- Optimized for Low Losses in IH Cooker Application
- Reliable and Cost Effective Single Die Solution
- These are Pb-Free Devices

## **Typical Applications**

- Inductive Heating
- Consumer Appliances
- Soft Switching

#### **ABSOLUTE MAXIMUM RATINGS**

Rating	Symbol	Value	Unit
Collector-emitter voltage	$V_{CES}$	1350	V
Collector current @ Tc = 25°C @ Tc = 100°C	I <sub>C</sub>	40 20	A
Pulsed collector current, $T_{pulse}$ limited by $T_{Jmax}$ , 10 $\mu s$ Pulse, $V_{GE} = 15 \text{ V}$	I <sub>CM</sub>	120	А
Diode forward current @ Tc = 25°C @ Tc = 100°C	I <sub>F</sub>	40 20	A
Diode pulsed current, $T_{pulse}$ limited by $T_{Jmax}$ , 10 $\mu s$ Pulse, $V_{GE}$ = 0 $V$	I <sub>FM</sub>	120	А
Gate-emitter voltage Transient Gate-emitter Voltage (T <sub>pulse</sub> = 5 μs, D < 0.10)	$V_{GE}$	±20 ±25	V
Power Dissipation @ Tc = 25°C @ Tc = 100°C	P <sub>D</sub>	394 197	W
Operating junction temperature range	T <sub>J</sub>	-40 to +175	°C
Storage temperature range	T <sub>stg</sub>	-55 to +175	°C
Lead temperature for soldering, 1/8" from case for 5 seconds	T <sub>SLD</sub>	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.




## ON Semiconductor®

## www.onsemi.com

20 A, 1350 V V<sub>CEsat</sub> = 2.20 V E<sub>off</sub> = 0.60 mJ





## **MARKING DIAGRAM**



A = Assembly Location

Y = Year WW = Work Week G = Pb-Free Package

#### **ORDERING INFORMATION**

Device	Package	Shipping
NGTB20N135IHRWG	TO-247 (Pb-Free)	30 Units / Rail


## THERMAL CHARACTERISTICS


Rating	Symbol	Value	Unit
Thermal resistance junction-to-case	$R_{ heta JC}$	0.38	°C/W
Thermal resistance junction-to-ambient	$R_{ heta JA}$	40	°C/W

## **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = 25°C unless otherwise specified)

Parameter	Test Conditions	Symbol	Min	Тур	Max	Unit
STATIC CHARACTERISTIC				•	-	
Collector–emitter breakdown voltage, gate–emitter short–circuited	$V_{GE} = 0 \text{ V, I}_{C} = 5 \text{ mA}$	V <sub>(BR)CES</sub>	1350	_	_	V
Collector-emitter saturation voltage	V <sub>GE</sub> = 15 V, I <sub>C</sub> = 20 A V <sub>GE</sub> = 15 V, I <sub>C</sub> = 20 A, T <sub>J</sub> = 175°C	V <sub>CEsat</sub>	- -	2.20 2.40	2.65 -	V
Gate-emitter threshold voltage	$V_{GE} = V_{CE}, I_{C} = 250 \mu A$	V <sub>GE(th)</sub>	4.5	5.5	6.5	V
Collector–emitter cut–off current, gate– emitter short–circuited	V <sub>GE</sub> = 0 V, V <sub>CE</sub> = 1350 V V <sub>GE</sub> = 0 V, V <sub>CE</sub> = 1350 V, T <sub>J</sub> = 175°C	I <sub>CES</sub>	_ _	_ _	0.5 2.0	mA
Gate leakage current, collector–emitter short–circuited	V <sub>GE</sub> = 20 V, V <sub>CE</sub> = 0 V	I <sub>GES</sub>	-	_	100	nA
DYNAMIC CHARACTERISTIC		•		•		
Input capacitance	V <sub>CE</sub> = 20 V, V <sub>GE</sub> = 0 V, f = 1 MHz	C <sub>ies</sub>	_	5290	_	pF
Output capacitance		C <sub>oes</sub>	_	124	_	
Reverse transfer capacitance		C <sub>res</sub>	-	100	-	
Gate charge total		$Q_g$	-	234	-	nC
Gate to emitter charge	$V_{CE} = 600 \text{ V}, I_{C} = 20 \text{ A}, V_{GE} = 15 \text{ V}$	Q <sub>ge</sub>	-	39	-	
Gate to collector charge		Q <sub>gc</sub>	-	105	-	
SWITCHING CHARACTERISTIC, INDUCT	TVE LOAD					
Turn-off delay time	$T_{J} = 25^{\circ}C$ $V_{CC} = 600 \text{ V, } I_{C} = 20 \text{ A}$ $R_{g} = 10 \Omega$ $V_{GE} = 0 \text{ V/ } 15 \text{ V}$	t <sub>d(off)</sub>	_	245	_	ns
Fall time		t <sub>f</sub>	_	175	_	
Turn-off switching loss		E <sub>off</sub>	-	0.60	-	mJ
Turn-off delay time	T <sub>J</sub> = 150°C	t <sub>d(off)</sub>	_	270	_	ns
Fall time	$V_{CC} = 600 \text{ V}, I_{C} = 20 \text{ A}$ $R_{c} = 10 \Omega$	t <sub>f</sub>	_	290	_	
Turn-off switching loss	$R_g = 10 \Omega$ $V_{GE} = 0 \text{ V/ } 15 \text{V}$	E <sub>off</sub>	-	1.40	-	mJ
DIODE CHARACTERISTIC						
Forward voltage	V <sub>GE</sub> = 0 V, I <sub>F</sub> = 20 A V <sub>GE</sub> = 0 V, I <sub>F</sub> = 20 A, T <sub>J</sub> = 175°C	V <sub>F</sub>	_ _	1.80 2.70	2.10 -	V

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.






16 V<sub>GE</sub>, GATE-EMITTER VOLTAGE (V) 14 12 10 6  $V_{CE} = 600 \text{ V}$ V<sub>GE</sub> = 15 V I<sub>C</sub> = 20 A 0 0 50 100 150 200 250 Q<sub>G</sub>, GATE CHARGE (nC)

Figure 7. Diode Forward Characteristics

Figure 8. Typical Gate Charge







Figure 9. Switching Loss vs. Temperature

Figure 10. Switching Time vs. Temperature






Figure 11. Switching Loss vs. I<sub>C</sub>

Figure 12. Switching Time vs. I<sub>C</sub>




Figure 13. Switching Loss vs. Ra




Figure 15. Switching Loss vs. V<sub>CE</sub>




Figure 17. Safe Operating Area

Figure 18. Reverse Bias Safe Operating Area




Figure 19. Collector Current vs. Switching Frequency

Figure 20. Typical  $V_{(BR)CES}$  vs. Temperature




Figure 21. IGBT Transient Thermal Impedance




Figure 22. Test Circuit for Switching Characteristics




Figure 23. Definition of Turn On Waveform





Figure 24. Definition of Turn Off Waveform

#### PACKAGE DIMENSIONS

TO-247 CASE 340AL ISSUE D



#### NOTES

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- CONTROLLING DIMENSION: MILLIMETERS. SLOT REQUIRED, NOTCH MAY BE ROUNDED
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH.
  MOLD FLASH SHALL NOT EXCEED 0.13 PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREME OF THE PLASTIC BODY.
- LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY
- ØP SHALL HAVE A MAXIMUM DRAFT ANGLE OF 1.5° TO THE TOP OF THE PART WITH A MAXIMUM DIAMETER OF 3.91.
- DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED

	MILLIMETERS		
DIM	MIN	MAX	
Α	4.70	5.30	
A1	2.20	2.60	
b	1.07	1.33	
b2	1.65	2.35	
b4	2.60	3.40	
С	0.45	0.68	
D	20.80	21.34	
E	15.50	16.25	
E2	4.32	5.49	
е	5.45 BSC		
F	2.655		
L	19.80	20.80	
L1	3.81	4.32	
P	3.55	3.65	
Q	5.40	6.20	
S	6.15 BSC		

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Phone: 81–3–5817–1050