2 A, 20 V Schottky Barrier Diode

These Schottky barrier diodes are optimized for low forward voltage drop and low leakage current and are offered in a Chip Scale Package (CSP) to reduce board space. The low thermal resistance enables designers to meet the challenging task of achieving higher efficiency and meeting reduced space requirements.

Features

- Low Forward Voltage Drop 450 mV (Typ.) @ $I_F = 2 A$
- Low Reverse Current $40 \ \mu A$ (Typ.) @ V_R = $20 \ V$
- 2 A of Continuous Forward Current
- ESD Rating Human Body Model: Class 3B
 - Machine Model: Class C
- High Switching Speed
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- LCD and Keypad Backlighting
- Camera Photo Flash
- Buck and Boost dc-dc Converters
- Reverse Voltage and Current Protection
- Clamping & Protection

MAXIMUM RATINGS


I	Rating	Symbol	Value	Unit
Reverse Voltage		V _R	20	V
Forward Current (DC)		١ _F	2	А
Forward Surge Cu	I _{FSM}	19	A	
Repetitive Peak Forward Current (Pulse Wave = 1 sec, Duty Cycle = 66%)		I _{FRM}	3.6	A
ESD Rating:	Human Body Model Machine Model	ESD	> 8 > 400	kV V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



ON Semiconductor®

www.onsemi.com



6E = Specific Device Code M = Date Code

PIN CONNECTIONS

1 0 2 CATHODE ANODE

ORDERING INFORMATION

Device	Package	Shipping [†]
NSR20206NXT5G	DSN2 (Pb–Free)	5000 / Tape & Reel


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Min	Тур	Max	Unit
Thermal Resistance Junction–to–Ambient (Note 1) Total Power Dissipation @ $T_A = 25^{\circ}C$	R _{θJA} P _D			245 510	°C/W mW
Thermal Resistance Junction–to–Ambient (Note 2) Total Power Dissipation @ $T_A = 25^{\circ}C$	R _{θJA} P _D			90 1.4	°C/W W
Storage Temperature Range	T _{stg}			-40 to +125	°C
Junction Temperature	TJ			+150	°C

1. Mounted onto a 4 in square FR-4 board 50 mm sq. 1 oz. Cu 0.06" thick single sided. Operating to steady state.

2. Mounted onto a 4 in square FR-4 board 650 mm sq. 1 oz. Cu 0.06" thick single sided. Operating to steady state.









Figure 2. Thermal Response (Note 2)

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
Reverse Leakage $(V_R = 10 V)$ $(V_R = 20 V)$	I _R		10 40	30 150	μΑ
Forward Voltage $(I_F = 10 \text{ mA})$ $(I_F = 100 \text{ mA})$ $(I_F = 500 \text{ mA})$ $(I_F = 1 \text{ A})$ $(I_F = 2 \text{ A})$	VF	- - - - -	250 310 360 390 450	290 350 400 430 490	mV
Total Capacitance ($V_R = 2.0 \text{ V}, f = 1.0 \text{ MHz}$)	CT	-	140	-	pF
Reverse Recovery Time ($I_F = I_R = 10 \text{ mA}, I_{R(REC)} = 1.0 \text{ mA}, Figure 3$)	t _{rr}	-	75	-	ns
Peak Forward Recovery Voltage ($I_F = 100 \text{ mA}, t_r = 20 \text{ ns}, \text{ Figure 4}$)	V _{FRM}	-	430	-	mV

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.












Figure 4. Peak Forward Recover Voltage Definition

TYPICAL CHARACTERISTICS







DOCUMENT NUMBER:	98AON79729F	Electronic versions are uncontrolled except when accessed directly from the Document Reposito Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION: DSN2, 1.6X0.8, 1.2P, (0603)		PAGE 1 OF 1			
ON Semiconductor and unarrest and the semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.					

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>