Onsemi

MOSFET - Power, Single **N-Channel, TOLL 100 V, 1.8 mΩ, 272 A**

NTBLS1D7N10MC

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- Lowers Switching Noise/EMI
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit	
Drain-to-Source Voltage			V _{DSS}	100	V	
Gate-to-Source Voltage			V _{GS}	±20	V	
Continuous Drain		$T_C = 25^{\circ}C$	I _D	272	А	
Current $R_{\theta JC}$ (Notes 1, 3)	Steady	T _C = 100°C		192		
Power Dissipation	State	$T_{C} = 25^{\circ}C$	PD	295	W	
$R_{\theta JC}$ (Note 1)		T _C = 100°C		147		
Continuous Drain Current R _{0.IA}		$T_A = 25^{\circ}C$	Ι _D	29	А	
(Notes 1, 2, 3)	Steady	T _A = 100°C		20		
Power Dissipation	State	$T_A = 25^{\circ}C$	PD	3.4	W	
$R_{\theta JA}$ (Notes 1, 2)		$T_A = 100^{\circ}C$		1.7		
Pulsed Drain Current	T _A = 25	°C, t _p = 10 μs	I _{DM}	2137	А	
Operating Junction and Storage Temperature Range			T _J , T _{stg}	–55 to +175	°C	
Source Current (Body Diode)			۱ _S	226	А	
Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = 97 A)			E _{AS}	606	mJ	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS


Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	0.51	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	43	

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.

3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
100 V	1.8 m Ω @ 10 V	272 A




N-CHANNEL MOSFET



CASE 100CU

MARKING DIAGRAM



WW = Work Week ZZ = Lot Traceability

1D7N10MC = Specific Device Code

ORDERING INFORMATION


See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I_D = 250 μ A		100			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J				60		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V, T_{J} = 25 °C$				10	۵
		V _{DS} = 100 V	T _J = 125°C			100	μA
Gate-to-Source Leakage Current	I _{GSS}	$V_{DS} = 0 V, V_{GS} = 20 V$				100	nA
ON CHARACTERISTICS (Note 4)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D =$	698 μA	2.0		4.0	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J				-10.5		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 80 A		1.5	1.8	mΩ
Forward Transconductance	9 _{FS}	V _{DS} = 10 V, I _D = 80 A			220		S
CHARGES AND CAPACITANCES							
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 50 V			9200		pF
Output Capacitance	C _{OSS}				4600		
Reverse Transfer Capacitance	C _{RSS}				79		
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 10 V, V _{DS} = 50 V; I _D = 80 A			115		nC
Threshold Gate Charge	Q _{G(TH)}				24		
Gate-to-Source Charge	Q _{GS}				47		
Gate-to-Drain Charge	Q _{GD}				16		
Plateau Voltage	V _{GP}				5		V
SWITCHING CHARACTERISTICS (Note 5)						
Turn-On Delay Time	t _{d(ON)}				48		
Rise Time	t _r	V_{GS} = 10 V, V_{DS} = 50 V, I_{D} = 80 A, R_{G} = 6 Ω			38		- ns
Turn-Off Delay Time	t _{d(OFF)}				76		
Fall Time	t _f				31		
DRAIN-SOURCE DIODE CHARACTERIS	TICS						
Forward Diode Voltage	V _{SD}	V _{GS} = 0 V,	$T_J = 25^{\circ}C$		0.82	1.3	v
	I _S = 80 Å		T _J = 125°C		0.70		
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dIS/dt = 100 A/µs, I _S = 62 A			98		ns
Reverse Recovery Charge	Q _{RR}				160		nC
Charge Time	t _a				47		ns
Discharge Time	t _b				52		ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 4. Pulse Test: pulse width $\leq 300 \ \mu$ s, duty cycle $\leq 2\%$. 5. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS





Figure 13. Transient Thermal Impedance

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NTBLS1D7N10MCTXG	1D7N10MC	H–PSOF8L (Pb–Free)	2000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not onvey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative