

PNP Transistor, 100 V, 3.0 A, Low V_{CE(sat)}

NSS1C300ET4G

onsemi's e²PowerEdge family of low $V_{CE(sat)}$ transistors are surface mount devices featuring ultra low saturation voltage ($V_{CE(sat)}$) and high current gain capability. These are designed for use in low voltage, high speed switching applications where affordable efficient energy control is important.

Typical applications are DC–DC converters and power management in portable and battery powered products such as cellular and cordless phones, PDAs, computers, printers, digital cameras and MP3 players. Other applications are low voltage motor controls in mass storage products such as disc drives and tape drives. In the automotive industry they can be used in air bag deployment and in the instrument cluster. The high current gain allows e²PowerEdge devices to be driven directly from PMU's control outputs, and the Linear Gain (Beta) makes them ideal components in analog amplifiers.

Features

- Complement to NSS1C301ET4G
- NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant


MAXIMUM RATINGS $(T_A = 25^{\circ}C)$

Rating	Symbol	Max	Unit
Collector-Base Voltage	V_{CBO}	140	Vdc
Collector-Emitter Voltage	V_{CEO}	100	Vdc
Emitter-Base Voltage	V _{EB}	6.0	Vdc
Collector Current - Continuous	Ic	3.0	Adc
Collector Current - Peak	I _{CM}	6.0	Adc
Base Current	Ι _Β	0.5	Adc
Total Power Dissipation @ T _C = 25°C Derate above 25°C	P _D	33 0.26	W W/°C
Total Power Dissipation (Note 1) @ T _A = 25°C Derate above 25°C	P _D	2.1 0.017	W W/°C
Operating and Storage Junction Temperature Range	T _J , T _{stg}	-65 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1

100 VOLTS, 3.0 AMPS PNP LOW $V_{CE(sat)}$ TRANSISTOR





DPAK CASE 369C STYLE 1

MARKING DIAGRAM



Y = Year WW = Work Week 1C30E = Device Code G = Pb-Free

ORDERING INFORMATION

Device	Package	Shipping [†]
NSS1C300ET4G	DPAK (Pb-Free)	2500/ Tape & Reel
NSV1C300ET4G	DPAK (Pb-Free)	2500/ Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

These ratings are applicable when surface mounted on the minimum pad sizes recommended.

THERMAL CHARACTERISTICS

Characteristic		Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	3.8	°C/W
Thermal Resistance, Junction-to-Ambient (Note 2)	$R_{\theta JA}$	59.5	°C/W

^{2.} These ratings are applicable when surface mounted on the minimum pad sizes recommended.

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS			•		
Collector – Emitter Breakdown Voltage (I _C = -10 mAdc, I _B = 0)	V _{(BR)CEO}	-100	-	-	Vdc
Collector – Base Breakdown Voltage (I _C = -0.1 mAdc, I _E = 0)	V _{(BR)CBO}	-140	-	-	Vdc
Emitter – Base Breakdown Voltage (I _E = -0.1 mAdc, I _C = 0)	V _{(BR)EBO}	-6.0	-	-	Vdc
Collector Cutoff Current (V _{CB} = -140 Vdc, I _E = 0)	I _{CBO}	-	-	-0.1	μAdc
Emitter Cutoff Current (V _{EB} = -6.0 Vdc)	I _{EBO}	-	-	-0.1	μAdc
ON CHARACTERISTICS					
DC Current Gain (Note 3) $ \begin{aligned} &(I_C = -0.1 \text{ A, } V_{CE} = -2.0 \text{ V}) \\ &(I_C = -0.5 \text{ A, } V_{CE} = -2.0 \text{ V}) \\ &(I_C = -1.0 \text{ A, } V_{CE} = -2.0 \text{ V}) \\ &(I_C = -3.0 \text{ A, } V_{CE} = -2.0 \text{ V}) \end{aligned} $	h _{FE}	180 180 120 50	- - - -	- - 360 -	-
Collector – Emitter Saturation Voltage (Note 3) $ \begin{pmatrix} I_C = -0.1 \text{ A, } I_B = -10 \text{ mA} \end{pmatrix} $ $ \begin{pmatrix} I_C = -1.0 \text{ A, } I_B = -0.100 \text{ A} \end{pmatrix} $ $ \begin{pmatrix} I_C = -2.0 \text{ A, } I_B = -0.200 \text{ A} \end{pmatrix} $ $ \begin{pmatrix} I_C = -3.0 \text{ A, } I_B = -0.300 \text{ A} \end{pmatrix} $	V _{CE(sat)}	- - - -	- - -	-0.070 -0.150 -0.250 -0.400	V
Base – Emitter Saturation Voltage (Note 3) $(I_C = -1.0 \text{ A}, I_B = -0.1 \text{ A})$	V _{BE(sat)}	-	-	-1.0	V
Base – Emitter Turn–on Voltage (Note 3) (I _C = –1.0 A, V _{CE} = –2.0 V)	V _{BE(on)}	-	-	-0.900	V
Cutoff Frequency ($I_C = -500 \text{ mA}$, $V_{CE} = -10 \text{ V}$, $f = 100 \text{ MHz}$)	f _T	_	100	-	MHz
Input Capacitance (V _{EB} = 5.0 V, f = 1.0 MHz)	Cibo	-	360	-	pF
Output Capacitance (V _{CB} = 10 V, f = 1.0 MHz)	Cobo	-	60	-	pF

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 2. Pulsed Condition: Pulse Width = 300 μ s, Duty Cycle \leq 2%.

TYPICAL CHARACTERISTICS




Figure 1. DC Current Gain

Figure 2. DC Current Gain




Figure 3. Collector-Emitter Saturation Voltage

Figure 4. Collector-Emitter Saturation Voltage




Figure 5. Base-Emitter Saturation Voltage

Figure 6. Base-Emitter Saturation Voltage

TYPICAL CHARACTERISTICS




Figure 7. Base-Emitter On Voltage

Figure 8. Collector Saturation Region




Figure 9. Capacitance

Figure 10. Current-Gain-Bandwidth Product




Figure 11. Safe Operating Area

TYPICAL CHARACTERISTICS





Figure 12. Typical Transient Thermal Response, Junction-to-Case





DOCUMENT NUMBER:	98AON10527D	Electronic versions are uncontrolled except when accessed directly from the Document Repository Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	DPAK (SINGLE GAUGE)		PAGE 1 OF 1	

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales