# onsemi

# **MOSFET** - Power, Single N-Channel, STD Gate, SO8FL

# 80 V, 3 mΩ, 135 A NTMFS3D5N08X

#### Features

- Low Q<sub>RR</sub>, Soft Recovery Body Diode
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Q<sub>G</sub> and Capacitance to Minimize Driver Losses
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

#### **Typical Applications**

- Synchronous Rectification (SR) in DC-DC and AC-DC
- Primary Switch in Isolated DC-DC Converter
- Motor Drives


#### **MAXIMUM RATINGS** (T<sub>J</sub> = $25^{\circ}$ C unless otherwise stated)


Parameter	Symbol	Value	Unit	
Drain-to-Source Voltage		V <sub>DSS</sub>	80	V
Gate-to-Source Voltage		V <sub>GS</sub>	±20	V
Continuous Drain Current	$T_{C} = 25^{\circ}C$	Ι <sub>D</sub>	135	А
(Note 1)	$T_{\rm C} = 100^{\circ}{\rm C}$		96	
Power Dissipation (Note 1)	$T_C = 25^{\circ}C$	PD	119	W
Pulsed Drain Current	T <sub>C</sub> = 25°C,	I <sub>DM</sub>	543	А
Pulsed Source Current (Body Diode)	t <sub>p</sub> = 100 μs	I <sub>SM</sub>	543	
Operating Junction and Storage Range	T <sub>J</sub> , T <sub>STG</sub>	–55 to +175	°C	
Source Current (Body Diode)	I <sub>S</sub>	179	А	
Single Pulse Avalanche Energy (I <sub>PK</sub> = 47 A) (Note 3)	E <sub>AS</sub>	110	mJ	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- Actual continuous current will be limited by thermal & electromechanical application board design.
  Eve of 110 m Lis based on started Tv = 25°C Lis = 47 A V/c = 64 V/c
- 3.  $\vec{E}_{AS}$  of 110 mJ is based on started T<sub>J</sub> = 25°C, I<sub>AS</sub> = 47 A, V<sub>DD</sub> = 64 V, V<sub>GS</sub> = 10 V, 100% avalanche tested

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
80 V	$3~\mathrm{m}\Omega~@~10~\mathrm{V}$	135 A





## ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 3 of this data sheet.

#### THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	1.26	°C/W
Thermal Resistance, Junction-to-Ambient (Notes 4 and 5)	$R_{\thetaJA}$	39	

Surface-mounted on FR4 board using 1 in<sup>2</sup> pad size, 1 oz. Cu pad.
 R<sub>thJA</sub> is determined by the user's board design.

# **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = $25^{\circ}$ C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Тур	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS}$ = 0 V, $I_D$ = 1 mA	80			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	${\Delta V_{(BR)DSS}}/{\Delta T_J}$	$I_D$ = 1 mA. Referenced to 25°C		31.6		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{DS}$ = 80 V, $T_{J}$ = 25°C	1		1	μA
		V <sub>DS</sub> = 80 V, T <sub>J</sub> = 125°C			250	
Gate-to-Source Leakage Current	I <sub>GSS</sub>	$V_{DS} = 0 V, V_{GS} = 20 V$			100	nA
ON CHARACTERISTICS						
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	$V_{GS}$ = 10 V, I <sub>D</sub> = 31 A		2.6	3	mΩ
		$V_{GS}$ = 6 V, $I_{D}$ = 15 A		4.0	5.8	
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS}$ = $V_{DS}$ , $I_D$ = 153 $\mu$ A	2.4		3.6	V
Gate Threshold Voltage Temperature Coefficient	${\Delta V_{GS(TH)} / \over \Delta T_J}$	$V_{GS}$ = $V_{DS}$ , $I_D$ = 153 $\mu$ A		-7.5		mV/°C
Forward Transconductance	9FS	V <sub>DS</sub> = 5 V, I <sub>D</sub> = 31 A		97		S
CHARGES, CAPACITANCES & GATE RE	SISTANCE					
Input Capacitance	C <sub>ISS</sub>			2680		pF
Output Capacitance	C <sub>OSS</sub>			780		
Reverse Transfer Capacitance	C <sub>RSS</sub>	V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 40 V, f = 1 MHz		12		
Output Charge	Q <sub>OSS</sub>			56		nC
Total Gate Charge	Q <sub>G(TOT)</sub>	$V_{GS}$ = 6 V, $V_{DD}$ = 40 V; $I_D$ = 31 A		23		
				38		
Threshold Gate Charge	Q <sub>G(TH)</sub>			8		
Gate-to-Source Charge	Q <sub>GS</sub>	$V_{GS}$ = 10 V, $V_{DD}$ = 40 V; $I_{D}$ = 31 A		13		
Gate-to-Drain Charge	Q <sub>GD</sub>			6		
Gate Plateau Voltage	V <sub>GP</sub>			4.7		V
Gate Resistance	R <sub>G</sub>	f = 1 MHz		0.7		Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	t <sub>d(ON)</sub>			23		ns
Rise Time	t <sub>r</sub>	Resistive Load,		7		]
Turn-Off Delay Time	t <sub>d(OFF)</sub>	$V_{GS}$ = 0/10 V, $V_{DD}$ = 40 V, $I_{D}$ = 31 A, $R_{G}$ = 2.5 $\Omega$		32		]
Fall Time	t <sub>f</sub>			5		<u> </u>
SOURCE-TO-DRAIN DIODE CHARACTE	RISTICS					
Forward Diode Voltage	$V_{SD}$	$V_{GS}$ = 0 V, I <sub>S</sub> = 31 A, T <sub>J</sub> = 25°C		0.82	1.2	V
		$V_{GS}$ = 0 V, I <sub>S</sub> = 31 A, T <sub>J</sub> = 125°C		0.66		1

#### **ELECTRICAL CHARACTERISTICS** ( $T_J = 25^{\circ}C$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Тур	Мах	Unit	
SOURCE-TO-DRAIN DIODE CHARACTERISTICS							
Reverse Recovery Time	t <sub>RR</sub>			22		ns	
Charge Time	t <sub>a</sub>	V <sub>GS</sub> = 0 V, dl/dt = 1000 A/μs,		12			
Discharge Time	t <sub>b</sub>			10			
Reverse Recovery Charge	Q <sub>RR</sub>			144		nC	


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

#### **DEVICE ORDERING INFORMATION**

Device	Marking	Package	Shipping <sup>†</sup>
NTMFS3D5N08XT1G	3D5N08	DFN5 (Pb–Free)	1500 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## **TYPICAL CHARACTERISTICS**






Figure 3. On-Resistance vs. Gate Voltage





Figure 5. Normalized ON Resistance vs. Junction Temperature











Figure 4. On-Resistance vs. Drain Current





# **TYPICAL CHARACTERISTICS**











Figure 9. Resistive Switching Time Variation vs. Gate Resistance










Figure 10. Diode Forward Characteristics




Figure 12. Avalanche Current vs Pulse Time (UIS)

# **TYPICAL CHARACTERISTICS**





Figure 15. Transient Thermal Response

#### PACKAGE DIMENSIONS



\*For additional information on our Pb–Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent\_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages,

#### ADDITIONAL INFORMATION

#### TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales