ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

Power MOSFET

30 V, 19 A, Single N–Channel, SOIC–8 FL Features

- Fast Switching Times
- Low Gate Charge
- Low R_{DS(on)}
- Low Inductance SOIC-8 Package
- These are Pb-Free Devices

Applications

- Notebooks, Graphics Cards
- DC-DC Converters
- Synchronous Rectification

MAXIMUM RATINGS ($T_J = 25^{\circ}C$ unless otherwise stated)

Parame	Symbol	Value	Unit		
Drain-to-Source Voltage			V _{DSS}	30	V
Gate-to-Source Voltage			V _{GS}	±20	V
Continuous Drain Current	Steady	$T_A = 25^{\circ}C$	I _D	11.5	А
(Note 1)	State	$T_A = 85^{\circ}C$		8.0	
	$t \le 10 s$	$T_A = 25^{\circ}C$		19	
Power Dissipation (Note 1)	Steady State	T _A = 25°C	PD	2.2	W
	t ≤ 10 s			6.25	
Continuous Drain Current		$T_A = 25^{\circ}C$	۱ _D	7.8	А
(Note 2)	Steady	$T_A = 85^{\circ}C$		5.6	
Power Dissipation (Note 2)	State	$T_A = 25^{\circ}C$	P _D	1.0	W
Pulsed Drain Current	t _p ≤	10 μs	I _{DM}	58	А
Operating Junction and Storage Temperature			T _J , T _{STG}	-55 to 150	°C
Source Current (Body Diode)			۱ _S	6.25	А
Single Pulse Drain-to-Source Avalanche Energy. V _{DD} = 25 V, V _{GS} = 10 V, I _{PK} = 7.0 A, L = 10 mH, R _G = 25 Ω			E _{AS}	245	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Ambient - Steady State (Note 1)	R_{\thetaJA}	56.5	°C/W
Junction-to-Ambient – t \leq 10 s (Note 1)	$R_{\theta JA}$	20	
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	124	

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Surface-mounted on FR4 board using 1 in sq pad size

(Cu area = 1.127 in sq [1 oz] including traces).


 Surface-mounted on FR4 board using the minimum recommended pad size (Cu area = 0.412 in sq).



ON Semiconductor®

http://onsemi.com

V _{(BR)DSS}	R _{DS(on)} Typ	I _D Max
30 V	7.3 mΩ @ 10 V	19 A
30 V	10.1 mΩ @ 4.5 V	107



·

ORDERING INFORMATION


Device	Package	Shipping [†]
NTMFS4708NT1G	SOIC-8 FL (Pb-Free)	1500 / āpe & Reel
NTMFS4708NT3G	SOIC-8 FL (Pb-Free)	5000 / āpe & Reel


†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise specified)

Parameter	Symbol	Test Condition	on	Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I _D = 250 µA		30			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J				10		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}		$T_J = 25^{\circ}C$			1.0	μΑ
		V_{GS} = 0 V, V_{DS} = 24 V	T _J = 125°C			50	
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS} =	±20V			±100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D = 2$	250 μA	1.0		2.5	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J				5.0		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V_{GS} = 10 V, I _D =	11.5 A		7.3	10	mΩ
		V _{GS} = 4.5 V, I _D =	9.5 A		10.1	14	
Forward Transconductance	9 FS	V _{DS} = 15 V, I _D =	11.5 A		23		S
CHARGES, CAPACITANCES AND GA	ATE RESISTAI	NCE					
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1.0 MHz, V _{DS} = 24 V			970		pF
Output Capacitance	C _{OSS}				440		-
Reverse Transfer Capacitance	C _{RSS}				115		
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 4.5 V, V _{DS} = 15 V; I _D = 11.5 A			10	15	nC
Threshold Gate Charge	Q _{G(TH)}				1.3		1
Gate-to-Source Charge	Q _{GS}				2.6		
Gate-to-Drain Charge	Q _{GD}				4.8		
Gate Resistance	R _G				1.95		Ω
SWITCHING CHARACTERISTICS (No	ote 4)						
Turn-On Delay Time	t _{d(on)}				6.7		ns
Rise Time	t _r	Vcs = 10 V. Vod = 15 V	/. lo = 1.0 A.		4.3		1
Turn-Off Delay Time	t _{d(off)}	V_{GS} = 10 V, V_{DD} = 15 V, I_{D} = 1.0 A, $$R_{G}$$ = 3.0 Ω			20		
Fall Time	t _f				16		
DRAIN-SOURCE DIODE CHARACTE	RISTICS					•	
Forward Diode Voltage	V _{SD}	V _{GS} = 0 V, I _S = 6.25 A	$T_J = 25^{\circ}C$		0.78	1.0	V
			T _J = 125°C		0.60		
Reverse Recovery Time	t _{RR}	V_{GS} = 0 V, d_{IS}/d_t = 100 A/µs, I_S = 6.25 A			32		ns
Charge Time	ta				15.5		
Discharge Time	t _b				16.5	ļ	
Reverse Recovery Charge	Q _{RR}				24		nC


Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
Switching characteristics are independent of operating junction temperatures.





PACKAGE DIMENSIONS

DFN6 5x6, 1.27P (SO8 FL) CASE 488AA-01 ISSUE C



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and with a registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights not the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death agosciated with such unintended or unauthorized use even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

Phone: 421 33 790 2910

Phone: 81-3-5773-3850

Japan Customer Focus Center

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor PD. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative