ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

Power MOSFET 22 Amps, 60 Volts

N-Channel TO-220 and D²PAK

Designed for low voltage, high speed switching applications in power supplies, converters and power motor controls and bridge circuits.

Typical Applications

- Power Supplies
- Converters
- Power Motor Controls
- Bridge Circuits

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	60	Vdc
Drain-to-Gate Voltage (R _{GS} = 10 MΩ)	V_{DGR}	60	Vdc
Gate-to-Source Voltage - Continuous - Non-Repetitive (t _p ≤10 ms)	V _{GS} V _{GS}	±20 ±30	Vdc
Drain Current - Continuous @ T _A = 25°C - Continuous @ T _A = 100°C - Single Pulse (t _p ≤ 10 μs)	I _D I _D	22 10 66	Adc Apk
Total Power Dissipation @ T _A = 25°C Derate above 25°C	P _D	60 0.4	W/°C
Operating and Storage Temperature Range	T _J , T _{stg}	-55 to +175	ô
Single Pulse Drain-to-Source Avalanche Energy – Starting T_J = 25°C (V_{DD} = 50 Vdc, V_{GS} = 10 Vdc, L = 1.0 mH, V_{DS} = 60 Vdc, $I_{L(pk)}$ = 12 A, RG = 25 Ω)	EAS	72	ĘĴ
Thermal Resistance - Junction-to-Case - Junction-to-Ambient	R _{0JC} R _{0JA}	2.5 62.5	°C/W
Maximum Lead Temperature for Soldering Purposes, 1/8" from case for 10 seconds	TĹ	260	°C




ON Semiconductor™


http://onsemi.com

22 AMPERES 60 VOLTS

 $R_{DS(on)} = 60 \text{ m}\Omega$



MARKING DIAGRAMS & PIN ASSIGNMENTS



ORDERING INFORMATION

Device	Package	Shipping
NTP22N06	TO-220AB	50 Units/Rail
NTB22N06	D ² PAK	50 Units/Rail
NTB22N06T4	D ² PAK	800/Tape & Reel

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted)

Cr	Symbol	Min	Тур	Max	Unit		
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Vo (V _{GS} = 0 Vdc, I _D = 250 μAdc) Temperature Coefficient (Positiv	V _{(BR)DSS}	60 -	71 71	- -	Vdc mV/°C		
Zero Gate Voltage Drain Curren (V_{DS} = 60 Vdc, V_{GS} = 0 Vdc) (V_{DS} = 60 Vdc, V_{GS} = 0 Vdc,	I _{DSS}	- -		1.0 10	μAdc		
Gate-Body Leakage Current (V	_{GS} = ±20 Vdc, V _{DS} = 0 Vdc)	I _{GSS}	_	-	±100	nAdc	
ON CHARACTERISTICS (Note 1)						
Gate Threshold Voltage (Note 1 $(V_{DS} = V_{GS}, I_D = 250 \mu Adc)$ Threshold Temperature Coeffici	V _{GS(th)}	2.0	3.09 7.0	4.0 -	Vdc mV/°C		
Static Drain-to-Source On-Res (V _{GS} = 10 Vdc, I _D = 11 Adc)	R _{DS(on)}	-	52	60	mΩ		
Static Drain-to-Source On-Volt $(V_{GS} = 10 \text{ Vdc}, I_D = 22 \text{ Adc})$ $(V_{GS} = 10 \text{ Vdc}, I_D = 11 \text{ Adc}, T_D = 11 \text{ Adc})$	V _{DS(on)}	- 1	1.2 1.11	1.6	Vdc		
Forward Transconductance (No	g _{FS}	<i>.</i>	12	2-	mhos		
DYNAMIC CHARACTERISTICS			1	3 VC			
Input Capacitance		C _{iss}	60	502	700	pF	
Output Capacitance	$(V_{DS} = 25 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}, f = 1.0 \text{ MHz})$	Coss	-	160	225		
Transfer Capacitance		C_{rss}	_()	46	65		
SWITCHING CHARACTERISTIC	S (Note 2)	7,72	70				
Turn-On Delay Time		t _{d(on)}	-	12	25	ns	
Rise Time	(V _{DD} = 30 Vdc, I _D = 22 Adc,	t _r	-	39	80		
Turn-Off Delay Time	V_{GS} = 10 Vdc, R_G = 9.1 Ω) (Note 1)	t _{d(off)}	-	18	40		
Fall Time		t _f	-	34	70		
Gate Charge		Q _T	-	15.5	32	nC	
	$(V_{DS} = 48 \text{ Vdc}, I_D = 22 \text{ Adc}, V_{GS} = 10 \text{ Vdc})$ (Note 1)	Q ₁	_	3.4	-		
	igs to tall, (total	Q ₂	_	7.7	-		
SOURCE-DRAIN DIODE CHARACTERISTICS							
Forward On-Voltage	$(I_S = 22 \text{ Adc}, V_{GS} = 0 \text{ Vdc}) \text{ (Note 1)}$ $(I_S = 22 \text{ Adc}, V_{GS} = 0 \text{ Vdc}, T_J = 150^{\circ}\text{C})$	V _{SD}	- -	1.07 1.0	1.15 -	Vdc	
Reverse Recovery Time	2,8,	t _{rr}	_	43	İ	ns	
$(I_{S} = 22 \text{ Adc}, V_{GS} = 0 \text{ Vdc}, \\ dI_{S}/dt = 100 \text{ A/}\mu\text{s}) \text{ (Note 1)}$		ta	_	32	İ		
0	t _b	_	11	-			
Reverse Recovery Stored Char	Q_{RR}	_	0.071	-	μС		

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperatures.




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance versus
Gate-to-Source Voltage




Figure 4. On-Resistance versus Drain Current and Gate Voltage




Figure 5. On–Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current versus Voltage




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage versus Total Charge




Figure 9. Resistive Switching Time Variation versus Gate Resistance




Figure 10. Diode Forward Voltage versus Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Avalanche Energy versus Starting Junction Temperature






Figure 13. Thermal Response




PACKAGE DIMENSIONS

TO-220 THREE-LEAD TO-220AB

CASE 221A-09 **ISSUE AA**





- NOTES:


 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

 2. CONTROLLING DIMENSION: INCH.

 3. DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND LEAD IRREGULARITIES ARE ALLOWED.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.570	0.620	14.48	15.75
В	0.380	0.405	9.66	10.28
C	0.160	0.190	4.07	4.82
D	0.025	0.035	0.64	0.88
F	0.142	0.147	3.61	3.73
G	0.095	0.105	2.42	2.66
Н	0.110	0.155	2.80	3.93
J	0.018	0.025	0.46	0.64
K	0.500	0.562	12.70	14.27
L	0.045	0.060	1.15	1.52
N	0.190	0.210	4.83	5.33
Q	0.100	0.120	2.54	3.04
R	0.080	0.110	2.04	2.79
S	0.045	0.055	1.15	1.39
T	0.235	0.255	5.97	6.47
٥	0.000	0.050	0.00	1.27
V	0.045		1.15	
Z		0.080		2.04





- 11. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH.

	INC	HES	MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.340	0.380	8.64	9.65	
В	0.380	0.405	9.65	10.29	
C	0.160	0.190	4.06	4.83	
D	0.020	0.035	0.51	0.89	
Е	0.045	0.055	1.14	1.40	
G	0.100 BSC		2.54 BSC		
Н	0.080	0.110	2.03	2.79	
J	0.018	0.025	0.46	0.64	
K	0.090	0.110	2.29	2.79	
S	0.575	0.625	14.60	15.88	
V	0.045	0.055	1.14	1.40	

STYLE 2: PIN 1. GATE

- 2. DRAIN 3. SOURCE 4. DRAIN



ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice on semiconductor and are registered readerlands of semiconductor Components industries, Ite (SCILLC) . Solitude services are inject to make triangles without further holice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada

Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center

Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative