

MOSFET – Power, Single N-Channel

40 V, 7.3 mΩ, 52 A

NVMFS5C466NL

Features

- Small Footprint (5x6 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- NVMFS5C466NLWF Wettable Flank Option for Enhanced Optical Inspection
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	40	V
Gate-to-Source Voltage	9		V _{GS}	±20	V
Continuous Drain		T _C = 25°C	I _D	52	Α
Current R _{θJC} (Notes 1, 3)	Steady	T _C = 100°C		37	
Power Dissipation	State	T _C = 25°C	P _D	37	W
R _{θJC} (Note 1)		T _C = 100°C		19	
Continuous Drain		T _A = 25°C	I _D	16	Α
Current R _{θJA} (Notes 1, 2, 3)	Steady	T _A = 100°C		11	
Power Dissipation	State	T _A = 25°C	P_{D}	3.5	W
R _{θJA} (Notes 1 & 2)		T _A = 100°C	1	1.75	
Pulsed Drain Current	$T_A = 25$	°C, t _p = 10 μs	I _{DM}	238.6	Α
Operating Junction and Storage Temperature			T _J , T _{stg}	-55 to + 175	°C
Source Current (Body Diode)			Is	31.25	Α
Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = 2.93 A)			E _{AS}	65	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	4.0	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	43	

The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX	
40 V	7.3 m Ω @ 10 V	52 A	
	12 mΩ @ 4.5 V	52 A	



N-CHANNEL MOSFET






DFN5 5x6, 1.27P (SO-8FL) CASE 488AA

DFNW5 5x6 (FULL-CUT SO8FL WF) CASE 507BA

MARKING DIAGRAM



XXXXXX = 5C466NL

(NVMFS5C466NL) or

466LWF

(NVMFS5C466NLWF)

A = Assembly Location

= Year

W = Work Week

ZZ = Lot Traceability

ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 5 of this data sheet.

^{2.} Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.

3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.


ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condi	tion	Min	Тур	Max	Unit
OFF CHARACTERISTICS	•				•	•	•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0 \text{ V}, I_D =$	250 μΑ	40	-	-	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /			-	25	-	mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V,	T _J = 25 °C	-	-	10	
		$V_{DS} = 40 \text{ V}$	T _J = 125°C	-	-	250	μΑ
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS}	= 20 V	-	-	100	nA
ON CHARACTERISTICS (Note 4)					-		
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D$	= 30 μΑ	1.2	_	2.2	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J			-	-4.9	_	mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 4.5 V	I _D = 10 A	-	9.7	12	mΩ
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 10 A	-	6.1	7.3	mΩ
Forward Transconductance	9FS	V _{DS} =15 V, I _D	= 10 A	-	33	-	S
CHARGES, CAPACITANCES & GATE RESI	STANCE				•	•	•
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 25 V		-	860	_	
Output Capacitance	Coss			-	360	-	pF
Reverse Transfer Capacitance	C _{RSS}			-	15	-	
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 4.5 V, V _{DS} = 32 V; I _D = 10 A		_	7	_	nC
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 10 V, V _{DS} = 32 V; I _D = 10 A		_	16	_	nC
Threshold Gate Charge	Q _{G(TH)}			-	1.8	_	
Gate-to-Source Charge	Q_{GS}	V _{GS} = 10 V, V _{DS} = 32 V; I _D = 10 A		-	3.3	_	nC
Gate-to-Drain Charge	Q_{GD}			-	2.5	_	
Plateau Voltage	V_{GP}			-	3.4	_	V
SWITCHING CHARACTERISTICS (Note 5)					-		
Turn-On Delay Time	t _{d(ON)}			-	8	-	
Rise Time	t _r	V_{GS} = 10 V, V_{DS} = 32 V, I_{D} = 10 A, R_{G} = 1 Ω		-	24	-	
Turn-Off Delay Time	t _{d(OFF)}	$I_D = 10 \text{ A}, R_G$	= 1 Ω	-	29	-	ns
Fall Time	t _f			1	6	-	
DRAIN-SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage	V_{SD}	$V_{GS} = 0 \text{ V},$ $I_{S} = 10 \text{ A}$ $T_{J} = 25^{\circ}\text{C}$ $T_{J} = 125^{\circ}\text{C}$		-	0.84	1.2	.,
				-	0.71	_	V
Reverse Recovery Time	t _{RR}	$V_{GS} = 0 \text{ V, } dI_{S}/dt = 100 \text{ A/}\mu\text{s,}$ $I_{S} = 10 \text{ A}$		-	24	_	
Charge Time	t _a			-	11	_	ns
Discharge Time	t _b			-	12	_	
Reverse Recovery Charge	Q_{RR}			-	11	٧	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in Avalanche

TYPICAL CHARACTERISTICS




Figure 13. Thermal Response

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NVMFS5C466NLT1G	5C466L	DFN5 5x6, 1.27P (SO-8FL) (Pb-Free)	1500 / Tape & Reel
NVMFS5C466NLWFT1G	466LWF	DFNW5, 5x6 (FULL-CUT SO8FL WF) (Pb-Free, Wettable Flanks)	1500 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.





0.10

SIDE VIEW

DFN5 5x6, 1.27P (SO-8FL) CASE 488AA ISSUE N

DATE 25 JUN 2018

NOTES:

- DIMENSIONING AND TOLERANCING PER
- ASME Y14.5M, 1994. CONTROLLING DIMENSION: MILLIMETER. DIMENSION D1 AND E1 DO NOT INCLUDE
- MOLD FLASH PROTRUSIONS OR GATE BURRS

	MILLIMETERS			
DIM	MIN	NOM	MAX	
Α	0.90	1.00	1.10	
A1	0.00	-	0.05	
b	0.33	0.41	0.51	
С	0.23	0.28	0.33	
D	5.00	5.15	5.30	
D1	4.70	4.90	5.10	
D2	3.80	4.00	4.20	
E	6.00	6.15	6.30	
E1	5.70	5.90	6.10	
E2	3.45	3.65	3.85	
е	1.27 BSC			
G	0.51	0.575	0.71	
K	1.20	1.35	1.50	
L	0.51	0.575	0.71	
L1	0.125 REF			
M	3.00	3.40	3.80	
θ	0 °		12 °	

GENERIC MARKING DIAGRAM*



XXXXXX = Specific Device Code

= Lot Traceability

= Assembly Location Α

Υ = Year W = Work Week

ZZ

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ", may or may not be present. Some products may not follow the Generic Marking.





DETAIL A

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

Electronic versions are uncontrolled except when accessed directly from the Document Repository. **DOCUMENT NUMBER:** 98AON14036D Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. **DESCRIPTION:** DFN5 5x6, 1.27P (SO-8FL) **PAGE 1 OF 1**

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

IDENTIFIER





CASE 507BA **ISSUE A**



MILLIMETERS

N□M.

0.575

0.575

0.150 REF

1.35

MAX. 1.10 0.05 0.51

0.33

5.30 5.10

4.20

6.30 6.10

3.85

0.71


1.50

0.71



DIM

DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
CONTROLLING DIMENSION: MILLIMETERS
DIMENSIONS DI AND EI DO NOT INCLUDE MOLD FLASH,
PROTRUSIONS, OR GATE BURRS.
THIS PACKAGE CONTAINS WETTABLE FLANK DESIGN
FEATURES TO AID IN FILLET FORMATION ON THE LEADS DURING MOUNTING.




Α	0.90	1.00
A1	0.00	
b	0.33	0.41
С	0.23	0.28
D	5.00	5.15
D1	4.70	4.90
D2	3.80	4.00
Е	6.00	6.15
E1	5.70	5.90
E2	3.45	3.65
е		1.27 BSC

0.51

1.20

0.51

MIN



e/2


BOTTOM VIEW

-DETAIL B

DETAIL A

TOP VIEW





0.965

4X 1.00-

G

Κ

L1

GENERIC MARKING DIAGRAM*

PIN 5 (EXPOSED PAD)



= Assembly Location Α

Υ = Year W

ZZ

= Work Week = Lot Traceability

XXXXXX = Specific Device Code *This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " =", may or may not be present. Some products

may not follow the Generic Marking.

RECOMMENDED MOUNTING FOOTPRINT

For additional information on our Pb-Free strategy and soldering details, please download the $\square N$ Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	98AON26450H
DOGGINEITI ITOMBEITI	3070112040011

Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

4X 0.75

DESCRIPTION: DFNW5 5x6 (FULL-CUT SO8FL WF) **PAGE 1 OF 1**

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales