

# PNP General-Purpose Transistor, 60 V

#### **PN2907A**

#### Description

The PN2907A is 60 V PNP bipolar transistor designed for use as a general-purpose amplifier or switch in applications that require up to 500 mA. The NPN complementary type is the PN2222A.

#### **Features**

- High DC Current Gain (h<sub>FE</sub>) Range: 100 ~ 300
- High-Current Gain Bandwidth Product (f<sub>T</sub>): 200 MHz (Minimum)
- Maximum Turn-On Time (t<sub>on</sub>): 45 ns
- Maximum Turn-Off Time (t<sub>off</sub>): 100 ns
- This is a Pb-Free Device

## **ABSOLUTE MAXIMUM RATINGS** ( $T_A = 25$ °C unless otherwise noted) (Note 1, 2)

Symbol	Parameter	Value	Unit
V <sub>CEO</sub>	Collector-Emitter Voltage	-60	V
V <sub>CBO</sub> Collector–Base Voltage		-60	V
V <sub>EBO</sub>	Emitter-Base Voltage	-5.0	V
I <sub>C</sub>	I <sub>C</sub> Collector Current – Continuous		mA
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Junction Temperature Range	–55 to +150	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


- 1. These ratings are based on a maximum junction temperature of 150°C.
- These are steady-state limits. onsemi should be consulted on applications involving pulsed or low-duty cycle operations.

#### THERMAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise noted)

Symbol	Parameter	Max (Note 3)	Unit
P <sub>D</sub>	Total Device Dissipation	625	mW
	Derate Above 25°C	5.0	mW/°C
$R_{ heta JC}$	Thermal Resistance, Junction to Case	83.3	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	200	°C/W

3. PCB size: FR-4 76 x 114 x 1.57 mm $^3$  (3.0 inch x 4.5 inch x 0.062 inch) with minimum land pattern size.








TO-92 3 4.825x4.76 CASE 135AN

#### **MARKING DIAGRAM**



2907A = Specific Device Code A = Assembly Site Y = Year of Production WW = Work Week Number

#### **ORDERING INFORMATION**

See detailed ordering and shipping information on page 2 of this data sheet.

#### **PN2907A**

### **ELECTRICAL CHARACTERISTICS** ( $T_A = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Max	Unit
OFF CHAR	ACTERISTICS				
V <sub>(BR)CEO</sub>	Collector-Emitter Breakdown Voltage (Note 4)	$I_C = -10 \text{ mA}, I_B = 0$	-60	_	V
V <sub>(BR)CBO</sub>	Collector-Base Breakdown Voltage	$I_C = -10 \mu A, I_E = 0$	-60	_	V
V <sub>(BR)EBO</sub>	Emitter-Base Breakdown Voltage	$I_E = -10 \mu A, I_C = 0$	-5.0	_	V
I <sub>BL</sub>	Base Cut-Off Current	$V_{CE} = -30 \text{ V}, V_{EB} = -0.5 \text{ V}$	_	-50	nA
I <sub>CEX</sub>	Collector Cut-Off Current	$V_{CE} = -30 \text{ V}, V_{EB} = -0.5 \text{ V}$	-	-50	nA
I <sub>CBO</sub>	Collector Cut-Off Current	V <sub>CB</sub> = -50 V, I <sub>E</sub> = 0	-	-0.02	μΑ
		$V_{CB} = -50 \text{ V}, I_E = 0, T_A = 150^{\circ}\text{C}$	_	-20	
ON CHARA	CTERISTICS				
h <sub>FE</sub>	DC Current Gain	I <sub>C</sub> = -0.1 mA, V <sub>CE</sub> = -10 V	75	_	
		I <sub>C</sub> = -1.0 mA, V <sub>CE</sub> = -10 V	100	_	
		$I_C = -10 \text{ mA}, V_{CE} = -10 \text{ V}$	100	_	
		I <sub>C</sub> = -150 mA, V <sub>CE</sub> = -10 V (Note 4)	100	300	
		$I_C = -500 \text{ mA}, V_{CE} = -10 \text{ V (Note 4)}$	50	-	
V <sub>CE</sub> (sat)	Collector-Emitter Saturation Voltage (Note 4)	I <sub>C</sub> = -150 mA, I <sub>B</sub> = -15 mA	-	-0.4	V
		$I_C = -500 \text{ mA}, I_B = -50 \text{ mA}$	-	-1.6	
V <sub>BE</sub> (sat)	Base-Emitter Saturation Voltage	I <sub>C</sub> = -150 mA, I <sub>B</sub> = -15 mA (Note 4)	-	-1.3	V
		$I_C = -500 \text{ mA}, I_B = -50 \text{ mA}$	-	-2.6	
MALL SIG	NAL CHARACTERISTICS				
f <sub>T</sub>	Current Gain – Bandwidth Product	$I_C = -50 \text{ mA}, V_{CE} = -20 \text{ V}, f = 100 \text{ MHz}$	200	-	MHz
C <sub>ob</sub>	Output Capacitance	V <sub>CB</sub> = -10 V, I <sub>E</sub> = 0, f = 100 kHz	-	8.0	pF
C <sub>ib</sub>	Input Capacitance	$V_{EB} = -2.0 \text{ V}, I_{C} = 0, f = 100 \text{ kHz}$	-	30	pF
WITCHING	CHARACTERISTICS				
t <sub>on</sub>	Turn-On Time	$V_{CC} = -30 \text{ V, } I_{C} = -150 \text{ mA,}$	-	45	ns
t <sub>d</sub>	Delay Time	$I_{B1} = -15 \text{ mA}$	-	10	ns
t <sub>r</sub>	Rise Time	7	_	40	ns
t <sub>off</sub>	Turn-Off Time	V <sub>CC</sub> = -6.0 V, I <sub>C</sub> = -150 mA,	-	100	ns
ts	Storage Time	$I_{B1} = I_{B2} = -15 \text{ mA}$	_	80	ns
t <sub>f</sub>	Fall Time	7	_	30	ns

<sup>4.</sup> Pulse test: pulse width  $\leq 300~\mu s,$  duty cycle  $\leq 2.0\%.$ 

#### **ORDERING INFORMATION**

Part Number	Top Mark	Package	Shipping <sup>†</sup>
PN2907ABU	2907A	TO-92 3 4.825x4.76 (Pb-Free)	10000 Units / Bulk
PN2907ATF	TO-92 3 4.825x4.76		2000 / Tape & Reel
PN2907ATFR		LEADFORMER (Pb-Free)	
PN2907ATA			2000 Units / Fan-Fold
PN2907ATAR			

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, <u>BRD8011/D</u>.

#### PN2907A

#### TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. Typical Pulsed Current Gain vs. Collector Current




Figure 2. Collector – Emitter Saturation Voltage vs. Collector Current




Figure 3. Base-Emitter Saturation Voltage vs. Collector Current




Figure 4. Base-Emitter On Voltage vs. Collector Current




Figure 5. Collector Cut-Off Current vs. Ambient Temperature




Figure 6. Input and Output Capacitance vs. Reverse Voltage

#### PN2907A

#### TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 7. Switching Times vs. Collector Current




Figure 9. Rise Time vs. Collector and Turn-On Base Currents




Figure 8. Turn-On and Turn-Off Times vs. Collector Current




Figure 10. Power Dissipation vs. Ambient Temperature

#### TYPICAL PERFORMANCE CHARACTERISTICS (f = 1.0 kHz)




Figure 11. Common Emitter Characteristics




Figure 12. Common Emitter Characteristics






Figure 13. Common Emitter Characteristics

#### TO-92 3 4.825x4.76 CASE 135AN ISSUE O


**DATE 31 JUL 2016** 





NOTES: UNLESS OTHERWISE SPECIFIED

- DRAWING WITH REFERENCE TO JEDEC TO-92 RECOMMENDATIONS. A)
- ALL DIMENSIONS ARE IN MILLIMETERS.
  DRAWING CONFORMS TO ASME Y14.5M—2009.




DOCUMENT NUMBER:	98AON13880G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	TO-92 3 4.825X4.76		PAGE 1 OF 1


ON Semiconductor and III are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

#### TO-92 3 4.83x4.76 LEADFORMED

CASE 135AR ISSUE O


**DATE 30 SEP 2016** 





NOTES: UNLESS OTHERWISE SPECIFIED

- A) DRAWING WITH REFERENCE TO JEDEC TO-92 RECOMMENDATIONS.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DRAWING CONFORMS TO ASME Y14.5M-1994



DOCUMENT NUMBER:	98AON13879G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	TO-92 3 4.83X4.76 LEADFORMED		PAGE 1 OF 1

ON Semiconductor and at a trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

#### ADDITIONAL INFORMATION

**TECHNICAL PUBLICATIONS:** 

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales