# **Hyperfast Rectifier** 15 A, 600 V

## RHRG1560-F085

#### **Description**

The RHRG1560 F085 is an hyperfast diode with soft recovery characteristics (trr < 55ns). It has half the recovery time of ultrafast diode and is of silicon nitride passivated ion-implanted epitaxial planar construction.

This device is intended for use as a freewheeling/clamping diode and rectifier in a variety of automotive switching power supplies and other power switching automotive applications.

Its low stored charge and hyperfast soft recovery minimize ringing and electrical noise in many power switching circuits, thus reducing power loss in the switching transistors.

#### **Features**

- High Speed Switching ( $t_{rr} = 26 \text{ ns (Typ.)} @ I_F = 15 \text{ A}$ )
- Low Forward Voltage( $V_F = 1.86 \text{ V (Typ.)} @ I_F = 15 \text{ A}$ )
- Avalanche Energy Rated
- AEC-Q101 Qualified
- This Device is Pb-Free

#### **Applications**

- Switching Power Supply
- Power Switching Circuits
- Automotive and General Purpose

#### ABSOLUTE MAXIMUM RATINGS (T<sub>C</sub> = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Peak Repetitive Reverse Voltage	$V_{RRM}$	600	V
Working Peak Reverse Voltage	V <sub>RWM</sub>	600	V
DC Blocking Voltage	$V_{R}$	600	٧
Average Rectified Forward Current $(T_C = 25 ^{\circ}C)$	I <sub>F(AV)</sub>	15	Α
Non-repetitive Peak Surge Current (Halfwave 1 Phase 50 Hz)	I <sub>FSM</sub>	45	Α
Avalanche Energy (1 A, 40 mH)	E <sub>AVL</sub>	20	mJ
Operating Junction and Storage Temperature	T <sub>J,</sub> T <sub>STG</sub>	–55 to +175	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



## ON Semiconductor®


www.onsemi.com



#### MARKING DIAGRAM



\$Y	= ON Semiconductor Logo
&Z	= Assembly Plant Code
&3	= Numeric Date Code
&K	= Lot Code
RHRG1560	= Specific Device Code



### **ORDERING INFORMATION**

See detailed ordering and shipping information on page 2 of this data sheet.

## **THERMAL CHARACTERISTICS** ( $T_C = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	Max	Units
$R_{ heta JC}$	Maximum Thermal Resistance, Junction to Case	1	°C/W
$R_{\theta JA}$	Maximum Thermal Resistance, Junction to Ambient	45	°C/W

#### PACKAGE MARKING AND ORDERING INFORMATION

Device Marking	Device	Package	Tube	Quantity
RHRG1560	RHRG1560-F085	TO-247	-	30

## **ELECTRICAL CHARACTERISTICS** (T<sub>C</sub> = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions		Min.	Тур.	Max.	Unit
I <sub>R</sub>	Instantaneous Reverse Current	V <sub>R</sub> = 600 V	T <sub>C</sub> = 25°C	-	_	100	uA
			T <sub>C</sub> = 175°C	-	_	1000	uA
V <sub>FM</sub>	Instantaneous Forward Voltage	I <sub>F</sub> = 15 A	T <sub>C</sub> = 25°C	-	1.86	2.3	V
(Note 1)			T <sub>C</sub> = 175°C	-	1.28	1.6	٧
t <sub>rr</sub> (Note 2)	Reverse Recovery Time	$I_F = 1 \text{ A},$ $di/dt = 100 \text{ A/}\mu\text{s},$ $V_{CC} = 390 \text{ V}$	T <sub>C</sub> = 25°C	-	25	50	ns
		I <sub>F</sub> = 15 A, di/dt = 100 A/μs,	T <sub>C</sub> = 25°C	-	26	55	ns
		$V_{CC} = 390 \text{ V}$	T <sub>C</sub> = 175°C	-	137	-	ns
ta tb Q <sub>rr</sub>	Reverse Recovery Time Reverse Recovery Charge	I <sub>F</sub> = 15 A, di/dt = 100 A/μs, V <sub>CC</sub> = 390 V	T <sub>C</sub> = 25°C	-	15 11 21	- - -	ns ns nC

 Pulse: Test Pulse width = 300 μs, Duty Cycle = 2%
 Guaranteed by design
 Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

## **TEST CIRCUITS AND WAVEFORMS**




Figure 1. T<sub>rr</sub> Test Circuit




Figure 2. T<sub>rr</sub> Waveforms and Definitions




Figure 3. Avalanche Energy Test Circuit




Figure 4. Avalanche Current and Voltage Waveforms

#### TYPICAL PERFORMANCE CHARECTERISTICS




Figure 5. Typical Forward Voltage Drop vs. Forward Current




Figure 7. Typical Junction Capacitance




Figure 9. Typical Reverse Recovery Current vs. di/dt




Figure 6. Typical Reverse Current vs. Reverse Voltage




Figure 8. Typical Reverse Recovery Time vs. di/dt




Figure 10. Forward Current Derating Curve

## TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 11. Reverse Recovery Charge





Figure 12. Transient Thermal Response Curve


#### TO-247-2LD CASE 340CL **ISSUE A**





- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DRAWING CONFORMS TO ASME Y14.5 2009.
  D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
- E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

#### **GENERIC MARKING DIAGRAM\***



XXXX = Specific Device Code

= Assembly Location

= Year

WW = Work Week

= Assembly Lot Code

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

	DATE 03 E	
Ø P —		Ø P1 D2
E1 —	1	D1
,		9

DIM	MILLIMETERS			
	MIN	NOM	MAX	
Α	4.58	4.70	4.82	
A1	2.29	2.40	2.66	
A2	1.30	1.50	1.70	
b	1.17	1.26	1.35	
b2	1.53	1.65	1.77	
С	0.51	0.61	0.71	
D	20.32	20.57	20.82	
D1	16.37	16.57	16.77	
D2	0.51	0.93	1.35	
Е	15.37	15.62	15.87	
E1	12.81	~	~	
E2	4.96	5.08	5.20	
е	~	11.12	~	
L	15.75	16.00	16.25	
L1	3.69	3.81	3.93	
ØΡ	3.51	3.58	3.65	
Ø <b>P</b> 1	6.61	6.73	6.85	
Q	5.34	5.46	5.58	
S	5.34	5.46	5.58	

DOCUMENT NUMBER:	98AON13850G	Electronic versions are uncontrolled except when accessed directly from the Document Reposito Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	TO-247-2LD		PAGE 1 OF 1	

ON Semiconductor and un are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

#### ADDITIONAL INFORMATION

**TECHNICAL PUBLICATIONS:** 

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales