ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

RHRD660S9A-F085



Data Sheet

May 2013

6A, 600V Hyperfast Diodes

The RHRD660S9A-F085 is hyperfast diodes with soft recovery characteristics (t_{rr} < 30ns). It has half the recovery time of ultrafast diodes and are silicon nitride passivated ion-implanted epitaxial planar construction.

This device is intended for use as freewheeling/ clamping diodes and rectifiers in a variety of switching power supplies and other power switching applications. Its low stored charge and hyperfast soft recovery minimize ringing and electrical noise in many power switching circuits reducing power loss in the switching transistors.

Formerly developmental type TA49057.



Features

- Hyperfast with Soft Recovery......

- · Avalanche Energy Rated
- Planar Construction •
- Qualified to AEC Q101
- RoHS Compliant

Applications

- · Switching Power Supplies
- · Power Switching Circuits
- General Purpose

Ordering Information

PART NUMBER	PACKAGE	BRAND
RHRD660S9A-F085	TO-252	RHR660

Symbol



Packaging



Absolute Maximum Ratings T_C = 25°C, Unless Otherwise Specified

	RHRD660S9A-F085	UNITS
Peak Repetitive Reverse Voltage	600	V
Working Peak Reverse Voltage	600	V
DC Blocking Voltage	600	V
Average Rectified Forward Current	6	А
Repetitive Peak Surge Current I _{FRM} (Square Wave, 20kHz)	12	А
Nonrepetitive Peak Surge Current I _{FSM} (Halfwave, 1 Phase, 60Hz)	60	A
Maximum Power Dissipation	50	W
Avalanche Energy (See Figures 10 and 11) EAVL	10	mJ
Operating and Storage Temperature	-55 to 175	°C
Maximum Lead Temperature for Soldering		
(Leads at 0.063 in. (1.6mm) from case for 10s)	300	°C
Package Body for 10s, see Tech Brief 334TPKG	260	°C

SYMBOL	TEST CONDITION	MIN	ТҮР	MAX	UNITS
V _F	I _F = 6A	-	-	2.1	V
	I _F = 6A, T _C = 150 ^o C	-	-	1.7	V
I _R	V _R = 600V	-	-	100	μΑ
	V _R = 600V, T _C = 150 ^o C	-	-	500	μΑ
t _{rr}	I _F = 1A, dI _F /dt = 200A/μs	-	-	30	ns
	$I_F = 6A$, $dI_F/dt = 200A/\mu s$	-	-	35	ns
t _a	I _F = 6A, dI _F /dt = 200A/μs	-	16	-	ns
t _b	I _F = 6A, dI _F /dt = 200A/μs	-	8.5	-	ns
Q _{RR}	I _F = 6A, dI _F /dt = 200A/μs	-	45	-	nC
CJ	V _R = 10V, I _F = 0A	-	20	-	pF
R _{θJC}		-	-	3	°C/W

Electrical Specifications $T_C = 25^{\circ}C$, Unless Otherwise Specified

DEFINITIONS

 V_F = Instantaneous forward voltage (pw = 300µs, D = 2%).

 I_R = Instantaneous reverse current.

 t_{rr} = Reverse recovery time (See Figure 9), summation of $t_a + t_b$.

 t_a = Time to reach peak reverse current (See Figure 9).

 t_b = Time from peak I_{RM} to projected zero crossing of I_{RM} based on a straight line from peak I_{RM} through 25% of I_{RM} (See Figure 9).

Q_{RR} = Reverse recovery charge.

 C_J = Junction capacitance.

 $R_{\theta JC}$ = Thermal resistance junction to case.

pw = Pulse width.

D = Duty cycle.

Typical Performance Curves




FIGURE 1. FORWARD CURRENT vs FORWARD VOLTAGE




FIGURE 2. REVERSE CURRENT vs REVERSE

Typical Performance Curves (Continued)





FIGURE 3. t_{rr}, t_a AND t_b CURVES vs FORWARD CURRENT








FIGURE 4. trr, ta AND tb CURVES vs FORWARD CURRENT




FIGURE 6. CURRENT DERATING CURVE





FIGURE 7. JUNCTION CAPACITANCE vs REVERSE VOLTAGE

www.onsemi.com 3

Test Circuits and Waveforms








FIGURE 10. AVALANCHE ENERGY TEST CIRCUIT




FIGURE 9. trr WAVEFORMS AND DEFINITIONS




FIGURE 11. AVALANCHE CURRENT AND VOLTAGE WAVEFORMS

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative