

Bipolar Transistor

–30 V, –0.7 A, Low $V_{CE(sat)}$ PNP Single
CPH3

30A02CH

Features

- Large Current Capacitance
- Low Collector-to-Emitter Saturation Voltage (Resistance)
 $R_{CE(sat)}$ Typ. = 580 m Ω ($I_C = 0.7$ A, $I_B = 35$ mA)
- Small ON-resistance (R_{on})

Applications


- Low-frequency Amplifier, High-speed Switching, Small Motor Drive

Specifications

ABSOLUTE MAXIMUM RATINGS ($T_a = 25^\circ\text{C}$)


Parameter	Symbol	Conditions	Ratings	Unit
Collector-to-Base Voltage	V_{CBO}		–30	V
Collector-to-Emitter Voltage	V_{CEO}		–30	V
Emitter-to-Base Voltage	V_{EBO}		–5	V
Collector Current	I_C		–700	mA
Collector Current (Pulse)	I_{CP}		–1.4	A
Collector Dissipation	P_C	Mounted on a ceramic board (600 mm ² x 0.8 mm)	700	mW
Junction Temperature	T_j		150	°C
Storage Temperature	T_{stg}		–55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.




CPH3
CASE 318BA

MARKING DIAGRAM



ELECTRICAL CONNECTION




ORDERING INFORMATION

See detailed ordering and shipping information on page 4 of this data sheet.

ELECTRICAL CHARACTERISTICS ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Conditions	Ratings			Unit
			Min	Typ	Max	
Collector Cutoff Current	I_{CBO}	$V_{CB} = -30\text{ V}, I_E = 0\text{ A}$	–	–	–100	nA
Emitter Cutoff Current	I_{EBO}	$V_{EB} = -4\text{ V}, I_C = 0\text{ A}$	–	–	–100	nA
DC Current Gain	h_{FE}	$V_{CE} = -2\text{ V}, I_C = -10\text{ mA}$	200	–	500	
Gain–Bandwidth Product	f_T	$V_{CE} = -10\text{ V}, I_C = -50\text{ mA}$	–	520	–	MHz
Output Capacitance	C_{ob}	$V_{CB} = -10\text{ V}, f = 1\text{ MHz}$	–	4.7	–	pF
Collector–to–Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = -200\text{ mA}, I_B = -10\text{ mA}$	–	–110	–220	mV
Base–to–Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = -200\text{ mA}, I_B = -10\text{ mA}$	–	–0.9	–1.2	V
Collector–to–Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = -10\text{ }\mu\text{A}, I_E = 0\text{ A}$	–30	–	–	V
Collector–to–Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = -1\text{ mA}, R_{BE} = \infty$	–30	–	–	V
Emitter–to–Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = -10\text{ }\mu\text{A}, I_C = 0\text{ A}$	–5	–	–	V
Turn–On Time	t_{on}	See specified Test Circuit.	–	35	–	ns
Storage Time	t_{stg}		–	125	–	ns
Fall Time	t_f		–	25	–	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Switching Time Test Circuit**Figure 1. Switching Time Test Circuit**




Figure 2. $I_C - V_{CE}$




Figure 3. $I_C - V_{BE}$




Figure 4. $h_{FE} - I_C$




Figure 5. $V_{CE(sat)} - I_C$




Figure 6. $V_{CE(sat)} - I_C$




Figure 7. $V_{BE(sat)} - I_C$

30A02CH




Figure 8. $C_{ob} - V_{CB}$




Figure 9. $f_T - I_C$




Figure 10. $R_{on} - I_B$




Figure 11. $P_C - T_a$


ORDERING INFORMATION

Device	Package	Shipping [†]
30A02CH-TL-E	CPH3 (Pb-Free)	3,000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

ON

DATE 30 NOV 2011



onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales