# SB05-03Q

# Schottky Barrier Diode 30V, 0.5A, Low IR, Single MCP



# **Applications**

• High frequency rectification (switching regulators, converters, choppers)

# Features

- Low forward voltage (VF max=0.55V)
- Fast reverse recovery time (trr max=10ns)

- Low switching noise
- Low leakage current and high reliability due to highly reliable planar structure
- · Small-sized package, permitting SB05-03Q-applied sets to be compact and slim

# **Specifications**


#### Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Conditions	Ratings	Unit
Repetitive Peak Reverse Voltage	VRRM		30	V
Nonrepetitive Peak Reverse Surge Voltage	VRSM		35	V
Average Output Current	IO		500	mA
Surge Forward Current	IFSM	50Hz sine wave, 1 cycle	3	А
Junction Temperature	Tj		-55 to +125	°C
Storage Temperature	Tstg		-55 to +125	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

#### Package Dimensions

unit : mm (typ) 7023A-005




#### Product & Package Information

- Package : MCP
- JEITA, JEDEC : SC-70, SOT-323
- Minimum Packing Quantity : 3,000 pcs./reel


#### Packing Type: TL

Marking






#### **Electrical Connection**



#### Electrical Characteristics at Ta=25°C


Parameter	Symbol	Conditions	Ratings			Unit
		Conditions	min	typ	max	Unit
Reverse Voltage	VR	IR=150μA	30			V
Forward Voltage	VF	IF=500mA			0.55	V
Reverse Current	IR	V <sub>R</sub> =15V			30	μΑ
Interterminal Capacitance	С	V <sub>R</sub> =10V, f=1MHz		16		рF
Reverse Recovery Time	trr	IF=IR=100mA, See specified Test Circuit.			10	ns
Thermal Resistance	Rth(j-a)			600		°C / W

### trr Test Circuit



#### **Ordering Information**

•			
Device	Package	Shipping	memo
SB05-03Q-TL-E	MCP	3,000pcs./reel	Pb Free




# Embossed Taping Specification SB05-03Q-TL-E

1. Packing Format

Package Name	Carrier Tape	Maximum Number of devices contained (pcs)		Packing format		
	Туре	Reel Inner	box Outer box	Inner BOX (C-1) Outer BOX (A-7)		
MCP	MCP	3,000 15,0	00 90,000	) 5 reels contained 6 inner boxes contained		
				Dimensions:mm (external) Dimensions:mm (external)		
				183×72×185 440×195×210		
Reel label, Inner box label <u>Outer box label</u>						
Packing method (unit:mm) It is a label at the time of factory ship The form of a label may change in physica distribution process.						
0			<	<u>69</u> <u>108</u>		
	Type LOT Quan Orig Reel la	No> tity -> in -> N	(17) LOT OO 11 11111 11111 111111 (0) QTY OO 11 11111 111111 (2) SPBCIAL 11 1111111111111111111111111111111111	COOCOOOO TYPE CODE IIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIII		
			Labe			
			LEAD FR			
			LEAD FR	REE 4 JEITA Phase 3		


2. Taping configuration

2-1. Carrier tape size (unit:mm)




Those with oen electrode terminal on the feed hole side  $\cdots TL$ 

# Outline Drawing SB05-03Q-TL-E



# Land Pattern Example



ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/A