




SOD-123 2L 1.60x2.69x1.16 CASE 425 ISSUE H


DATE 29 FEB 2024



TOP VIEW







NOTES:

- DIMENSION AND TOLERANCING PER ASME Y14.5M, 2018
- 2. CONTROLLING DIMENSION: MILLIMETERS

	MILLIMETER			
DIM	MIN.	N□M.	MAX.	
А	0.94	1.17	1.35	
A1	0.00	0.05	0.10	
A2	1.16 REF.			
b	0.51	0.61	0.71	
C	_	_	0.15	
D	1.40	1.60	1.80	
E	2.54	2.69	2.84	
Н	3.56	3.68	3,86	
L	0.25 REF.			
<u>S</u>	0°		10°	
θ1	0°		10°	



RECOMMENDED MOUNTING FOOTPRINT *For additional information on or Pb-Free strategy and soldering details, please download the DN Semiconductor Soldering and Mounting Techniques Reference manual SDLDERRM/D.

GENERIC MARKING DIAGRAM*



XXX = Specific Device Code

M = Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

STYLE 1: PIN 1. CATHODE

2. ANOD			

DOCUMENT NUMBER:	98ASB42927B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SOD-123 2L 1.60x2.69x1.16		PAGE 1 OF 1	

onsemi and ONSemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.