ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

Guidelines for SMT Assembly of 0201 DSN Package



ON Semiconductor®

http://onsemi.com

APPLICATION NOTE

Package Overview

ON Semiconductor's $0.6 \ge 0.3 \mod DSN$ (Dual Silicon No-lead) two pin package. This small package outline provides a component option that can be added to a design with minimal impact to the overall PCB area budget enhancing the ease of layout in space constrained applications.

The DSN package is a chip level package using solder-able metal contacts under the package similar to DFN style packages. The DSN style package enables 100% utilization of the package area for active silicon with, offering a significant performance per board area advantage compared to products in plastic molded packages. A finished package is shown in Figure 1.



Figure 1. 0.60 mm x 0.30 mm Two-Lead Package

Component Placement

DSN packages must be mounted properly to avoid any misplacement which can result in well-soldered devices, for

small 0201 DSN package with smaller pitch <0.45 mm NSMD pads is recommended, to provide a solder mask opening larger than the footprint of the package. This is a very critical step to prevent the tilting of devices from side-to-side or end-to-end and creating short circuit by solder/flux bridge as shown in Figures 2, 3 and 4.





Figure 15: SEM image showing the other side of D2.

Figure 16: SEM image showing the continuous bridging by material (most probably flux).

Figure 4. Actual Solder Bridge Caused by Improper Mounting



Figure 5. IV Curve Before Solder Bridge Caused by Improper Mounting



Figure 6. Short Circuit IV Caused by Improper Mounting

Recommended Board Mounting Process

The package board mounting process can be optimized by first defining and controlling the following:

- 1. Mounting pads.
- 2. Solder mask design guidelines.
- 3. Stencil for applying solder paste on to the PCB.
- 4. Choice of proper solder paste.
- 5. Package placement.
- 6. Reflow of the solder paste.
- 7. Final inspection of the solder joints.
- 8. PCB circuit traces width.

Figure 7 shows the size and orientation of the package on the recommended PCB mounting pads, solder mask and solder stencil.



Figure 7. Recommended Mounting Pattern

Solder Mask

Two types of PCB solder mask openings commonly used for surface mount leadless style packages are:

- 1. Non Solder Masked Defined (NSMD)
- 2. Solder Masked Defined (SMD)

The solder mask is pulled away from the solder–able metallization for NSMD pads, while the solder mask overlaps the edge of the metallization for SMD pads as shown in Figure 8. For SMD pads, the solder mask restricts the flow of solder paste on the top of the metallization and prevents the solder from flowing down the side of the metal pad. This is different from the NSMD configuration where the solder flows both across the top and down the sides of the PCB metallization.



Figure 8. Comparison of NSMD vs. SMD Pads

NSMD pad is recommended over SMD pads. It is easier to define and control the location and size of copper pad verses the solder mask opening. This is because the copper etch process capability has a tighter tolerance than that of the solder mask process. NSMD pads also allow for easier visual inspection of the solder fillet.

Printed Circuit Board Solder Pad Design

Based on results of board mount testing, ON Semiconductor's recommended mounting pads and solder mask opening are shown in Figures 9 and 10. Maximum acceptable nPCB mounting pads and solder mask opening are shown in Figure 9, and summary in Table 1.



Figure 9. Recommended Mounting Pattern





Table 1. SOLDER PAD DESIGN

Parameters	Solder Mask
Solder Mask L	0.85 mm
Solder Mask W	0.45 mm
Mounting Pad L	0.30 mm
Mounting Pad W	0.35 mm
Stencil Thickness	80–120 μm
Stencil Aperture	~0.30 mm
Stencil Paste	90%wt alloy 10% system flux

Conclusions

The 0201 DSN2 package offers a 70% board space reduction from the popular 0402 outline. The guidelines outlined in this application note will ensure optimal board mounting results with maximized bond strength and minimal tilting causing short circuit, and avoiding misalignment between solder mask and board pads can result high SMT failure rate.

References

1. EIA 726:2002

 8 mm Punched And Embossed Carrier Taping Of Surface Mount Components
For Automatic Handling Of Devices Generally
Smaller Than 2.0 mm X 1.2 mm.

2. IEC 60286

- 3 Packaging of components for automatic handling – Part 3:

Packaging of Surface–Mount Devices (SMDs) or components on continuous tapes.

3. On Semiconductor

- Board Application note - AND8398/D

ON Semiconductor and **OD** are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemic.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death massociated with such unintended or unauthorized use provides coupry or manufacture of the part. SCILLC and is the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This litera

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421-32, 700-2010

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative