ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

DN06004/D



Design Note – DN06004/D

SEPIC LED Driver

ON Semiconductor

Device	Application	Input Voltage	Output Power	Topology	I/O Isolation	
CS5171	Miners Light	4 Vdc	2 W	SEPIC	NO	

Other Specifications						
	Output 3	Output 4				
Output Voltage	3.5 V	N/A	N/A	N/A		
Nominal Current	350 mA	N/A	N/A	N/A		


Minimum Efficiency	70%
Operating Temp. Range	0 to +70°C


Circuit Description


This application is for the LED driver to be powered from a source that can be higher or lower than the LED voltage and must be efficient as possible. The SEPIC topology was chosen. The schematic in the following page shows a 4 V SEPIC LED driver using the CS5171 as a DC-DC boost regulator. The CS5171 operates at 260 KHz with about 65% efficiency with a 4.0V input. The MBRM110LT1 is a 10V schottky diode with a forward drop of < 0.3V. The NCS2001 operates as amplifier for the current sense voltage across R2 and drives the feedback pin on the CS5171.


Key Features

- SEPIC LED Driver
- 350 mA LED Current









DN06004/D

Bill of Materials

Ref.	Qty.	Description	Value	Package	Vendor	Vendor PN	Digikey #
U1	1	IC Boost Controller		SO-8	ON Semi	CS5171ED8	
U2	1	Amplifier		SOT23-5	ON Semi	NCS2001SN2T1	
D1	1	Diode	10 V Schottky	Powermite	ON Semi	MBRM110LT1	
LED1	1			STAR / O	LUXON	LXHL-NW98	
J1	1				Phoenix Contact	1715035	
C1	1	Capacitor	.01 uf	805	Panasonic	ECJ-2VB1H103K	PCC103BNCT-ND
C2	1	Capacitor	22 uf	smd	Panasonic	EEF-CD1B220R	PCE3168CT-ND
C3	1	Capacitor	200 nf	805	Panasonic	ECJ-2VB1C224K	PCC1816CT-ND
C4	1	Capacitor	22 uf	smd	Panasonic	EEF-CD1B220R	PCE3168CT-ND
C5	1	Capacitor	2.2 uf	1206	Panasonic	ECJ-3YB1C225K	PCC1931TR-ND
L					-		
R1	1	Resistor	5.1 K ohm	1206	Panasonic		P5.1KECT-ND
R2	1	Resistor	.56 ohm 1%	1206	Panasonic		P.56RCT-ND
R3	1	Resistor	5.1 K ohm 1%	1206	Panasonic		P5.1KFCT-ND
R4	1	Resistor	1 K ohm 1%	1206	Panasonic		P1.0KFCT-ND
R5	1	Resistor	1 K ohm 1%	1206	Panasonic		P1.0KFCT-ND
	4	la ducto a	00 ut	l	O all anaft		
L1	1	Inductor	22 uh	smd	Coil_craft	MSS6132-223MXD	
L2	1	Inductor	22 uh	smd	Coil_craft	MSS6132-223MXD	
-							
DOD							
PCB	1	CS5171 SEPIC raw board				CS5171 Rev A	

© 2006 ON Semiconductor.

Disclaimer: ON Semiconductor is providing this design note "AS IS" and does not assume any liability arising from its use; nor does ON Semiconductor convey any license to its or any third party's intellectual property rights. This document is provided only to assist customers in evaluation of the referenced circuit implementation and the recipient assumes all liability and risk associated with its use, including, but not limited to, compliance with all regulatory standards. ON Semiconductor may change any of its products at any time, without notice.

Design note created by Roger Miller, e-mail: roger.miller@onsemi.com