

MOSFET - N-Channel, POWERTRENCH[®], SyncFET[™]

30 V, 18 A, 9.3 mΩ

FDMC7692S

General Description


This FDMC7692S is produced using **onsemi's** advanced POWERTRENCH process that has been especially tailored to minimize the on–state resistance. This device is well suited for Power Management and load switching applications common in Notebook Computers and Portable Battery Packs.

Features

- Max $r_{DS(on)} = 9.3 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, $I_D = 12.5 \text{ A}$
- Max $r_{DS(on)} = 13.6 \text{ m}\Omega$ at $V_{GS} = 4.5 \text{ V}$, $I_D = 10.4 \text{ A}$
- High Performance Technology for Extremely Low r_{DS(on)}
- These Devices are Pb-Free and are RoHS Compliant

Applications

- DC DC Buck Converters
- Notebook DC DC Application



WDFN8 3.3x3.3, 0.65P CASE 511DQ (Option A)


MARKING DIAGRAM



FDMC7692S = Specific Device Code A = Assembly Location XY = 2-Digit Date Code

KK = 2-Digit Lot Run Traceability Code

PIN ASSIGNMENT



ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet.

MOSFET MAXIMUM RATINGS ($T_A = 25^{\circ}C$ unless otherwise noted)


Symbol	Parameter			Rating	Unit
V _{DS}	Drain to Source Voltage			30	V
V _{GS}	Gate to Source Voltage		±20	V	
I _D	Drain Current	Continuous	T _C = 25°C	18	Α
		Continuous (Note 1a)	T _A = 25°C	12.5	
		Pulsed	•	45	
E _{AS}	Single Pulse Avalanche Energy (Note 2)		21	mJ	
P _D	Power Dissipation		T _C = 25°C	27	W
	Power Dissipation (Note 1a)		T _A = 25°C	2.3	
T _J , T _{STG}	Operating and Storage Junction Temperature Range		-55 to 150	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Parameter	Rating	Unit
Rелс	Thermal Resistance, Junction to Case		°C/W
Reja	Thermal Resistance, Junction to Ambient (Note 1a)	53	

^{1.} $R_{\theta JA}$ is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



a. 53°C/W when mounted on a 1 in² pad of 2 oz copper



b. 125°C/W when mounted on a minimum pad of 2 oz copper

2. E_{AS} of 21 mJ is based on starting $T_{J} = 25^{\circ}C$; L = 0.3 mH, $I_{AS} = 12.0$ A, $V_{DD} = 27$ V, $V_{GS} = 10$ V. 100% test at L = 3 mH, $I_{AS} = 3.2$ A.

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHARA	CTERISTICS					
BV _{DSS}	Drain to Source Breakdown Voltage	I _D = 1 mA, V _{GS} = 0 V	30	-	-	V
$\Delta BV_{DSS} / \Delta T_{J}$	Breakdown Voltage Temperature Coefficient	I _D = 10 mA, referenced to 25°C	-	16	-	mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V	-	-	500	μΑ
I _{GSS}	Gate to Source Leakage Current	V _{GS} = 20 V, V _{DS} = 0 V	ı	-	100	nA
ON CHARAC	CTERISTICS (Note 3)					
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 1 \text{ mA}$	1.2	2.0	3.0	V
$\Delta V_{GS(th)}$ / ΔT_J	Gate to Source Threshold Voltage Temperature Coefficient	I _D = 10 mA, referenced to 25°C	ı	-5	=	mV/°C
r _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 12.5 A	ı	7.8	9.3	mΩ
		V _{GS} = 4.5 V, I _D = 10.4 A	ı	10.8	13.6	
		V _{GS} = 10 V, I _D = 12.5 A, T _J = 125°C	_	9.6	13.0	
9FS	Forward Transconductance	V _{DS} = 5 V, I _D = 12.5 A	1	62	_	S
DYNAMIC C	HARACTERISTICS					
C _{iss}	Input Capacitance	V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHz	-	1040	1385	pF
C _{oss}	Output Capacitance		-	445	590	pF
C _{rss}	Reverse Transfer Capacitance		-	40	60	pF
Rg	Gate Resistance	f = 1 MHz	ı	1.1	2.9	Ω
SWITCHING	CHARACTERISTICS					
t _{d(on)}	Turn-On Delay Time	$V_{DD} = 15 \text{ V}, I_D = 12.5 \text{ A}, V_{GS} = 10 \text{ V},$	-	9	17	ns
t _r	Rise Time	$R_{GEN} = 6 \Omega$	ı	3	10	ns
t _{d(off)}	Turn-Off Delay Time		ı	19	34	ns
t _f	Fall Time		-	3	10	ns
Qg	Total Gate Charge	$V_{GS} = 0 \text{ V to } 10 \text{ V}, V_{DD} = 15 \text{ V}, I_D = 12.5 \text{ A}$	-	16	23	nC
		V _{GS} = 0 V to 4.5 V, V _{DD} = 15 V, I _D = 12.5 A	-	8	10	nC
Q _{gs}	Total Gate Charge	V _{DD} = 15 V, I _D = 12.5 A	-	4	_	nC
Q _{gd}	Gate to Drain "Miller" Charge		-	2	-	nC
DRAIN-SOU	IRCE DIODE CHARACTERISTICS			•	•	•
V _{SD}	Source to Drain Diode Forward Voltage	V _{GS} = 0 V, I _S = 12.5 A (Note 3)	-	0.9	1.3	V
		V _{GS} = 0 V, I _S = 0.9 A (Note 3)	-	0.5	0.7	1
t _{rr}	Reverse Recovery Time	I _F = 12.5 A, di/dt = 300 A/μs	-	21	33	ns
Q _{rr}	Reverse Recovery Charge	1		16	29	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Pulse Test: Pulse Width < 300 µs, Duty cycle < 2.0%.

TYPICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)




Figure 1. On Region Characteristics




Figure 2. Normalized On–Resistance vs.
Drain Current and Gate Voltage




Figure 3. Normalized On Resistance vs. Junction Temperature




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted) (continued)




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Forward Bias Safe Operating Area




Figure 11. Single Pulse Maximum Power Dissipation

TYPICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted) (continued)




Figure 12. Junction-to-Ambient Transient Thermal Response Curve

ORDERING INFORMATION


Device	Device Marking	Package Type	Shipping [†]
FDMC7692S	FDMC7692S	WDFN8 3.3x3.3, 0.65P case 511DQ (Pb-Free)	3000 / Tape & Reel


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


POWERTRENCH is a registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.


SyncFET is a trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.


WDFN8 3.3x3.3, 0.65P CASE 511DQ **ISSUE 0**

















UNLESS SPECIFIED **BOTTOM VIEW** (OPTION B)

Electronic versions are uncontrolled except when accessed directly from the Document Repository. **DOCUMENT NUMBER:** 98AON13648G Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.


DESCRIPTION: WDFN8 3.3X3.3, 0.65P


ON Semiconductor and un are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.


PAGE 1 OF 2

WDFN8 3.3x3.3, 0.65P CASE 511DQ ISSUE O

DATE 31 OCT 2016







ALL DIMENSIONS AS PER OPTION A UNLESS SPECIFIED BOTTOM VIEW (OPTION C)

NOTES:

- A. PACKAGE DOES NOT FULLY CONFORM TO JEDEC REGISTRATION MO-240.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 2009.
- D. LAND PATTERN RECOMMENDATION IS EXISTING INDUSTRY LAND PATTERN
- E. DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH. BURRS OR MOLD FLASH SHALL NOT EXCEED 0.10MM.

DOCUMENT NUMBER:	98AON13648G	Electronic versions are uncontrolled except when accessed directly from the Document Reposito Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	WDFN8 3.3X3.3, 0.65P		PAGE 2 OF 2	

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI., and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems. or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales