

# NCP6951EVK

## Camera PMIC with Flash LED Driver Evaluation Board User's Manual



ON Semiconductor®

[www.onsemi.com](http://www.onsemi.com)

### EVK BOARD USER'S MANUAL

#### Overview

The NCP6951EVK evaluation kit is a full assembled circuit board for evaluation and test of the NCP6951. This document provides documentation, test procedure and equipment set-up for the complete evaluation of the NCP6951. The NCP6951EVK comes with one NCP6951 evaluation board, 1 MCU board for I<sup>2</sup>C master and associated cables.

#### General Description

The NCP6951 integrated circuit is part of the ON Semiconductor mini power management IC family. It is optimized to supply battery powered portable application sub-systems such as camera function, microprocessors, etc. This device integrates one high efficiency 600 mA Step-down DCDC converter with DVS (Dynamic Voltage Scaling), 5 low dropout (LDO) voltage regulators and a 1.5 A Flash LED driver in WLCSP24 package.

#### Features

- 1 Flash LED Driver
  - ◆ Adaptive Boost Supply or Bypass Mode depending on  $V_{in}$  and  $V_{flash}$  Conditions
  - ◆ Programmable Flash Current from 100 mA to 1.6 A by 100 mA Steps
  - ◆ Programmable Safety and Inhibit Timer to Limit the Flash Duration and Protect the Application

- 1 DC-DC Converters (3 MHz, 1  $\mu$ H / 10  $\mu$ F, 600 mA)
  - ◆ Peak Efficiency 95%
  - ◆ Programmable Output Voltage from 0.8 V to 2.3 V by 50 mV Steps
- 5 Low Noise – Low Dropout Regulators
  - ◆ Programmable Output Voltage from 1.7 V to 3.3 V for LDOs 1, 2, 3
  - ◆ Programmable Output Voltage from 1.2 V to 2.85 V for LDOs 4, 5
  - ◆ 200 mA Output Current Capability: LDOs 1, 2, 3, 4
  - ◆ 300 mA Output Current Capability LDO 5
  - ◆ 45  $\mu$ Vrms Low Output Noise
- Control
  - ◆ Fully Programmable through a 400 kHz / 3.4 MHz I<sup>2</sup>C with Pins Selectable I<sup>2</sup>C Address and Interrupt Output
- Small Footprint: 2.57 x 1.65 mm WLCSP 0.4 mm Pitch




Figure 1. Evaluation Board Picture

# NCP6951EVK

**Table 1. BOARD COMPONENTS DESCRIPTION**

Qty	Reference	Value	PCB Footprint	MFR	Part Number
1	–	NCP6951 PMIC	–	ON Semiconductor	NCP6951
1	C1	Ceramic Capacitor 2.2 $\mu$ F 6.3 V X5R	0402	TDK	C1005X5R0J225K050BC
7	C3 $\rightarrow$ C9	Ceramic Capacitor 1 $\mu$ F 6.3 V X5R	0402	TDK	C1005X5R0J105K05BB
1	C11	Ceramic Capacitor 4.7 $\mu$ F 6.3 V X5R	0603	TDK	C1608X5R0J475K080AB
1	C2	Ceramic Capacitor 10 $\mu$ F 6.3 V X5R	0603	TDK	C1608X5R0J106K080AB
1	C10	Ceramic Capacitor 22 $\mu$ F 6.3 V X5R	0603	TDK	C1608X5R0J226M080AC
4	C13 $\rightarrow$ C16	Ceramic Capacitor 100 $\mu$ F 6.3 V X5R	1210	TDK	C3225X5R0J107M250AC
1	C12	Ceramic Capacitor 100 nF 6.3 V X5R	0402	TDK	
1	L1	Inductor	2016	TOKO	DFE201612R–H–1R0N
1	L2	Inductor		TOKO	FDSD0412–1R0 or DFE252012F–1R0
1	D1			LUMILED	LXCL–PWF4
1	D2			SAMSUNG	SPFCW04301BL
8	LTR100 $\rightarrow$ LTR107	Jumper Header Vertical Mount, 2 positions, 100 mils	100 mils	Tyco Electronics / AMP	5–826629–0
3	J15 $\rightarrow$ J17	Jumper Header Vertical Mount, 3 positions, 100 mils	100 mils	Tyco Electronics / AMP	5–826629–0
14	J1 $\rightarrow$ J14	Banana Jack		Hirschmann Test and Measurement	930160000
1	J18	Connector header 26 pos		3M	N2526–6002–RB
19	TP1 $\rightarrow$ TP19	Test Point		Keystone Electronics	5011
4	Q1, Q3, R1, R2	Not Mounted			
3	JUMP1 $\rightarrow$ JUMP3	Jumper Connector	400 mils	Harwin	D3082–B01
10	S101 $\rightarrow$ S110	Shorted			
4	SH1 $\rightarrow$ SH4	Current sense			
4	Spacer nylon	H1, H2, H3, H4		Richco Plastic co	R908–4

# NCP6951EVK

**Table 2. CONNECTOR DESCRIPTION**

	Pin	Description
<b>Input Power</b>		
J1 → J6	J3, J5	Negative input connected to GND pin
	J1	Flash LED power supply
	J2	DCDC power supply
	J4, J5	LDOs power supply
<b>Input Power</b>		
J7 → J14	J8, J14	Negative output connected to GND pin
	J7	DCDC1 output
	J9	LDO1 output
	J10	LDO2 output
	J11	LDO3 output
	J12	LDO4 output
	J13	LDO5 output
<b>Chip Control</b>		
MCU	SDA	I <sup>2</sup> C data, connect to SDA pin or the 26 pins ribbon cable
	SCL	I <sup>2</sup> C data, connect to SCL pin or the 26 pins ribbon cable
	HWEN	Master enable pin connected to the 26 pins ribbon cable thru J3
	FLEN	Flash LED driver enable pin
	FLSEL	Flash LED driver selectable pin

# NCP6951EVK

## ASSEMBLY LAYER




Figure 2. Assembly Layer

# NCP6951EVK

## SCHEMATIC





Figure 3. Evaluation Board Schematic

REV	DATE	DESCRIPTION	AUTHOR
B	01/29/13	Add ifl current sense, separate LED footprint	O. Next Lines
A	10/04/13	Original schematic	O. Next Lines
<b>ON SEMICONDUCTOR</b> 195 Chemin des Corbeilles BP63515 91061 Evry-Courcouronnes Cedex 1 France			 Rev <b>B.0</b>
<b>NCP6951 Evaluation Board</b> <b>TLS-P-001-B-0114-OM</b>			
DWG NO		Rev	
TLS-P-001-A-0913-OM		B.0	
Friday, February 14, 2014	Scale	Size C	Sheet 1 of <Total # of pages>

# NCP6951EVK

## SOFTWARE INSTALLATION

Double click on NCP6951\_setup.exe file. Follow the instructions set-up.

It is recommended to copy the NCP6951\_setup.exe to a local directory: If eval kit is already installed, a simple double click on NCP6951.exe will launch the GUI.

**Important notice:** In order to properly install drivers and software, please launch NCP6951\_setup.exe file before connects the MCU board.




Figure 4.

# NCP6951EVK

## QUICK CONFIGURATION

### Power Supply

NCP6951 requires at least 1 external power supply:  
Vbat (J2) : supply between 2.5V to 5.5V.

### Jumpers Configuration

The HWEN, FLEN and FLSEL jumpers are configured by default to work with the ON Semiconductor I<sup>2</sup>C interface board.

S103, S104 and S106 shunt are soldered to use only one power supply for the DCDCs, LDOs and FLASH.

S101, S102 and S110 are soldered to close the loop of the inside buck and boost converter. To measure the current, user has to unsolder the jumper and use SH1, SH2 or SH4.

### Load

#### *DCDCx Converters*

An electronic load or passive load can be connected between J7 and J8 for DCDC1.

#### *LDOx Regulators*

An electronic load or passive load can be connected between J9 and J8 or J14 for LDO1, between J10 and J8 or J14 for LDO2, J11 and J8 or J14 for LDO3, J12 and J8 or J14 for LDO4, J13 and J8 or J14 for LDO5.

#### *FLASH LED Driver*

Evaluation board is delivered with D1 or D2 soldered.

## PCB LAYOUT




Figure 5. Top Layer

# NCP6951EVK





Figure 6. Bottom Layer

ON Semiconductor and the  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada  
**Europe, Middle East and Africa Technical Support:**  
Phone: 421 33 790 2910  
**Japan Customer Focus Center**  
Phone: 81-3-5817-1050

**ON Semiconductor Website:** [www.onsemi.com](http://www.onsemi.com)  
**Order Literature:** <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative