

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.

FAIRCHILD

SEMICONDUCTOR IM

FDS4672A

40V N-Channel PowerTrench[®] MOSFET

General Description

This N-Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low $R_{\text{DS}(\text{ON})}$ and fast switching speed.

Applications


DC/DC converter

Features

- 11 A, 40 V. $R_{\text{DS(ON)}}$ = 13 m Ω @ V_{GS} = 4.5 V
- + High performance trench technology for extremely low $R_{\text{DS}(\text{ON})}$
- Low gate charge (35 nC typical)
- High power and current handling capability
- RoHS Compliant







Absolute Maximum Ratings T_A=25°C unless otherwise noted

Symbol		Parameter		Ratings	Units
V _{DSS}	Drain-Sourc	e Voltage		40	V
V _{GSS}	Gate-Source	e Voltage		±12	V
I _D	Drain Curre	nt – Continuous	(Note 1a)	11	A
		– Pulsed		50	
E _{AS}	Single Pulse	e Avalanche Energy	(Note 3)	181	mJ
P _D	Power Dissi	pation for Single Operation	(Note 1a)	2.5	W
			(Note 1b)	1.4	
			(Note 1c)	1.2	
T _J , T _{STG}	Operating a	Operating and Storage Junction Temperature Range		-55 to +175	°C
Therma	I Charact	eristics			
R _{0JA}	Thermal Resistance, Junction-to-Ambient		nt (Note 1a)	50	°C/W
R _{0JC}	Thermal Re	rmal Resistance, Junction-to-Case		25	
Packag	e Marking	g and Ordering In	formation		
Device Marking			Reel Size	Tape width	Quantity
FDS4672A		FDS4672A	13"	12mm	2500 units

©2007 Fairchild Semiconductor Corporation

FDS4672A Rev C1 (W)

FDS4672A

February 2007

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Chai	racteristics					
BV _{DSS}	Drain–Source Breakdown Voltage	$V_{GS} = 0 V, I_D = 250 \mu A$	40			V
ΔBV _{DSS} ΔTJ	Breakdown Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, Referenced to 25°C		37		mV/°0
IDSS	Zero Gate Voltage Drain Current	$V_{DS} = 32 V, V_{GS} = 0 V$			1	μA
IGSSF	Gate-Body Leakage, Forward	$V_{GS} = 12 V$, $V_{DS} = 0 V$			100	nA
IGSSR	Gate-Body Leakage, Reverse	$V_{GS} = -12 V V_{DS} = 0 V$			-100	nA
On Char	acteristics (Note 2)					
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$	0.8	1.2	2.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, Referenced to 25°C		-4		mV/°0
R _{DS(on)}	Static Drain–Source On–Resistance	$V_{GS} = 4.5 \text{ V}, I_D = 11 \text{ A}$ $V_{GS} = 4.5 \text{ V}, I_D = 11 \text{ A}, T_J = 125^{\circ}\text{C}$		10 15	13 21	mΩ
I _{D(on)}	On-State Drain Current	$V_{GS} = 4.5 \text{ V}, V_{DS} = 5 \text{ V}$	50			Α
g _{FS}	Forward Transconductance	$V_{DS} = 5 V, I_{D} = 11 A$		65		S
Dvnami	c Characteristics	•		•		
C _{iss}	Input Capacitance	$V_{DS} = 20 V$, $V_{GS} = 0 V$,		4766		pF
Coss	Output Capacitance	f = 1.0 MHz		346		pF
C _{rss}	Reverse Transfer Capacitance			155		pF
Switchir	ng Characteristics (Note 2)	-	1			
t _{d(on)}	Turn–On Delay Time	$V_{DD} = 20 V, I_D = 1 A,$		17	31	ns
tr	Turn–On Rise Time	$V_{GS} = 4.5$ V, $R_{GEN} = 6 \Omega$		9	18	ns
t _{d(off)}	Turn–Off Delay Time			43	68	ns
t _f	Turn–Off Fall Time	-		14	25	ns
Q _g	Total Gate Charge	$V_{DS} = 20 V, I_D = 11 A,$		35	49	nC
Q _{gs}	Gate-Source Charge	$V_{GS} = 4.5 V$		7.8		nC
Q _{gd}	Gate–Drain Charge			8.8		nC
Drain-S	ource Diode Characteristics	and Maximum Ratings				
I _s	Maximum Continuous Drain–Source				2.1	Α
V _{SD}	Drain–Source Diode Forward Voltage	$V_{GS} = 0 V$, $I_S = 2.1 A$ (Note 2)		0.7	1.2	V


Scale 1 : 1 on letter size paper

0000


2. Pulse Test: Pulse Width < 300 μ s, Duty Cycle < 2.0%

 $\textbf{3}. Starting \; \textbf{T}_{J} = 25^{o} \textbf{C}, \; \textbf{L} = 3 \textbf{m} \textbf{H}, \textbf{I}_{D} = 11 \textbf{A}, \; \textbf{V}_{DD} = 40 \textbf{V}, \; \textbf{V}_{GS} = 10 \textbf{V}$


FDS4672A Rev C1 (W)



FDS4672A Rev C1 (W)



FDS4672A Rev C1 (W)



TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx™ ActiveArray™ Bottomless™ GTO™ Build it Now™ CoolFET™ I²C[™] CROSSVOLT™ i-Lo™ DOME™ EcoSPARK™ E²CMOS™ EnSigna™ FACT® FAST® FASTr™ FPS™ FRFET™ MSX™

FACT Quiet Series™ GlobalOptoisolator™ HiSeC™ ImpliedDisconnect[™] IntelliMAX™ **ISOPLANAR™** LittleFET™ MICROCOUPLER™ MicroFET™ MicroPak™ MICROWIRE™ MSXPro™ Across the board. Around the world.™ Programmable Active Droop™

OCX™ OCXPro™ **OPTOLOGIC**[®] **OPTOPLANAR™** PACMAN™ POP™ Power247™ PowerEdge™ PowerSaver™ PowerTrench[®] **QFET**® QS™ QT Optoelectronics™ Quiet Series™ RapidConfigure™ RapidConnect™ µSerDes™ ScalarPump™

SILENT SWITCHER® SMART START™ SPM™ Stealth™ SuperFET™ SuperSOT™-3 SuperSOT[™]-6 SuperSOT™-8 SyncFET™ TCM™ TinvBoost™ TinyBuck™ TinyPWM™ TinyPower™ TinyLogic® TINYOPTO™ TruTranslation™ UHC®

UniFET™ VCX™

Wire™

DISCLAIMER

DISCLAIMENT FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

The Power Franchise[®]

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS **Definition of Terms**

Datasheet Identification	Product Status	Definition		
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.		
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.		
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.		
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.		

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC