

# FDMD8430

## Dual N-Channel PowerTrench<sup>®</sup> MOSFET

30 V, 28 A, 2.12 mΩ

### General Description

This package integrates two N-Channel devices connected internally in common-source configuration. This enables very low package parasitics and optimized thermal path to the common source pad on the bottom. Provides a very small footprint (3.3 x 5 mm) for higher power density.

### Features

- Max  $r_{DS(on)}$  = 2.12 mΩ at  $V_{GS} = 10\text{ V}$ ,  $I_D = 28\text{ A}$
- Max  $r_{DS(on)}$  = 2.95 mΩ at  $V_{GS} = 4.5\text{ V}$ ,  $I_D = 24\text{ A}$
- Ideal for Flexible Layout in Secondary Side Synchronous Rectification
- 100% UIL Tested
- Termination is Lead-free and RoHS Compliant



### Applications

- Isolated DC-DC Synchronous Rectifiers
- Common Ground Load Switches




ON Semiconductor<sup>®</sup>

[www.onsemi.com](http://www.onsemi.com)



PQFN8  
PowerTrench  
CASE 483AU



### ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.


# FDMD8430

**Table 1. MOSFET MAXIMUM RATINGS**  $T_A = 25^\circ\text{C}$  unless otherwise noted.

Symbol	Parameter	Rating	Units
$V_{DS}$	Drain to Source Voltage	30	V
$V_{GS}$	Gate to Source Voltage	$\pm 20$	V
$I_D$	Drain Current – Continuous	$T_C = 25^\circ\text{C}$ (Note 1)	95
	– Continuous	$T_C = 100^\circ\text{C}$ (Note 1)	60
	– Continuous	$T_A = 25^\circ\text{C}$ (Figure 1)	28
	– Pulsed	(Note 2)	562
$E_{AS}$	Single Pulse Avalanche Energy	(Note 3)	96
$P_D$	Power Dissipation	$T_C = 25^\circ\text{C}$	29
	Power Dissipation	$T_A = 25^\circ\text{C}$ (Figure 1)	2.1
$T_J, T_{STG}$	Operating and Storage Junction Temperature Range	$-55$ to $+150$	$^\circ\text{C}$


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Computed continuous current limited to Max Junction Temperature only, actual continuous current will be limited by thermal & electro-mechanical application board design.
2. Pulse  $I_D$  refers to Figure 13 Forward Bias Safe Operating Area.
3.  $E_{AS}$  of 96 mJ is based on starting  $T_J = 25^\circ\text{C}$ ;  $L = 0.3$  mH,  $I_{AS} = 31.7$  A,  $V_{DD} = 27$  V.



a.  $60^\circ\text{C/W}$  when mounted on a  $1\text{in}^2$  pad of 2 oz. copper

**Figure 1.**



b.  $160^\circ\text{C/W}$  when mounted on a minimum pad of 2 oz. copper

**Figure 2.**

**Table 2. THERMAL CHARACTERISTICS**

$R_{\theta JC}$	Thermal Resistance, Junction to Case	4.7	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Figure 1)	60	

4.  $R_{\theta JA}$  is determined with the device mounted on a  $1\text{in}^2$  pad 2 oz copper pad on a  $1.5 \times 1.5$  in. board of FR-4 material,  $R_{\theta CA}$  is determined by the user's board design.

**Table 3. PACKAGE MARKING AND ORDERING INFORMATION**

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMD8430	FDMD8430	Power 3.3 x 5	13"	12 mm	3000 units

# FDMD8430

**Table 4. ELECTRICAL CHARACTERISTICS**  $T_J = 25^\circ\text{C}$  unless otherwise noted.

Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
<b>OFF CHARACTERISTICS</b>						
$BV_{DSS}$	Drain to Source Breakdown Voltage	$I_D = 250 \mu\text{A}$ , $V_{GS} = 0 \text{ V}$	30			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \mu\text{A}$ , referenced to $25^\circ\text{C}$		17		mV/ $^\circ\text{C}$
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS} = 24 \text{ V}$ , $V_{GS} = 0 \text{ V}$			1	$\mu\text{A}$
$I_{GSS}$	Gate to Source Leakage Current	$V_{GS} = \pm 20 \text{ V}$ , $V_{DS} = 0 \text{ V}$			$\pm 100$	nA
<b>ON CHARACTERISTICS</b>						
$V_{GS(th)}$	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$ , $I_D = 250 \mu\text{A}$	1.0	1.6	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \mu\text{A}$ , referenced to $25^\circ\text{C}$		-5		mV/ $^\circ\text{C}$
$r_{DS(on)}$	Static Drain to Source On Resistance	$V_{GS} = 10 \text{ V}$ , $I_D = 28 \text{ A}$		1.5	2.12	m $\Omega$
		$V_{GS} = 4.5 \text{ V}$ , $I_D = 24 \text{ A}$		2.0	2.95	
		$V_{GS} = 10 \text{ V}$ , $I_D = 28 \text{ A}$ , $T_J = 125^\circ\text{C}$		1.7	2.4	
$g_{FS}$	Forward Transconductance	$V_{DD} = 5 \text{ V}$ , $I_D = 28 \text{ A}$			250	S
<b>DYNAMIC CHARACTERISTICS</b>						
$C_{iss}$	Input Capacitance	$V_{DS} = 15 \text{ V}$ , $V_{GS} = 0 \text{ V}$ , $f = 1 \text{ MHz}$		3595	5035	pF
$C_{oss}$	Output Capacitance			1150	1610	pF
$C_{rss}$	Reverse Transfer Capacitance			112	160	pF
$R_g$	Gate Resistance			2.3	4.5	$\Omega$
<b>SWITCHING CHARACTERISTICS</b>						
$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 15 \text{ V}$ , $I_D = 28 \text{ A}$ , $V_{GS} = 10 \text{ V}$ , $R_{GEN} = 6 \Omega$		11	20	ns
$t_r$	Rise Time			8	16	ns
$t_{d(off)}$	Turn-Off Delay Time			71	114	ns
$t_f$	Fall Time			20	36	ns
$Q_{g(tot)}$	Total Gate Charge	$V_{GS} = 0 \text{ V to } 10 \text{ V}$	$V_{DD} = 15 \text{ V}$ , $I_D = 28 \text{ A}$	52	90	nC
	Total Gate Charge	$V_{GS} = 0 \text{ V to } 4.5 \text{ V}$		25	45	nC
$Q_{gs}$	Gate to Source Charge			10		nC
$Q_{gd}$	Gate to Drain "Miller" Charge			7		nC
<b>DRAIN-SOURCE DIODE CHARACTERISTICS</b>						
$V_{SD}$	Source to Drain Diode Forward Voltage	$V_{GS} = 0 \text{ V}$ , $I_S = 28 \text{ A}$ (Note 5)		0.8	1.2	V
$t_{rr}$	Reverse Recovery Time	$I_F = 28 \text{ A}$ , $di/dt = 100 \text{ A}/\mu\text{s}$		40	64	ns
$Q_{rr}$	Reverse Recovery Charge			22	36	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: Pulse Width < 300  $\mu\text{s}$ , Duty Cycle < 2.0%.

TYPICAL CHARACTERISTICS  $T_J = 25^\circ\text{C}$  unless otherwise noted.




Figure 3. On Region Characteristics




Figure 4. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 5. Normalized On-Resistance vs. Junction Temperature




Figure 6. On-Resistance vs. Gate to Source Voltage




Figure 7. Transfer Characteristics




Figure 8. Source to Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS  $T_J = 25^\circ\text{C}$  unless otherwise noted.




Figure 9. Gate Charge Characteristics




Figure 10. Capacitance vs. Drain to Source Voltage




Figure 11. Unclamped Inductive Switching Capability




Figure 12. Maximum Continuous Drain Current vs. Case Temperature




Figure 13. Forward Bias Safe Operating Area




Figure 14. Single Pulse Maximum Power Dissipation

# FDMD8430

TYPICAL CHARACTERISTICS  $T_J = 25^\circ\text{C}$  unless otherwise noted.






Figure 15. Junction-to-Case Transient Thermal Response Curve




PQFN8 3.30x5.00x0.75, 0.65P  
CASE 483AU  
ISSUE B


DATE 19 APR 2024




TOP VIEW




FRONT VIEW



BOTTOM VIEW



DETAIL A  
SCALE: 2X



RECOMMENDED LAND PAD

NOTES: UNLESS OTHERWISE SPECIFIED  
A) DOES NOT FULLY CONFORM TO JEDEC REGISTRATION, MO229 DATED 8/2012.  
B) ALL DIMENSIONS ARE IN MILLIMETERS.  
C) DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH. MOLD FLASH OR BURRS DOES NOT EXCEED 0.10MM.  
D) DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.  
E) IT IS RECOMMENDED TO HAVE NO TRACES OR VIAS WITHIN THE KEEP OUT AREA.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.70	0.75	0.80
A1	0.00	-	0.05
A3	0.20 REF		
b	0.27	0.32	0.37
D	3.20	3.30	3.40
D2	2.04	2.14	2.24
D3	1.22	1.32	1.42
D4	0.48	0.58	0.68
E	4.90	5.00	5.10
E2	2.40	2.50	2.60
E3	1.56 REF		
E4	0.10	0.20	0.30
e	0.65 BSC		
k	0.30	0.40	0.50
L	0.44	0.54	0.64
L4	1.04	1.14	1.24
L5	0.75	0.85	0.95
z	0.51 REF		

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

DOCUMENT NUMBER:	98AON13669G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	PQFN8 3.30x5.00x0.75, 0.65P	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)