

Is Now Part of



# **ON Semiconductor**®

# To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="mailto:www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to <a href="mailto:Fairchild\_questions@onsemi.com">Fairchild\_questions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.



SEMICONDUCTOR®

### November 2013

## FQPF2N70


### **N-Channel QFET<sup>®</sup> MOSFET** 700 V, 2.0 A, 6.3 Ω


### Description

This N-Channel enhancement mode power MOSFET is produced using Fairchild Semiconductor's proprietary planar stripe and DMOS technology. This advanced MOSFET technology has been especially tailored to reduce on-state resistance, and to provide superior switching performance and high avalanche energy strength. These devices are suitable for switched mode power supplies, active power factor correction (PFC), and electronic lamp ballasts.

### Features

- 2.0 A, 700 V,  $R_{DS(on)}$  = 6.3  $\Omega$  (Max.) @  $V_{GS}$  = 10 V,  $I_{D}$  = 1.0 A
- Low Gate Charge (Typ. 9 nC)
- Low Crss (Typ. 5 pF)
- 100% Avalanche Tested





### Absolute Maximum Ratings T<sub>c</sub> = 25°C unless otherwise noted.


Symbol		Parameter		FQPF2N70	Unit
V <sub>DSS</sub>	Drain-Source Voltage			700	V
I <sub>D</sub>	Drain Current	- Continuous (T <sub>C</sub> = 25°C)		2.0*	Α
		- Continuous (T <sub>C</sub> = 100°C)		1.3*	А
I <sub>DM</sub>	Drain Current	- Pulsed	(Note 1)	8.0*	Α
V <sub>GSS</sub>	Gate-Source Voltage		± 30	V	
E <sub>AS</sub>	Single Pulsed Avalanche Energy (Note 2)		140	mJ	
I <sub>AR</sub>	Avalanche Current (Note 1)		(Note 1)	2.0	А
E <sub>AR</sub>	Repetitive Avalanche Energy (Note 1)		2.8	mJ	
dv/dt	Peak Diode Recovery dv/dt (Note 3)		4.5	V/ns	
P <sub>D</sub>	Power Dissipation	(T <sub>C</sub> = 25°C)		28	W
		- Derate Above 25°C		0.22	W/°C
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Temperature Range		-55 to +150	°C	
Τ <sub>L</sub>	Maximum Lead Temperature for Soldering, 1/8" from Case for 5 seconds			300	°C


\*Drain current limited by maximum junction temperature.


### **Thermal Characteristics**


Symbol	Parameter	FQPF2N70	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case, Max.	4.46	°C/W
$R_{ extsf{ heta}JA}$	Thermal Resistance, Junction-to-Ambient, Max.	62.5	0,00


Part Nu	nber	Top Mark	Package	Packing Method	Reel Size	Та	e Width	Qu	antity
FQPF2	N70	FQPF2N70	TO-220F	Tube	N/A		N/A	50	) units
lectric	al Ch	naracteristics	T <sub>c</sub> = 25°	C unless otherwise no	oted				
Symbol		Parameter		Test Conditi	1	Min.	Тур.	Max.	Unit
Off Cha			14	V <sub>GS</sub> = 0 V, I <sub>D</sub> = 250 μ	٨	700			
BV <sub>DSS</sub> ABV <sub>DSS</sub>		Source Breakdown Vo	0	ν <sub>GS</sub> – 0 ν, 1 <sub>D</sub> – 250 μ	A	700			V
ΔDV <sub>DSS</sub> ΔT <sub>J</sub>	Breako	lown Voltage Tempera ient	ature	$I_D = 250 \ \mu A$ , Referen			0.4		V/°C
DSS	Zero Gate Voltage Drain Current		rent	$V_{DS}$ = 700 V, $V_{GS}$ = 0				10	μA
	2010 0	ale voltage Brain ou	Tont	$V_{DS}$ = 560 V, $T_{C}$ = 12				100	μΑ
GSSF		ody Leakage Current		$V_{GS}$ = 30 V, $V_{DS}$ = 0 V				100	nA
GSSR	Gate-E	ody Leakage Current	, Reverse	$V_{GS}$ = -30 V, $V_{DS}$ = 0 V				-100	nA
On Cha	racter	istics							
V <sub>GS(th)</sub>	Gate T	hreshold Voltage		$V_{DS} = V_{GS}, I_D = 250$	μΑ	3.0		5.0	V
R <sub>DS(on)</sub>		Drain-Source sistance		V <sub>GS</sub> = 10 V, I <sub>D</sub> = 1.0 A	4		5.0	6.3	Ω
JFS	Forwar	d Transconductance		V <sub>DS</sub> = 50 V, I <sub>D</sub> = 1.0 /	٩		2.45		S
C <sub>iss</sub> C <sub>oss</sub> C <sub>rss</sub>	Output	Capacitance Capacitance Se Transfer Capacitan	се	V <sub>DS</sub> = 25 V, V <sub>GS</sub> = 0 f = 1.0 MHz	V,		270 38 5	350 50 7	pF pF pF
Switchi	na Ch	aracteristics							
d(on)	-	n Delay Time						30	ns
r		n Rise Time		$V_{DD}$ = 350 V, I <sub>D</sub> = 2.0 A, R <sub>G</sub> = 25 Ω				80	ns
d(off)		ff Delay Time						50	ns
f		ff Fall Time		0	(Note 4)			70	ns
ן ל <sup>מ</sup>		ate Charge		V <sub>DS</sub> = 560 V, I <sub>D</sub> = 2.0	Δ		8.1	11	nC
λ <sub>gs</sub>		ource Charge		V <sub>DS</sub> = 500 V, I <sub>D</sub> = 2.0 A, V <sub>GS</sub> = 10 V			1.7		nC
Q <sub>gd</sub>		rain Charge			(Note 4)		4.4		nC
Drain-S	ource	<b>Diode Characte</b>	ristics an	d Maximum Rati	ngs				
S	Maxim	um Continuous Drain	Source Diod	le Forward Current				2.0	Α
SM	Maxim	um Pulsed Drain-Sou	rce Diode Fo	orward Current			/	8.0	Α
/ <sub>SD</sub>	Drain-S	Source Diode Forward	l Voltage	$V_{GS}$ = 0 V, I <sub>S</sub> = 2.0 A				1.4	V
'n	Revers	e Recovery Time		$V_{GS}$ = 0 V, I <sub>S</sub> = 2.0 A	,		260		ns
ຊ <sub>rr</sub>	Revers	e Recovery Charge		$dI_F$ / $dt$ = 100 A/µs			1.09	-	μC
	<sub>AS</sub> = 2.0 A,	-width limited by maximum ju V <sub>DD</sub> = 50 V, R <sub>G</sub> = 25 Ω, star		ure.					











http://www.fairchildsemi.com/package/packageDetails.html?id=PN\_TF220-003

FQPF2N70 — N-Channel QFET<sup>®</sup> MOSFET



SEMICONDUCTOR

#### TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

1			
	AccuPower™	F-PFS™	-215
	AX-CAP <sup>®</sup> *	FRFET <sup>®</sup>	
	BitSiC™	Global Power Resource <sup>SM</sup>	PowerTrench <sup>®</sup>
	Build it Now™	GreenBridge™	PowerXS™
	CorePLUS™	Green FPS™	Programmable Active Droop™
	CorePOWER™	Green FPS™ e-Series™	QFET®
	CROSSVOLT™	Gmax™	QS™
	CTL™	GTO™	Quiet Series™
	Current Transfer Logic™	IntelliMAX™	RapidConfigure™
	DEUXPEED®	ISOPLANAR™	
	Dual Cool™	Marking Small Speakers Sound Louder	
	EcoSPARK <sup>®</sup>	and Better™	Saving our world, 1mW/W/kW at a time™
	EfficentMax™	MegaBuck™	SignalWise™
	ESBC™	MICROCOUPLER™	SmartMax™
	<b>F</b> B	MicroFET™	SMART START™
	+	MicroPak™	Solutions for Your Success™
	Fairchild <sup>®</sup>	MicroPak2™	SPM®
	Fairchild Semiconductor®	MillerDrive™	STEALTH™
	FACT Quiet Series™	MotionMax™	SuperFET®
	FACT®	mWSaver®	SuperSOT™-3
	FAST <sup>®</sup>	OptoHiT™	SuperSOT™-6
	FastvCore™	OPTOLOGIC®	SuperSOT <sup>™</sup> -8
	FETBench™	OPTOPLANAR®	SupreMOS®
	FPS™		SyncFET™

\*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

#### DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

- Life support devices or systems are devices or systems which, (a) are 1. intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Sync-Lock™ SYSTEM<sup>®\*</sup> GENERAL

TinyBoost

TinyBuck®

TinyCalc™ TinyLogic® TINYOPTO™ TinvPower™ TinyPWM™

TinyWire™

TranSiC™

UHC® Ultra FRFET™ UniFFT™ VCX™ VisualMax™

XS™

VoltagePlus™

TriFault Detect™

TRUECURRENT®\* µSerDes™ 

#### ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.Fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

#### PRODUCT STATUS DEFINITIONS Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death a

### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC