

NTAT6H406N

MOSFET – N-Channel

80 V, 2.9 mΩ, 175 A

Features

- Low On-Resistance
- High Current Capability
- 100% Avalanche Tested
- ATPAK Package is Pin-compatible with DPAK (TO-252)
- Pb-Free, Halogen Free and RoHS Compliance

Typical Applications

- Multi Lib Protection
- Motor Control

Specifications

Table 1. ABSOLUTE MAXIMUM RATING at $T_A = 25^\circ\text{C}$

Parameter	Symbol	Value	Unit
Drain to Source Voltage	V_{DS}	80	V
Gate to Source Voltage	V_{GS}	± 20	V
Drain Current (DC)	I_D	175	A
Drain Current (Pulse) $PW \leq 10 \text{ ms}$, Duty Cycle $\leq 1\%$	I_{DP}	600	A
Power Dissipation $T_C = 25^\circ\text{C}$	P_D	90	W
Operating Junction and Storage Temperature	T_J, T_{STG}	-55 to $+150$	$^\circ\text{C}$
Single Pulse Drain to Source Avalanche Energy ($L = 0.1 \text{ mH}$, $I_{L(pk)} = 55 \text{ A}$)	E_{AS}	151	mJ
Lead Temperature for Soldering Purposes, 3 mm from Case for 10 seconds	T_L	260	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

Table 2. THERMAL RESISTANCE RATINGS

Parameter	Symbol	Value	Unit
Junction to Case Steady State ($T_C = 25^\circ\text{C}$)	$R_{\theta JC}$	1.38	$^\circ\text{C/W}$
Junction to Ambient (Note 1)	$R_{\theta JA}$	77.2	$^\circ\text{C/W}$

1. Surface mounted on FR4 board using a 130 mm², 1 oz. Cu pad.





ON Semiconductor®

www.onsemi.com


V_{DS}	$R_{DS(on)}$ Max	I_D Max
80 V	2.9 mΩ @ 10V	175 A

ELECTRICAL CONNECTION N-Channel



**DPAK / ATPAK
CASE 369AM**

MARKING DIAGRAM



ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet.

NTAT6H406N

Table 3. ELECTRICAL CHARACTERISTICS at $T_A = 25^\circ\text{C}$

Parameter	Symbol	Conditions	Value			Unit
			min	typ	max	
Drain to Source Breakdown Voltage	$V_{(BR)DSS}$	$I_D = 1\text{ mA}, V_{GS} = 0\text{ V}$	80			V
Zero-Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 80\text{ V}, V_{GS} = 0\text{ V}$			10	μA
Gate to Source Leakage Current	I_{GSS}	$V_{GS} = \pm 20\text{ V}, V_{DS} = 0\text{ V}$			± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = 10\text{ V}, I_D = 1\text{ mA}$	2.0		4.0	V
Forward Transconductance	g_{FS}	$V_{DS} = 10\text{ V}, I_D = 50\text{ A}$		185		S
Static Drain to Source On-State Resistance	$R_{DS(on)}$	$I_D = 50\text{ A}, V_{GS} = 10\text{ V}$		2.2	2.9	$\text{m}\Omega$
Input Capacitance	C_{ISS}	$V_{DS} = 40\text{ V}, f = 1\text{ MHz}$		8040		pF
Output Capacitance	C_{OSS}			1120		pF
Reverse Transfer Capacitance	C_{RSS}			40		pF
Turn-ON Delay Time	$t_d(on)$	$V_{GS} = 10\text{ V}, V_{DS} = 48\text{ V},$ $I_D = 50\text{ A}, R_G = 50\text{ }\Omega,$		77		ns
Rise Time	t_r			420		ns
Turn-OFF Delay Time	$t_d(off)$			310		ns
Fall Time	t_f			155		ns
Total Gate Charge	Q_G	$V_{DS} = 48\text{ V}, V_{GS} = 10\text{ V},$ $I_D = 50\text{ A}$		110		nC
Gate to Source Charge	Q_{GS}			32.4		nC
Gate to Drain "Miller" Charge	Q_{GD}			31.8		nC
Forward Diode Voltage	V_{SD}	$I_S = 100\text{ A}, V_{GS} = 0\text{ V}$		0.9	1.5	V
Reverse Recovery Time	t_{RR}	$I_S = 50\text{ A}, V_{GS} = 0\text{ V},$ $dI/dt = 100\text{ A}/\mu\text{s}$		90		ns
Reverse Recovery Charge	Q_{RR}			126		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate to Source Voltage




Figure 4. On-Resistance vs. Case Temperature




Figure 5. Diode Forward Voltage vs. Current




Figure 6. Switching Time vs. Drain Current

TYPICAL CHARACTERISTICS (continued)




Figure 7. Capacitance Variation




Figure 8. Gate to Source Voltage vs. Total Charge




Figure 9. Safe Operating Area




Figure 10. Power Dissipation vs. Case Temperature





Figure 11. Thermal Response

DPAK (Single Gauge) / ATPAK
CASE 369AM
ISSUE O

DATE 29 FEB 2012



Pin2 is idle pin with electrical
designation only carried

DOCUMENT NUMBER:	98AON67243E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	DPAK (SINGLE GAUGE) / ATPAK	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales