NTQS6463

Power MOSFET

-20 V, -6.8 A, P-Channel TSSOP-8

Features

- New Low Profile TSSOP-8 Package
- Ultra Low R_{DS(on)}
- Higher Efficiency Extending Battery Life
- Logic Level Gate Drive
- Diode Exhibits High Speed, Soft Recovery
- Avalanche Energy Specified
- $\bullet \ \ I_{DSS}$ and $V_{DS(on)}$ Specified at Elevated Temperatures

Applications

- Power Management in Portable and Battery-Powered Products, i.e.: Computers, Printers, PCMCIA Cards, Cellular and Cordless Telephones
- Lithium Ion Battery Applications
- Note Book PC

MAXIMUM RATINGS (T_C = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	-20	V
Gate-to-Source Voltage	V_{GS}	±12	V
Drain Current (Note 1) - Continuous @ T _A = 25°C - Continuous @ T _A = 70°C - Pulsed (Note 3)	I _D I _D I _{DM}	-5.5 -4.4 ±30	A
Total Power Dissipation (Note 1) @ T _A = 25°C	P _D	0.93	W
Drain Current (Note 2) - Continuous @ T _A = 25°C - Continuous @ T _A = 70°C - Pulsed (Note 3)	I _D I _D	-6.8 -5.4 ±30	A
Total Power Dissipation (Note 2) @ T _A = 25°C	P _D	1.39	W
Operating and Storage Temperature Range	T _J , T _{stg}	-55 to +150	°C
Single Pulse Drain–to–Source Avalanche Energy – Starting $T_J = 25^{\circ}C$ ($V_{DD} = 40 \text{ V}, I_L = 18.4 \text{ A},$ $L = 5.0 \text{ mH}, R_G = 25 \Omega$)	E _{AS}	845	mJ
Thermal Resistance – Junction–to–Ambient (Note 1) Junction–to–Ambient (Note 2)	$R_{ heta JA}$	134 90	°C/W

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

- 1. Minimum 3" X 3" FR-4 board, steady state.
- 2. Mounted on 1" square (1 oz.) board, steady state.
- 3. Pulse Test: Pulse Width = 300 μs, Duty Cycle = 2%.




ON Semiconductor®

http://onsemi.com

V _{DSS}	R _{DS(on)} TYP	I _D MAX
-20 V	20 mΩ @ –10 V	-6.8 A

P-Channel



MARKING DIAGRAM



463 = Device Code Y = Year WW = Work Week N = MOSFET

PIN ASSIGNMENT



ORDERING INFORMATION

Device	Package	Shipping [†]
NTQS6463	TSSOP-8	100 Units/Rail
NTQS6463R2	TSSOP-8	3000/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.


NTQS6463

$\textbf{ELECTRICAL CHARACTERISTICS} \ (T_J = 25^{\circ}C \ unless \ otherwise \ noted)$

Characteri	Symbol	Min	Тур	Max	Unit	
STATIC						
Gate Threshold Voltage ($V_{DS} = V_{GS}$, $I_D =$	V _{GS(th)}	-0.45	-0.9	-	V	
Gate-Body Leakage ($V_{GS} = 0 \text{ V}, V_{GS} = \pm$	8 V)	I _{GSS}	-	_	±100	nA
Zero Gate Threshold Voltage Drain Current $(V_{DS} = -16 \text{ V}, V_{GS} = 0 \text{ V})$ $(V_{DS} = -16 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 70 ^{\circ}\text{C})$		I _{DSS}	- -	_ _	-1.0 -10	μΑ
Drain–Source On–State Resistance (Note 4) $(V_{GS} = -4.5 \text{ V}, I_D = -6.8 \text{ A})$ $(V_{GS} = -2.5 \text{ V}, I_D = -5.5 \text{ A})$		R _{DS(on)}		0.016 0.022	0.020 0.027	Ω
Forward Transconductance ($V_{DS} = -15 \text{ V}, I_D = -6.8 \text{ A}$) (Note 4)		9FS	_	21	-	S
Diode Forward Voltage (I _S = -1.3 A, V _{GS} = 0 V) (Note 4)		V_{SD}	_	-0.71	-1.1	V
DYNAMIC						
Total Gate Charge	$(V_{DS} = -10 \text{ V}, V_{GS} = -5.0 \text{ V},$	Q_g	_	28	50	nC
Gate-Source Charge		Q_{gs}	-	5.5	-	
Gate-Drain Charge	$I_D = -6.8 \text{ A}$	Q _{gd}	-	9.0	-	
Turn-On Delay Time	$(V_{DD} = -10 \text{ V}, I_{D} \cong -1.0 \text{ A}, V_{GS} = -4.5 \text{ V}, I_{D} \cong -0.0 \text{ C}$	t _{d(on)}	-	15	25	ns
Rise Time		t _r	-	22	40	
Turn-Off Delay Time		t _{d(off)}	_	90	150	
Fall Time	$R_G = 6.0 \Omega$)	t _f	-	53	90	
Source-Drain Reverse Recovery Time	$(I_F = -1.3 \text{ A, di/dt} = 100 \text{ A/}\mu\text{s})$	t _{rr}	_	45	80	ns

^{4.} Pulse Test: Pulse Width \leq 300 μ s, Duty Cycle \leq 2%.

NTQS6463



0.01

Figure 3. On-Resistance versus Gate-to-Source Voltage

-VGS, GATE-TO-SOURCE VOLTAGE (V)

0

2





Figure 5. On-Resistance Variation versus **Temperature**



-I_D, DRAIN CURRENT (A)

14

6




Figure 6. Drain-to-Source Leakage Current versus Voltage

POWER MOSFET SWITCHING

Switching behavior is most easily modeled and predicted by recognizing that the power MOSFET is charge controlled. The lengths of various switching intervals (Δt) are determined by how fast the FET input capacitance can be charged by current from the generator.

The published capacitance data is difficult to use for calculating rise and fall because drain–gate capacitance varies greatly with applied voltage. Accordingly, gate charge data is used. In most cases, a satisfactory estimate of average input current ($I_{G(AV)}$) can be made from a rudimentary analysis of the drive circuit so that

$$t = Q/I_{G(AV)}$$

During the rise and fall time interval when switching a resistive load, V_{GS} remains virtually constant at a level known as the plateau voltage, V_{SGP} . Therefore, rise and fall times may be approximated by the following:

$$t_r = Q_2 x R_G/(V_{GG} - V_{GSP})$$

$$t_f = Q_2 x R_G/V_{GSP}$$

where

 V_{GG} = the gate drive voltage, which varies from zero to V_{GG} R_G = the gate drive resistance

and Q₂ and V_{GSP} are read from the gate charge curve.


During the turn-on and turn-off delay times, gate current is not constant. The simplest calculation uses appropriate values from the capacitance curves in a standard equation for voltage change in an RC network. The equations are:

$$\begin{split} t_{d(on)} &= R_G \ C_{iss} \ In \ [V_{GG}/(V_{GG} - V_{GSP})] \\ t_{d(off)} &= R_G \ C_{iss} \ In \ (V_{GG}/V_{GSP}) \end{split}$$

The capacitance (C_{iss}) is read from the capacitance curve at a voltage corresponding to the off–state condition when calculating $t_{d(on)}$ and is read at a voltage corresponding to the on–state when calculating $t_{d(off)}$.

At high switching speeds, parasitic circuit elements complicate the analysis. The inductance of the MOSFET source lead, inside the package and in the circuit wiring which is common to both the drain and gate current paths, produces a voltage at the source which reduces the gate drive current. The voltage is determined by Ldi/dt, but since di/dt is a function of drain current, the mathematical solution is complex. The MOSFET output capacitance also complicates the mathematics. And finally, MOSFETs have finite internal gate resistance which effectively adds to the resistance of the driving source, but the internal resistance is difficult to measure and, consequently, is not specified.

The resistive switching time variation versus gate resistance (Figure 9) shows how typical switching performance is affected by the parasitic circuit elements. If the parasitics were not present, the slope of the curves would maintain a value of unity regardless of the switching speed. The circuit used to obtain the data is constructed to minimize common inductance in the drain and gate circuit loops and is believed readily achievable with board mounted components. Most power electronic loads are inductive; the data in the figure is taken with a resistive load, which approximates an optimally snubbed inductive load. Power MOSFETs may be safely operated into an inductive load; however, snubbing reduces switching losses.



GATE-TO-SOURCE OR DRAIN-TO-SOURCE VOLTAGE (V)

Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage versus Total Charge




Figure 9. Resistive Switching Time Variation versus Gate Resistance




Figure 10. Diode Forward Voltage versus Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area

SAFE OPERATING AREA

The Forward Biased Safe Operating Area curves define the maximum simultaneous drain—to—source voltage and drain current that a transistor can handle safely when it is forward biased. Curves are based upon maximum peak junction temperature and a case temperature (T_C) of 25°C. Peak repetitive pulsed power limits are determined by using the thermal response data in conjunction with the procedures discussed in AN569, "Transient Thermal Resistance — General Data and Its Use."

Switching between the off–state and the on–state may traverse any load line provided neither rated peak current (I_{DM}) nor rated voltage (V_{DSS}) is exceeded and the transition time (t_r , t_f) do not exceed 10 μs . In addition the total power averaged over a complete switching cycle must not exceed ($T_{J(MAX)} - T_C$)/($R_{\theta JC}$).

A Power MOSFET designated E-FET can be safely used in switching circuits with unclamped inductive loads. For reliable operation, the stored energy from circuit inductance dissipated in the transistor while in avalanche must be less than the rated limit and adjusted for operating conditions differing from those specified. Although industry practice is to rate in terms of energy, avalanche energy capability is not a constant. The energy rating decreases non–linearly with an increase of peak current in avalanche and peak junction temperature.


Although many E–FETs can withstand the stress of drain–to–source avalanche at currents up to rated pulsed current (I_{DM}), the energy rating is specified at rated continuous current (I_{D}), in accordance with industry custom. The energy rating must be derated for temperature. Maximum energy at currents below rated continuous I_{D} can safely be assumed to equal the values indicated.






TSSOP-8 CASE 948S **ISSUE C**

DATE 20 JUN 2008





- IOTES:

 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

 2. CONTROLLING DIMENSION: MILLIMETER.

 3. DIMENSION A DOES NOT INCLUDE MOLD FLASH. PROTRUSIONS OR GATE BURRS. MOLD FLASH OR GATE BURRS SHALL NOT EXCEED 0.15 (0.006) PER SIDE.
 DIMENSION B DOES NOT INCLUDE INTERLEAD
- FLASH OR PROTRUSION. INTERLEAD FLASH OR PROTRUSION SHALL NOT EXCEED 0.25 (0.010) PER SIDE.
 TERMINAL NUMBERS ARE SHOWN FOR
- REFERENCE ONLY.
 DIMENSION A AND B ARE TO BE DETERMINED AT DATUM PLANE -W-.

	MILLIMETERS		ETERS INCHES		
DIM	MIN	MAX	MIN	MAX	
Α	2.90	3.10	0.114	0.122	
В	4.30	4.50	0.169	0.177	
С		1.10		0.043	
D	0.05	0.15	0.002	0.006	
F	0.50	0.70	0.020	0.028	
G	0.65 BSC		0.026 BSC		
J	0.09	0.20	0.004	0.008	
J1	0.09	0.16	0.004	0.006	
K	0.19	0.30	0.007	0.012	
K1	0.19	0.25	0.007	0.010	
L	6.40 BSC		0.252		
M	0°	8°	0°	8°	

GENERIC MARKING DIAGRAM*



XXX = Specific Device Code = Assembly Location Α

= Year ww = Work Week = Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON00697D	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	TSSOP-8		PAGE 1 OF 1	

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales