

Use of NCP81172 for Extended Output Voltage Range



ON Semiconductor®

<http://onsemi.com>

Introduction

The NCP81172 is a general-purpose two-phase synchronous buck controller, which has a typical application circuit as shown in Figure 1 if PWM-VID function is not employed. In Figure 1, the voltage V_{REFIN} at REFIN pin is the reference voltage for regulation of output voltage V_{OUT} , i.e. $V_{OUT} = V_{REFIN} \cdot V_{REFIN}$. V_{REFIN} is always lower than the voltage V_{REF} having a typical value of 2 V. As a result of

APPLICATION NOTE

that, V_{OUT} cannot be higher than 2 V. To support applications with extended output voltage range, an application solution is illustrated in this application note.




Figure 1. Typical Application Circuit for $V_{OUT} < 2$ V

Solution Description

Figure 2 shows a proposed solution for extended output voltage range. The major difference from the solution of Figure 1 is that an additional resistor R_{FB2} is applied between FB pin and FBRTN pin, which boosts output voltage to be higher than the voltage set at REFIN pin.

In steady-state operation, the voltage difference between REFIN and GND is equal to the voltage difference between FB and FBRTN. Hence, the output voltage V_{OUT} is given by

$$V_{OUT} = V_{REFIN} \cdot \frac{R_{FB1} + R_{FB2}}{R_{FB2}} \quad (\text{eq. 1})$$

where the REFIN voltage V_{REFIN} is set by the resistor divider at REFIN pin:

$$V_{REFIN} = V_{REF} \cdot \frac{R_{VREF2}}{R_{VREF1} + R_{VREF2}} \quad (\text{eq. 2})$$




Figure 2. Application Circuit for Extended Output Voltage Range

One thing needs to mention, the NCP81172 is not designed for 2-phase applications in which conversion ratio V_{OUT}/V_{IN} is over 0.45. In another word, V_{IN} has to be higher than about 2.3 times of V_{OUT} in 2-phase mode to assure stable operation. However, the 1-phase operation does not have this limitation.

Design Guideline

1. REFIN Voltage Programming

The NCP81172 has an output over voltage protection function, which is based on voltage detection at FB pin. The over voltage threshold is equal to VREF having a typical value of 2 V. The maximum acceptable REFIN voltage can be defined by a predetermined over voltage threshold K_{OV} , e.g. 130%.

$$V_{REFIN} = \frac{V_{VREF}}{K_{OV}} \quad (\text{eq. 3})$$

Select resistance values for R_{VREF1} and R_{VREF2} to get the appropriate REFIN voltage, and make the total resistance value of the two resistors in a range from 5 k Ω to 50 k Ω .

2. Output Voltage Programming

After REFIN voltage is defined, the output voltage programming can be done by designing the feedback divider comprised of R_{FB1} and R_{FB2} . Usually R_{FB1} is arbitrarily selected in a range from 1 k Ω to 50 k Ω , and then R_{FB2} can be obtained by

$$R_{FB2} = R_{FB1} \cdot \frac{V_{REFIN}}{V_{OUT} - V_{REFIN}} \quad (\text{eq. 4})$$

3. Switching Frequency Programming

Switching frequency of the NCP81172 is programmed by a resistor R_{FS} applied from FS pin to ground. The typical switching frequency range is from 200 kHz to 800 kHz. Figure 3 shows a measurement based on a typical application under a condition of $V_{IN} = 12$ V, $V_{OUT} = V_{REFIN} = 1.0$ V, $I_{OUT} = 20$ A for PS0 mode operation (2-phase) and $I_{OUT} = 10$ A for PS1 mode operation (1-phase).




Figure 3. Switching Frequency Programmed by R_{FS} under Condition of $V_{OUT} = V_{REFIN} = 1.0$ V

The PWM control of the NCP81172, ramp pulse modulation (RPM), is one kind of ripple regulators. The three major determinant factors for the average PWM on time are input supply voltage V_{IN} , $REFIN$ voltage V_{REFIN} , and frequency programming resistor R_{FS} . The NCP81172 has a built-in V_{IN} feedforward function in internal ramp signal in order to reduce frequency variation caused by variable supply voltage, and it is not a concern in this application note. In applications with $V_{OUT} = V_{REFIN}$, PWM on time is proportional to V_{OUT} such that frequency maintains quasi constant when V_{OUT} changes if R_{FS} is fixed. Due to this reason, Figure 3 can be used as a frequency

programming reference for applications with $V_{OUT} = V_{REFIN}$.

However, situation changes in applications where V_{OUT} regulation level is higher than V_{REFIN} level, i.e. $V_{OUT} > V_{REFIN}$. The PWM on time does not change much over V_{OUT} level programming by means of adjusting R_{FB} at FB pin without any change in either R_{FS} or V_{REFIN} , therefore, the higher V_{OUT} level the higher switching frequency. Figure 4 shows an exemplary measurement under a condition of $V_{REFIN} = 1.0$ V, $R_{FS} = 62$ k Ω , and V_{OUT} changing from 1.0 V to 3.3 V by adjusting R_{FB} .





Figure 4. Switching Frequency Changes with V_{OUT} Programming under Condition of V_{REFIN} = 1.0 V and R_{FS} = 62 kΩ

To provide a guide for frequency programming in applications with V_{OUT} > V_{REFIN}, the switching frequency in PS0 mode operation (2-phase) can be estimated by

$$F_{SW(kHz)} = 6500 \cdot R_{FS(k\Omega)}^{-0.7} \cdot \left(\frac{V_{OUT}}{V_{REFIN}} \right)^{0.5} \quad (\text{eq. 5})$$

and the switching frequency in PS1 mode operation (1-phase) can be estimated by

$$F_{SW(kHz)} = 8500 \cdot R_{FS(k\Omega)}^{-0.77} \cdot \left(\frac{V_{OUT}}{V_{REFIN}} \right)^{0.83} \quad (\text{eq. 6})$$

ON Semiconductor and the  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative