



**Material Composition Declaration**  
 © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

1752-21.1	IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information
-----------	--	---------------------------	---

**Supplier Information**

<b>Company name*</b> On Semiconductor	Company unique ID	Unique ID Authority	<b>Response Date*</b> 2020-12-01
<b>Contact Name</b> Product-Env-Stewards	Title - Contact Product Enviro Compliance	<b>Phone - Contact*</b> NA	<b>Email - Contact*</b> Product-Env-Stewards@onsemi.com
<b>Authorized Representative*</b> Product-Env-Stewards	Title - Representative Product Enviro Compliance	<b>Phone - Representative*</b> NA	<b>Email - Representative*</b> Product-Env-Stewards@onsemi.com

Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
	AR1335HSSC11SMF A0-DRBR-E	13MP 1/3 CIS SO	2020-12-01		TA1	274.4	mg	Each

**Manufacturing Process Information**

Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating	Peak Process Body Temperature	Max Time at Peak Temperature	Number of Reflow Cycles
SnAgCu	CU Alloy	4	260 C	30 seconds	3

Comments

**For more information regarding material composition please refer to page 3**

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a "RoHS restricted substance") in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
RoHS Declaration *	5 - Item(s) is obsolete, no information is available		Supplier Acceptance * Accepted
<p><b>Exemption: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.</b></p>			
Exemption List Version	EL-2011/534/EU		
<b>Declaration Signature</b>			
<p><b>Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.</b></p>			
Supplier Digital Signature	Rastislav Drska		

**Homogeneous Material Composition Declaration for Electronic Products**

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Ceramic Substrate	182.0	mg	Supplier	Cobalt (Co)	7440-48-4		0.273	mg
			Supplier	Titanium Dioxide (TiO2)	13463-67-7		4.55	mg
			Supplier	Tungsten (W)	7440-33-7		0.455	mg
			Supplier	Magnesium Monoxide (MgO)	1309-48-4		3.64	mg
			Supplier	Calcium Oxide (CaO)	60873-85-0		0.728	mg
			Supplier	Silica Amorphous (SiO2)	7631-86-9		0.728	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		165.3925	mg
			B	Nickel (Ni)	7440-02-0		0.182	mg
			Supplier	Gold (Au)	7440-57-5		0.546	mg
			Supplier	Thallium (Tl)	82870-81-3		0.0455	mg
			Supplier	Chromium Trioxide (Cr2O3)	1308-38-9		5.46	mg
Die	20.7	mg		Misc.	proprietary data		0.0787	mg
			Supplier	Silicon (Si)	7440-21-3		20.4164	mg
			Supplier	Aluminum (Al)	7429-90-5		0.2049	mg
Die Attach	5.1	mg	Supplier	Silver (Ag)	7440-22-4		3.57	mg
			Supplier	Epoxy resins	129915-35-1		1.1475	mg
			Supplier	Gamma-Butyrolactone	96-48-0		0.3825	mg
Imaging Lens	56.0	mg	Supplier	Titanium Dioxide (TiO2)	13463-67-7		2.8	mg
			Supplier	Sodium Monoxide (Na2O)	1313-59-3		2.8	mg
			Supplier	Boron Trioxide (B2O3)	1303-86-2		2.8	mg
			Supplier	Zinc Monoxide (ZnO)	1314-13-2		2.8	mg
			B	Antimony Trioxide (Sb2O3)	1309-64-4		0.28	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		2.8	mg
			Supplier	Potassium Monoxide (K2O)	12136-45-7		2.8	mg
			Supplier	Silica Crystalline (SiO2)	14808-60-7		38.92	mg
Lid Attach	6.25	mg		Other Additive Agents	proprietary data		0.9375	mg
			Supplier	Photoinitiator	Proprietary Data		2.125	mg
			Supplier	Epoxy Prepolymer	Proprietary Data		3.1875	mg
Marking Ink	4.0	mg	Supplier	Bisphenol A_Epichlorohydrin polymer	25068-38-6		0.5	mg
			Supplier	1-Methoxy-2-propyl acetate (MPA)	108-65-6		1	mg
			Supplier	Butylglycol Acetate	112-07-2		1	mg
			Supplier	Solvent Naphtha (Solvent oil)	64742-94-5		0.5	mg

			Supplier	Cyclohexanone	108-94-1		0.5	mg
			Supplier	Xylene	1330-20-7		0.5	mg
Wire Bond - Au	0.35	mg	Supplier	Gold (Au)	7440-57-5		0.35	mg