



**Material Composition Declaration**  
 © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

1752-21.1	IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>	Form Type * Distribute	Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information
-----------	--	---------------------------	---

**Supplier Information**

<b>Company name*</b> <b>On Semiconductor</b>	Company unique ID	Unique ID Authority	<b>Response Date*</b> <b>2021-01-27</b>
<b>Contact Name</b> <b>Product-Env-Stewards</b>	Title - Contact Product Enviro Compliance	<b>Phone - Contact*</b> NA	<b>Email - Contact*</b> <b>Product-Env-Stewards@onsemi.com</b>
<b>Authorized Representative*</b> <b>Product-Env-Stewards</b>	Title - Representative Product Enviro Compliance	<b>Phone - Representative*</b> NA	<b>Email - Representative*</b> <b>Product-Env-Stewards@onsemi.com</b>


Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
	AR0144CSSC25SUK A0-CPBR	1MP 1/4 CIS SO	2021-01-27		TA1	57.72	mg	Each

**Manufacturing Process Information**

Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating	Peak Process Body Temperature	Max Time at Peak Temperature	Number of Reflow Cycles
<b>SnAgCu</b>	<b>CU Alloy</b>	<b>5</b>	<b>260</b> C	<b>30</b> seconds	<b>3</b>

Comments

**For more information regarding material composition please refer to page 3**

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a "RoHS restricted substance") in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
<b>RoHS Declaration *</b>	5 - Item(s) is obsolete, no information is available		<b>Supplier Acceptance *</b> Accepted
<b>Exemption: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.</b>			
Exemption List Version	EL-2011/534/EU		
<b>Declaration Signature</b>			
<b>Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.</b>			
Supplier Digital Signature	Rastislav Drska		

**Homogeneous Material Composition Declaration for Electronic Products**

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Die	9.53	mg		Misc.	proprietary data		0.0362	mg
			Supplier	Silicon (Si)	7440-21-3		9.3994	mg
			Supplier	Aluminum (Al)	7429-90-5		0.0943	mg
Die Attach	0.91	mg	Supplier	Bisphenol A_Epichlorohydrin polymer	25068-38-6		0.3413	mg
			Supplier	Ethylene Glycol	107-21-1		0.0091	mg
			Supplier	Sulfonium (Thiodi-4,1-phenylene)	89452-37-9		0.0273	mg
			Supplier	Modified Silicon Dioxide (SiO2)	67762-90-7		0.1911	mg
			Supplier	Formaldehyde Polymer	9003-36-5		0.3413	mg
Electrode	0.97	mg	Supplier	Titanium (Ti)	7440-32-6		0.0006	mg
			B	Nickel (Ni)	7440-02-0		0.5775	mg
			Supplier	Gold (Au)	7440-57-5		0.0233	mg
			Supplier	Copper (Cu)	7440-50-8		0.0146	mg
			Supplier	Aluminum (Al)	7429-90-5		0.354	mg
Glass Lid /Cap	40.57	mg	Supplier	Boron Trioxide (B2O3)	1303-86-2		5.7609	mg
			Supplier	Silica Amorphous (SiO2)	7631-86-9		20.285	mg
			Supplier	Barium Monoxide (BaO)	1304-28-5		9.7368	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		4.4627	mg
			Supplier	Calcium Monoxide (CaO)	1305-78-8		0.0406	mg
			B	Arsenic Trioxide (As2O3)	1327-53-3		0.284	mg
Lid Attach	0.01	mg		Photoinitiator	proprietary data		0.0025	mg
			Supplier	Epoxy Prepolymer	Proprietary Data		0.0075	mg
Resin Encapsulation	0.91	mg	Supplier	Pentaerythritol triacrylate	3524-68-3		0.1365	mg
			Supplier	2-(2-methoxypropoxy)propanol	34590-94-8		0.091	mg
			Supplier	Epoxy Phenol Novolak Resin	28064-14-4		0.091	mg
			Supplier	9-Phenylacridine	602-56-2		0.0455	mg
			Supplier	Bisphenol A_Epichlorohydrin polymer	25068-38-6		0.546	mg
Solder Ball	0.71	mg	Supplier	Silver (Ag)	7440-22-4		0.0543	mg
			Supplier	Tin (Sn)	7440-31-5		0.6397	mg
			Supplier	Copper (Cu)	7440-50-8		0.016	mg
Substrate and Solder Mask	4.11	mg	Supplier	Silica crystalline	14808-60-7, 14464-46-1		0.411	mg
			Supplier	Cured Resin of Solder Mask	Proprietary Data		1.9523	mg

			Supplier	Bismaleimide Triazine resin	Proprietary Data		1.7468	mg
--	--	--	----------	-----------------------------	------------------	--	--------	----