

 <b>Material Composition Declaration</b> © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.		This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.								
1752-21.1		IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>			Form Type * Distribute		Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information			
<b>Supplier Information</b>										
Company name* <b>onsemi</b>			Company unique ID		Unique ID Authority			Response Date* <b>2024-05-19</b>		
Contact Name <b>Product-Env-Stewards</b>			Title - Contact Product Enviro Compliance		Phone - Contact* <b>NA</b>			Email - Contact* <b>Product-Env-Stewards@onsemi.com</b>		
Authorized Representative* <b>Product-Env-Stewards</b>			Title - Representative Product Enviro Compliance		Phone - Representative* <b>NA</b>			Email - Representative* <b>Product-Env-Stewards@onsemi.com</b>		
	Requester Item Number	Mfr Item Number	Mfr Item Name		Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
		AR0147ATSC00XUE A5-DRBR	1MP 1/4 CIS SO		2024-05-19		MY5	182.002	mg	Each
<b>Manufacturing Process Information</b>										
	Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating		Peak Process Body Temperature		Max Time at Peak Temperature		Number of Reflow Cycles	
	<b>SnAgCu</b>	<b>CU Alloy</b>	<b>3</b>		<b>260</b> C		<b>30</b> seconds		<b>3</b>	
Comments										
<b>ATTENTION: MSL 3 Rated item requires Bake and Dry Pack (after electrical test)</b>										
<b>For more information regarding material composition please refer to page 3</b>										

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a “RoHS restricted substance”) in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier’s liability and the Company’s remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
RoHS Declaration *	1 - Item(s) does not contain RoHS restricted substances per the definition above		Supplier Acceptance * Accepted
<b>Exemption: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.</b>			
Exemption List Version	EL-2011/534/EU		
Declaration Signature			
<b>Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.</b>			
Supplier Digital Signature	Rastislav Drska		

## Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Die	18.4	mg		Misc.	proprietary data		0.0699	mg
			Supplier	Silicon (Si)	7440-21-3		18.1479	mg
			Supplier	Aluminum (Al)	7429-90-5		0.1822	mg
Die Attach	1.315	mg		Bismaleimide Monomer	proprietary data		0.5063	mg
			Supplier	POLY(ETHYLENE GLYCOL) PHENYL ETHER ACRYLATE	56641-05-5		0.0066	mg
			Supplier	2,2-Bis(4-hydroxyphenyl)propane-epichlorohydrin copolymer acrylate	55818-57-0		0.1315	mg
			Supplier	Bis(4-tert-butylcyclohexyl) peroxydicarbonate	15520-11-3		0.0066	mg
			Supplier	2,2-dimethyl-1,3-propanediyl dimethacrylate	1985-51-9		0.1315	mg
			Supplier	2-phenoxy ethyl acrylate	48145-04-6		0.1315	mg
			Supplier	Bisphenol A_Epichlorohydrin Polymer	25068-38-6		0.0066	mg
			Supplier	Other Additive Agents	Proprietary Data		0.263	mg
			Supplier	Formaldehyde Polymer	9003-36-5		0.1315	mg
Epoxy	1.214	mg	Supplier	Imidazole Addition	68490-66-4		0.3642	mg
			Supplier	Bisphenol A_Epichlorohydrin Polymer	25068-38-6		0.1214	mg
			Supplier	Zirconium Dioxide (ZrO2)	1314-23-4		0.1214	mg
			Supplier	Silica Amorphous (SiO2)	7631-86-9		0.1214	mg
			Supplier	Formaldehyde Polymer	9003-36-5		0.4856	mg
Imaging Lens	17.649	mg	Supplier	Titanium Dioxide (TiO2)	13463-67-7		0.9289	mg
			Supplier	Sodium Monoxide (Na2O)	1313-59-3		0.9289	mg
			Supplier	Zinc Monoxide (ZnO)	1314-13-2		0.9289	mg
			B	Antimony Trioxide (Sb2O3)	1309-64-4		0.093	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		0.9289	mg
			Supplier	Potassium Monoxide (K2O)	12136-45-7		0.9289	mg
			Supplier	Silica Crystalline (SiO2)	14808-60-7		12.9117	mg
Mold Compound	7.325	mg	Supplier	Hexahydromethylphthalic anhydride	25550-51-0		0.7325	mg
			Supplier	1,6-Bis(2,3-epoxypropoxy)naphthalene	27610-48-6		0.3663	mg
			Supplier	Bisphenol A_Epichlorohydrin Polymer	25068-38-6		0.3663	mg
			Supplier	Fused Silica (SiO2)	60676-86-0		5.86	mg
Solder Ball	38.864	mg	Supplier	Silver (Ag)	7440-22-4		1.1659	mg

			Supplier	Tin (Sn)	7440-31-5		37.5038	mg
			Supplier	Copper (Cu)	7440-50-8		0.1943	mg
Solder Mask	14.92	mg		Epoxy resin	proprietary data		8.1911	mg
			Supplier	Talc	14807-96-6		0.5222	mg
			Supplier	Misc.	Proprietary Data		0.3133	mg
			Supplier	Carbon Black (C)	1333-86-4		0.0746	mg
			Supplier	Silica Crystalline (SiO2)	14808-60-7		0.2984	mg
			Supplier	Barium Sulfate (BaSO4)	7727-43-7		5.5204	mg
Substrate Copper Foil	9.63	mg	Supplier	Copper (Cu)	7440-50-8		9.63	mg
Substrate - Core Material	61.62	mg		Epoxy resin	proprietary data		13.3531	mg
			Supplier	Fiber Glass (SiO2)	65997-17-3		48.2669	mg
Substrate Plating-Au	2.41	mg	Supplier	Gold (Au)	7440-57-5		2.41	mg
Substrate Plating-Cu	1.93	mg	Supplier	Copper (Cu)	7440-50-8		1.93	mg
Substrate Plating-Ni	5.78	mg	B	Nickel (Ni)	7440-02-0		5.78	mg
Wire Bond - Au	0.945	mg	Supplier	Gold (Au)	7440-57-5		0.945	mg